



C2G  
1ft (0.3m) Cat6a Snagless Unshielded (UTP) Ethernet Network Patch Cable - Orange  
Part No. CG-50836



This Snagless Unshielded Cat6a patch cable is ideal for use with 10GBase-T ports and equipment, such as network adapters, hubs, switches, routers, DSL/cable modems and patch panels, and enables 10 Gigabit data transmission over a 4 pair copper cable allowing connections up to 100 meters. Current Cat6 cabling systems may only support 10 Gigabit Ethernet over limited distances. Each patch cable is fully tested to meet ANSI/TIA 568 C.2 Cat6a channel requirements.

Constructed from high quality cable and plugs, this design offers improved alien cross talk performance. The Snagless hood is ideal for high density switch applications. Available in a variety of colors to easily color-code a network installation. Individual length label on each cable for ease of use.

Features & Benefits

Designed for network adapters, hubs, switches, routers, HDBaseT applications and more	Supports 10 Gigabit networks up to 328ft for fast data transmission and maximum performance
Meets the ANSI/TIA-568-C.2 Cat6a requirements for supporting a wide variety of applications	Constructed with unshielded twisted pair (UTP) wires, designed to counter EMI, RFI, and crosstalk
Snagless connector design for high density environments and protecting the RJ-45 connector's lock	Available in a variety of colors to color-code a network

Specifications

General Info

Product Line	C2G	Color	Orange
UPC Number	757120508366	Country Of Origin	Vietnam
Features	PoE (Power Over Ethernet)	Application Sector	Commercial, Industrial, Residential
Warranty Type	Lifetime	Type	Cable

Dimensions

Product Length US	1.0 FT	Cable Length	1 ft
-------------------	--------	--------------	------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	26 AWG
Cable Type	Booted, Ethernet Patch Cable, Snagless, Unshielded (UTP)	Jacket Rating	Standard / Non-Rated
Cable Diameter	6 mm	Adapter Rear	RJ-45 Male

