ProductSheet

Poly Savi 8410 Office Monaural Microsoft Teams Certified DECT 1920-1930 MHz Headset TAA (8L7F0AA)

Built for the modern office

Ready for the modern office with an intuitive user interface on the universal base that can connect to almost any Savi headset. Ensure flexibility for users with the ability to connect from your computer, desk phone or mobile phone [1].



Be heard clearly
With the Poly Savi 8400 Office series headset system, you can stay focused on your tasks while enjoying crystal-clear conversations thanks to a noise-canceling microphone with close conversation limiting.

Untether from your desk
Enjoy the convenience of hands-free calling and a longer roaming range with the Poly Savi 8400 office series. With up to 13 hours of talk time and the ability to roam up to 590 ft / 180 m means you can keep the calls going, even away from the desk [2].

Multi-device connectivity
Designed for the modern office with 3-way connectivity, the Poly Savi 8400 office series is the perfect solution for business calls allowing you to stay connected in the office. You can even conference four headsets together with the base for increased productivity.

Featuring

3-way connectivity
Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

Crystal-clear calls
Reduce background sounds with noise-canceling microphone and close conversation limiting.

Take it further
Everyone can move, multitask, and get more done with up to 13 hours of talk time on a single charge. Convenient voice prompts notify of mute status, wireless range limit and more.

Privacy is ensured
Privacy of your conversation is ensured: DECT™ security-certified headset.

Training made easy
Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

Specifications

Audio	Noise cancellation with close conversation limiting
Weight	115 g
Weight	0.25 lb
Package dimensions (W x D x H)	185 x 210 x 115 mm
Package weight	300 g
Battery life	Up to 13 hours (talk time); Up to 50 hours (standby time)
Special features	Color display on office base for audio settings management
Minimum System Requirements	USB Type-A port (PC); USB Type-C® port (PC); Bluetooth® (mobile phone); EHS interface (desk phone)
UPC number	197497836684
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Wireless headset; USB Type-A cable; USB Type-C® cable; Office base; AC power adapter; Charging cradle; Telephone interface cable (TIC)

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Does not connect to the Savi 7200 headset.

[2] Line of sight from computer.

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.