

OVERVIEW



1. SD card reader	6. USB-A (USB 5Gbps), Always On
2. USB-A (USB 5Gbps)	7. HDMI
3. Ethernet (RJ-45)	8. USB-C (USB4 40Gbps), with USB PD 3.0 & DP 1.4
4. Kensington Nano Security Slot	9. Headphone / microphone combo jack (3.5mm)
5. USB-C (USB 10Gbps), with USB PD 3.0 & DP 1.4	

PERFORMANCE

Processor

Processor Family

AMD Ryzen™ 3 / 5 / 7 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics
AMD Ryzen™ 3 7335U	4	8	3.0GHz	4.3GHz	2MB L2 / 8MB L3	AMD Radeon™ 660M Graphics
AMD Ryzen™ 5 7535HS	6	12	3.3GHz	4.55GHz	3MB L2 / 16MB L3	AMD Radeon™ 660M Graphics
AMD Ryzen™ 7 7735HS	8	16	3.2GHz	4.75GHz	4MB L2 / 16MB L3	AMD Radeon™ 680M Graphics

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- No preload operating system

Graphics

Graphics**

Graphics	Type	Memory	TGP	Key Features
AMD Radeon™ 660M	Integrated	Shared	Share CPU TDP	DirectX® 12
AMD Radeon™ 680M	Integrated	Shared	Share CPU TDP	DirectX® 12

Monitor Support

Monitor Support

Supports up to 4 independent displays (native display and 3 external monitors via HDMI®, USB-C® and USB4®)

- HDMI® supports up to 4K@60Hz
- USB-C® supports up to 5K@60Hz
- USB4® supports up to 5K@60Hz

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 64GB DDR5-4800

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Memory Type

DDR5-4800

Notes:

[1] Maximum memory is only to test technical readiness of notebook. Available memory to sell would vary.

Storage

Storage Support^[1]

Up to two drives, 2x M.2 SSD

- M.2 2280 SSD up to 2TB

Storage Slot

Two M.2 2280 PCIe® 4.0 x4 slots

Storage Type

Disk Type	Interface	Offering
M.2 2242 SSD	PCIe® NVMe®, PCIe® 4.0 x4	256GB / 512GB / 1TB

Notes:

[1] The system supports dual SSD via two M.2 slots, but Lenovo® only offers one SSD configuration and another SSD slot for user self-extension.
The max storage capacity is only technical readiness and may be different with current Lenovo® storage offerings.

Removable Storage

Card Reader

SD card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Audio™

Microphone

Dual-microphone array with smart noise-cancelling

Camera**

- FHD 1080p + IR hybrid, with privacy shutter, fixed focus
- FHD 1080p, with privacy shutter, fixed focus
- HD 720p, with privacy shutter, fixed focus

Battery

Battery**

- Integrated Li-Polymer 45Wh battery, supports Rapid Charge Pro (charge up to 50% in 30min)
- Integrated Li-Polymer 60Wh battery, supports Rapid Charge (charge up to 80% in 1hr)

Max Battery Life[1]

- Models with 45Wh battery:
MobileMark® 25: 7.46 hr
Local video (1080p) playback@150nits: 14.85 hr
- Models with 60Wh battery:
MobileMark® 25: 11.0 hr
Local video (1080p) playback@150nits: 17.75 hr

Notes:

[1] All battery life claims are approximate maximum and based on results using the MobileMark® 2014, MobileMark® 2018, MobileMark® 25, JEITA 2.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary depending on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter**[1]

- 65W USB-C® (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® slim (wall-mount) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

Notes:

[1] AC adapter offerings depend on the country.

Special Features

Special Features

Modern Standby

DESIGN

Display

Display**

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
14"	WUXGA (1920x1200)	None	IPS ^[1]	300nits	Anti-glare	16:10	1000:1	45% NTSC	60Hz	89°/89°/89°/89°	TÜV Low Blue Light (Software)
14"	WUXGA (1920x1200)	Multi-touch	IPS ^[2]	300nits	Anti-glare	16:10	1000:1	45% NTSC	60Hz	89°/89°/89°/89°	TÜV Low Blue Light (Software)
14"	WUXGA (1920x1200)	None	IPS ^[3]	300nits	Anti-glare	16:10	1000:1	100% sRGB	60Hz	89°/89°/89°/89°	Eyesafe® Certified 2.0

Touchscreen

- Add-on Film Touch, supports 10-point touch
- Non-touch

Notes:

[1], [2], [3] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Input Device

Keyboard

6-row, spill-resistant, multimedia Fn keys

Keyboard Backlight

- LED backlight
- Non-backlight

Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

Mechanical

Dimensions (WxDxH)^[1]

Models	Dimensions
Models with aluminium (top) and aluminium (bottom)	313.5 x 224 x 16.9 mm (12.34 x 8.82 x 0.67 inches)
Models with aluminium (top) and PC-ABS (bottom)	313.5 x 224 x 17.6 mm (12.34 x 8.82 x 0.69 inches)

Weight^[2]

Models	Weight
Models with aluminium (top) and PC-ABS (bottom)	Starting at 1.36 kg (2.99 lbs)
Models with aluminium (top) and aluminium (bottom)	Starting at 1.38 kg (3.04 lbs)

Case Color

Arctic grey, dual-tone design

Surface Treatment

Anodizing sandblasting

Case Material**

- Aluminium (top), PC-ABS (bottom)
- Aluminium (top), aluminium (bottom)

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet^[1]

Gigabit Ethernet, 1x RJ-45, supports Wake-on-LAN

WLAN + Bluetooth^{**}

- Wi-Fi® 6, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, M.2 card^[2]
- Wi-Fi® 6E, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, M.2 card^[3]

Notes:

[1] Wake-on-LAN needs the power adapter plugged in.

[2] Wi-Fi® 6 full features might be limited by country-level restrictions.

[3] Wi-Fi® 6E full features might be limited by country-level restrictions.

6GHz Wi-Fi® 6E operation is dependent on the support of the operating system, routers/APs/Gateways that support Wi-Fi® 6E, and the regional regulatory certifications & spectrum allocation.

Ports^[1]

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 and DisplayPort™ 1.4
- 1x USB-C® (USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 1.4
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x SD card reader

Notes:

[1] The transfer speed of the ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

Docking

Docking

Various docking solutions supported via USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkBook 14 G7 ARP](#)

SECURITY & PRIVACY

Security

Security Chip^[1]

Firmware TPM 2.0 integrated in SoC

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Fingerprint Reader

Touch style fingerprint reader integrated in power button, match-on-chip

BIOS Security

- Hard disk password
- Power-on password
- Self-healing BIOS
- Supervisor password

Other Security

- (Optional) IR camera for Windows® Hello (facial recognition)
- Camera privacy shutter

Notes:

[1] The Discrete TPM 2.0 is technical readiness.

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 2-year (1-yr battery) courier or carry-in service

ACCESSORIES

Bundled Accessories

Bundled Accessories^[1]

None

Notes:

[1] For more compatible accessory solutions, please visit [Accessories for ThinkBook 14 G7 ARP](#).

OPERATING REQUIREMENTS

Operating Environment

Temperature^[1]

- At altitudes up to 2438 m (8,000 ft)
 - Operating: 5°C to 35°C (41°F to 95°F)
 - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
 - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

ENVIRONMENTAL

Sustainability

Material

25% PCC recycled plastic used in the battery pack
50% PCC recycled plastic used in key caps
30% PCC recycled plastic used in speaker
90% PCC recycled plastic used in standard 65W adapter
97% recycled content in PIC cushion
90% recycled content in OBP bag
FSC certified content in carton box

CERTIFICATIONS

Green Certifications^[1]

Green Certifications^[2]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered^[3]
- ErP Lot 6
- ErP Lot 26
- RoHS compliant
- TCO Certified 9.0

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2] EPEAT™ registration and ENERGY STAR® certification are dependent on system OS. Please visit epeat.net and energystar.gov for more information.

[3] EPEAT™ is registered where applicable, please visit epeat.net for registration status by country.

Other Certifications**Mil-Spec Test**

MIL-STD-810H military test passed

Other Certifications

- (Optional) Eyesafe® Certified 2.0
- (Optional) TÜV Rheinland® Low Blue Light (Hardware Solution)
- (Optional) TÜV Rheinland® Low Blue Light (Software Solution)

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

