



Product Overview:

Available in three lengths, the LA-391 allows you to order RG-58 cable complete with both BNC connectors pre-assembled and ready to use.

Highlights:

- RG-58 cable complete with RG-58 connectors installed
- In 50', 100', or 150' options.



**WARNING:** This product can expose you to chemicals including DIDP, which is known to the State of California to cause cancer. For more information, go to [www.P65Warning.ca.gov](http://www.P65Warning.ca.gov)

Includes:  
RG-58 50 Ohm Preassembled Coaxial Cable

Product Specification: RG-58 50 Ohm Preassembled Coaxial Cable	
Physical	
Material	Polyethylene Insulation, PVC Jacket, tinned copper conductor, tinned copper braided shield
Diameter	Outer: .192 in. (4.88 mm), Inner: .116 in. (2.95 mm)
Cable Type	RG-58/U 50 Ohm
Shipping Weight	4 lbs. (1.81 kg) per 100 ft.
Unit Weight	3.5 lbs. (1.6 0 kg) per 100 ft.
RF	
Attenuation	2 dB per 50 ft. on 72 MHz, 4 dB per 50 ft. on 216 MHz