


ThinkPad L13 2-in-1 Gen 5 Intel

With powerful performance and a stunning display, this powerhouse device is designed to meet the diverse needs of on-the-go professionals. Up to Intel® U Series Core™ Ultra 7 Processor ensures lightning-fast performance, allowing professionals to crunch numbers, analyze data, and run complex applications with ease. With up to 32GB memory and 1TB SSD storage, it provides ample space to store critical documents, presentations and reports securely. The discrete TPM 2.0 adds an extra layer of security, safeguarding sensitive information against potential threats.



Built for business with cutting-edge technology

The mid-range ThinkPad L Series offers enterprise docking, enhanced security features and optional remote management capabilities.

Whether in the boardroom or outdoors, the 13.3" WUXGA multi-touch display with 100% sRGB and up to 400nits brightness provides stunning visuals, perfect for presentations and video conferences. Stay connected with Wi-Fi 6E and Thunderbolt 4, USB4, and HDMI ports, ensuring seamless communication and collaboration with teams.

With an optional fingerprint reader and IR camera, they can unlock the device securely with just a touch or a glance. The long-lasting battery life ensures uninterrupted productivity, while Wi-Fi 6E keeps professionals connected to high-speed internet networks.

Secure access effortlessly with dual authentication options – a fingerprint reader and IR camera. Combined with the discrete TPM 2.0 chip, data remains safeguarded against unauthorized access, enhancing peace of mind.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..

Accessories

Lenovo Wired VoIP Headset

- Optimized audio comfort
- Lightweight design
- Seamless management



PN: Teams : 4XD1M45626, UC : 4XD1M39028

Lenovo Go USB-C Wireless Mouse

- Ergonomically designed ambidextrous mouse with Villi painted grip and wireless connection via USB-C dongle
- Silent buttons with 2-way scroll wheel (up/down), programmable Utility Button on the side
- Default functions optimized for Teams calls, can be configured through Lenovo Go Central Software



PN: 4Y51C21216

ThinkPad L13 2-in-1 Gen 5 Intel

Performance

Processor

Intel U Series Core Ultra 5/7 Processor (Series 1)

Operating System

Windows 11 Pro
Windows 11 Home
Windows 11 DG Windows 10 Pro 64
Ubuntu Linux

Graphics

Intel Graphics (integrated)

Memory

8GB LPDDR5-6400, soldered
16GB LPDDR5-6400, soldered
32GB LPDDR5-6400, soldered

Storage¹

Up to 1x 1TB M.2 2280 PCIe NVMe SSD

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Dual-microphone array, far-field, Dolby Voice

Camera*

Front HD 720p, with privacy shutter
Front HD 720p, with privacy shutter; rear 5.0MP
Front FHD 1080p + IR hybrid, with privacy shutter
Front FHD 1080p + IR hybrid, with privacy shutter; rear 5.0MP

Battery²

46Wh (up to 11.03 hr) battery, Rapid Charge

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display³

13.3" WUXGA (1920x1200) IPS ARAS 16:10
- 300nits, 100% sRGB, 60Hz, touch

13.3" WUXGA (1920x1200) IPS AGAS 16:10
- 400nits, 100% sRGB, low power, 60Hz, Eyesafe, touch

³IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Multimode

Laptop, tent, stand and tablet modes supported by 360° hinge

Pen*

Lenovo Integrated Pen*

Keyboard

6-row, spill-resistant, optional backlight

Touchpad

TrackPoint and Mylar surface touchpad
56 x 115 mm (2.24 x 4.53 inches)

Dimensions⁴

305 x 218 x 17.06 mm (12.0 x 8.58 x 0.67 inches)

⁴The system dimensions may vary depending on configurations.

Weight⁵

Starting at 1.32 kg (2.92 lbs)

⁵The system weight is approximate and may vary depending on configurations

Color

Black
Grey

Case material

Aluminium (top), GFRP (bottom)

Connectivity

WLAN + Bluetooth^{6 7}

Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.3

⁶Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

⁷Bluetooth 5.3 operation requires Windows 11.

WWAN*

4G LTE CAT6 with embedded eSIM*

NFC

Near Field Communication*

Ports

2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On
1x USB-C (USB 20Gbps / USB 3.2 Gen 2x2), with USB PD 3.0 & DP 1.4
1x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0
Kensington Nano Security Slot
Smart card reader*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*

Manageability

System Management⁸

Intel vPro Enterprise*

⁸Intel vPro offers a superset of DASH's defined capabilities.

Certifications

Green Certifications^{9 10 11}

EPEAT Gold Registered
ENERGY STAR 8.0
ErP Lot 6
ErP Lot 26
TCO Certified 9.0
RoHS compliant

⁹The items listed under the "Green Certifications" section may not only refer to certification but also registration (self-declaration).

¹⁰EPEAT registration and ENERGY STAR certification are dependent on system OS.

¹¹EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.

Other Certifications

Eyesafe Certified 2.0*
TÜV Rheinland Low Blue Light (Hardware Solution)*
MIL-STD-810H