

ThinkCentre M75s Gen 2

Looking for a versatile device to support existing or new desk workers in your company? This compact, space-saving desktop can be configured to meet a wide variety of user expectations - from basic admin use to extensive productivity tasks. It comes with thoughtful features like Smart Power-On to which enables the PC to be started via a keyboard shortcut instead of reaching for the power button.



Rugged compact performance primed for business

Whether you run a small business or a department of an enterprise, these desktops are built to handle every workload. Easy to manage, they offer great expandability, rapid processing, and seamless switching between multiple programs.

For employees working with data or graphics, configure the device with 128GB DDR4 memory to boost multitasking performance, AMD Radeon 520 graphics, up to 2x fast SSD storage drives, and the latest AMD Ryzen™ 9 Pro processor.

There are 9x USB ports including 5 located on the front of the device. If data security is a concern, Smart USB protection can block data transfer but still enable keyboards, mice and printers to be used.

This versatile desktop offers a great balance of performance and expansion features, with the enterprise security and productivity features you need.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..

Accessories

ThinkVision T27i-10

- 27" Full HD monitor with wide viewing angle and 1000:1 contrast ratio
 - 1x HDMI, 1x DisplayPort, 1x VGA, 4x USB3.0, 1x USB3.0 Type-B upstream, audio out
 - Lift, Tilt, Pivot, Swivel stand for viewing comfort
-



ThinkVision T24i-10

- 23.8" Full HD monitor with 72% NTSC colour gamut & anti-glare coating
 - 1x HDMI, 1x DisplayPort, 1x VGA, 4x USB3.0, 1x USB3.0 Type-B upstream, audio out
 - Lift, Tilt, Pivot, Swivel stand for viewing comfort
-



ThinkCentre M75s Gen 2

Performance

Processor

Up to AMD Ryzen 9 Pro processor

Operating System

Powered by Windows 11 Pro

Graphics

AMD Radeon Vega 11, 8 or 3, optional AMD Radeon 520 2GB

Memory

Up to 128GB DDR4-3200

Storage**Internal storage:**

up to 1x 3.5" 2TB SATA HDD + 1x 2.5" 1TB SATA HDD or 2x 2.5" 256GB SATA SSD

M.2 SSD:

up to 1x 1TB M.2 PCIe NVMe

Optical*

Optional DVD-ROM or DVD burner

Design

Dimensions

Width: 93mm (3.6") Depth: 298mm (11.7") Height: 340mm (13.4")

Weight

Starting at 5.3kg (11.7lb)

Expansion Slots

PCIe x16, low-profile

PCIe x1, low-profile

Connectivity

Front I/O

2x USB 3.2 Gen 2, 2x USB 3.2 Gen 1, 1x USB 3.2 Type-C Gen 1, 1x microphone (3.5mm), 1x headphone / microphone combo jack (3.5mm), optional 3-in-1 card reader

Rear I/O

4x USB 2.0, 1x serial (9-pin), 1x ethernet (RJ-45), 2x DisplayPort, 1x HDMI, 1x line-out (3.5mm); Optional: 2x USB 3.2 Gen 1 via PCIe x1, 2x USB 3.2 Type-C Gen 2 via PCIe x4, 1x 2nd serial (9-pin), 1x parallel (25-pin)

Security & Privacy

Security

Kensington lock slot
Padlock slot
Smart USB protection
Hardware TPM

Certifications

Green Certifications

EPEAT Gold, Energy Star 8.0.

Optional Mechanical Peripherals

Optional Mechanical Peripherals

ThinkCentre Dust Filter
