



HU621

V7 PREMIUM USB HEADSET WITH ANC

V7's Premium USB Headset with ANC helps keep distractions down and your productivity up. Enhanced audio performance combined with professional features that adapt to your working day lets you perform at your best.

Enjoy optimal speech clarity with the environmental noise cancelling technology (ENC) - perfect for busy office settings so callers hear only you and not the conversations of your workmates. And Hybrid Active Noise Cancellation (ANC) helps reduce distracting high-frequency noises around the office like noisy air conditioning - so you can focus on the task at hand.

Other thoughtful features include 'Call-Busy' indicators so others can see your status, an on-cable remote and a convenient Lift-to-Mute boom.

Fully compatible with popular video conferencing programs including Microsoft Teams, Zoom, Google Meet, and many others.

- Active Noise Cancellation (ANC) helps reduce outside noise
- Noise cancelling (ENC) microphone for optimal communication
- Lift-to-Mute boom
- Call busy indicators
- On-cable remote control
- 1.8 meter cable with USB-A and USB-C connectors
- For Windows 10 and later, macOS and ChromeOS PCs



ALL-DAY COMFORT & PERSONALIZED FIT

Lightweight design - Ideal for extended wear. Adjustable headband, padded ear cushions and rotating ear cups provide a tailored fit



MINIMIZE DISTRACTIONS

ANC helps reduce high frequency noise and distraction



CLEAR COMMUNICATION

ENC noise cancelling microphone technology ensures optimal communications, whether in a busy office or remote work environment



LIFT-TO-MUTE BOOM MICROPHONE

Mute and unmute the microphone quickly and easily by raising or lowering the boom arm

HU621

V7 PREMIUM USB HEADSET WITH ANC



IMPROVE FOCUS ACTIVE NOISE CANCELLATION (ANC)

Enhance workspace focus by lowering outside noise and distractions




CALL BUSY INDICATORS

Integrated "call-busy" lights let others see your call status

MAXIMUM COMFORT DURING EXTENDED USE

Lightweight design with pivoting speakers, a fully adjustable fit and ultrasoft ear cushions



CLEAR COMMUNICATION ENVIRONMENTAL NOISE CANCELLATION (ENC)

Allow clients and colleagues to focus on you, not other conversations around the office




MUTE THE MIC WITH LIFT-TO-MUTE

Mute calls instantly by raising the boom arm and lower to resume speaking



SIMPLE CONTROLS - DUAL CONNECTIONS

The headset includes simple on-cable controls including Call Answer/End, Mute and Volume +/- and features a USB-C connector cable with an inline USB-A adapter, ensuring plug-n-play connectivity with all Windows 10 or later, Mac, or Chrome-based computers with an available USB-C or USB-A port.



Technical Specifications

GENERAL

Region:	US
SKU:	12GT04
Model:	HU621
UPC:	662919116526
Warranty:	2 years
Compliance:	CE, FCC, RoHS, UKCA
Country Of Origin:	China
Package Type:	OEM Box
Package Includes:	Headset, inline USB adapter, storage bag, quickstart guide, warranty and compliance documents

COLOR

Color:	Black
Accent Color:	Red

MICROPHONE

Type:	ENC noise canceling technology using two microphones
Boom:	135 mm (5.3 in) with 270° rotation and Lift-to-Mute
Mic Sensitivity:	-38 dBV/Pa ± 3 dB
Frequency range:	100 Hz to 14 kHz optimized for PC wideband audio up to 7 kHz

PACKAGE DIMENSIONS

Package Dimensions (L/W/H):	203.2 x 254 x 88.9 mm (8 x 10 x 3.5 in)
Shipping Weight:	12 oz (345.1 g)

DESIGN

Audio Segment:	Premium
Headset Form Factor:	On Ear
Controls:	Call answer/end, volume, mute

TECHNICAL

Connectivity:	USB-C with USB-A inline adapter
Decibels:	120 dB SPL ± 3 dB @1KHz
Impedance:	32 Ω
Driver Size:	32 mm
Frequency Range:	20 Hz to 20 kHz
Mic Sensitivity:	-38dBV/Pa
User Controls:	Call answer/end; Mute; Volume +/-; ANC on/off (on headset), Lift-to-Mute boom
ANC:	Hybrid Active Noise Cancellation

AUDIO

Speaker size:	32 mm
Speaker sensitivity:	120 dB SPL ± 3 dB @1KHz
Speaker max input power:	30 mW
Speaker Frequency Range:	20 Hz to 20 kHz
Impedance:	32 Ω

PRODUCT DIMENSIONS

Product Dim (L/W/H):	171.5 x 69.9 x 194.3 mm (6.75 x 2.75 x 7.65 in)
Product Weight:	190 g (6.7 oz)