



# NetShelter™ SX & SX Advanced Enclosures

The IT and AI racks you can feel certain about

Get ready for AI, and bring your business the power of global scale, sustainable leadership and unparalleled quality.



## SX Advanced for AI

- Space-optimized for liquid cooling, power distribution, and cabling
- Stronger, larger XL and XXL models
- Rack, stack & ship-ready with shock packaging and reinforced load ratings

Available for quote



## Peace of mind

- Built with all-steel construction
- Secured with 3-point locking system
- Backed by 5-year warranty



## More computing in less space

- Quality built IT racks made for AI applications and everyday excellence
- Outstanding load capacity, airflow and security



## Simplified daily workflows

- Makes daily operations more efficient, predictable and enjoyable
- Packed with features that make installation faster, easier and precise
- Ample space for equipment, organization and maintenance



	Available for quote	NEW		NEW		NEW	
	NetShelter SX Advanced		NetShelter SX Shock Package (original)		NetShelter SX (latest generation)	NetShelter SX (original)	
Static load	4250 lb. / 1928 kg	NEW	3750 lb. / 1705 kg*		4000 lb. / 1814 kg*	NEW	3750 lb. / 1705 kg*
Dynamic load	3500 lb. / 1588 kg	NEW	2250 lb. / 1020 kg*		2250 lb. / 1020 kg*	NEW	2250 lb. / 1020 kg*
Shipping load	3500 lb. / 1588 kg	NEW	2000 lb. / 907 kg		—		—
Shock packaging	✓	NEW	✓		—		—
Equipment mounting rails	19" EIA, adjust in .5 in. (12.7 mm) increments		19" EIA, adjust in .25 in. (6 mm) increments		19" EIA, adjust in .25 in. (6 mm) increments		19" EIA, adjust in .25 in. (6 mm) increments
Door perforation	80%		69%		80%		69%
Front door swing	130°, reversible, curved front		130°, reversible, curved front		270°(180 bayed), reversible, curved front		130°, reversible, curved front
Rear door swing	130°, flat front		130°, flat front		270°, flat front		130°, flat front
Side panels	Split, lockable		Split, lockable		Split, lockable		Split, lockable
Baying kit	Included		Included		Included		Included
Roof	4 extra large cable entry points		5 large cable entry points (3 front, 2 rear)		5 large cable entry points (3 front, 2 rear)		5 large cable entry points (3 front, 2 rear)
Bottom plate	Optional		Optional		Optional		Optional
Locking	3-point locking		Single-point locking		3-point locking		Single-point locking
Casters & leveling feet	Included		Included		Included		Included
Rear accessory	Full-height 0U accessory channels*		Full-height 0U accessory channels*		Full-height 0U accessory channels*		Full-height 0U accessory channels*
Door handles**	Key locking**		Key locking**		Key locking**		Key locking**
Toolless features	Doors, roof, roof cable trough (optional)		Doors, roof, roof cable trough (optional)		Doors, roof, roof cable trough (optional)		Doors, roof, roof cable trough (optional)
Certifications	UL, ISTA, RoHS, REACH		UL, ISTA, RoHS, REACH		UL, ISTA, RoHS, REACH		UL, ISTA, RoHS, REACH
Warranty	5 years		5 years		5 years		5 years

\*See SKUs for exact model specification. \*\*Options for combination lock, keycard access, and unique key cylinders available.

Learn more

# NetShelter SX & SX Advanced

## Technical specifications

	Model (Black)	Available in*		Model (White)	Available in*	Rack Units	Dimensions (mm)			Max Equipment Depth (mm)	Static (lb.)	Dynamic (lb.)	Shipping (lb.)	0U Accessory Channels	Doors & Sides		
		H	W				D										
NetShelter SX Advanced	High Strength & Shock Packaged	AR9557SPB2	Available for quote		-	-	48	2258	750	1295	1143	4250	3500	3500	4	✓	
		AR9587SPB2	Available for quote		-	-	48	2258	800	1295	1143	4250	3500	3500	4	✓	
		AR9657SPB2	Available for quote		-	-	48	2258	750	1470	1318	4250	3500	3500	4	✓	
		AR9558SPB2	Available for quote		-	-	52	2436	750	1295	1143	4250	3500	3500	4	✓	
		AR9588SPB2	Available for quote		-	-	52	2436	800	1295	1143	4250	3500	3500	4	✓	
		AR9658SPB2	Available for quote		-	-	52	2436	750	1470	1318	4250	3500	3500	4	✓	
NetShelter SX (latest generation)	Server Racks	AR3100B2	NAM	EUR	AR3100W2	NAM	42	1991	600	1070	915	4000	2250	-	2	✓	
		AR3150B2	NAM	EUR	AR3150W2	NAM	42	1991	750	1070	915	4000	2250	-	2	✓	
		AR3300B2	NAM	EUR	AR3300W2	NAM	EUR	42	1991	600	1200	1048	4000	2250	-	4	✓
		AR3350B2	NAM	EUR	AR3350W2	NAM	EUR	42	1991	750	1200	1048	4000	2250	-	4	✓
		AR3180B2	NAM	EUR	-	-	-	42	1991	800	1070	915	4000	2250	-	2	✓
		AR3380B2	NAM	EUR	AR3380W2	EUR	-	42	1991	800	1200	1048	4000	2250	-	4	✓
		AR3105B2	NAM	EUR	AR3105W2	NAM	-	45	2124	600	1070	915	4000	2250	-	2	✓
		AR3155B2	NAM	EUR	AR3155W2	NAM	-	45	2124	750	1070	915	4000	2250	-	2	✓
		AR3305B2	NAM	EUR	AR3305W2	NAM	-	45	2124	600	1200	1048	4000	2250	-	4	✓
		AR3355B2	NAM	EUR	AR3355W2	NAM	-	45	2124	750	1200	1048	4000	2250	-	4	✓
		AR3107B2	NAM	EUR	-	-	-	48	2258	600	1070	915	4000	2250	-	2	✓
		AR3157B2	NAM	EUR	-	-	-	48	2258	750	1070	915	4000	2250	-	2	✓
		AR3307B2	NAM	EUR	AR3307W2	NAM	EUR	48	2258	600	1200	1048	4000	2250	-	4	✓
		AR3357B2	NAM	EUR	AR3357W2	NAM	EUR	48	2258	750	1200	1048	4000	2250	-	4	✓
		AR3387B2	NAM	EUR	AR3387W2	EUR	-	48	2258	800	1200	1048	4000	2250	-	4	✓
		AR3187B2	NAM	EUR	-	-	-	48	2258	800	1070	915	4000	2250	-	2	✓
		AR3308B2	NAM	EUR	AR3308W2	NAM	EUR	52	2436	600	1200	1048	4000	2250	-	2	✓
		AR3358B2	NAM	EUR	AR3358W2	EUR	-	52	2436	750	1200	1048	4000	2250	-	2	✓
	AR3388B2	NAM	EUR	AR3388W2	EUR	-	52	2436	800	1200	1048	4000	2250	-	4	✓	
	Networking	AR3140B2	NAM	EUR	-	-	42	1991	750	1070	915	4000	2250	-	2	✓	
AR3340B2		NAM	EUR	AR3340W2	NAM	EUR	42	1991	750	1200	1048	4000	2250	-	4	✓	
AR3347B2		NAM	EUR	-	-	48	2258	750	1200	1048	4000	2250	-	4	✓		
Colo	AR3200B2	NAM	EUR	-	-	20 (x2)	1991	600	1070	915	4000	2250	-	0	✓		
NetShelter SX (original)	Server Racks	AR3003	WW	-	-	12	658	600	889	756	600	600	-	2	✓		
		AR3103	WW	-	-	12	658	600	1070	921	600	600	-	2	✓		
		AR3006	WW	-	-	18	925	600	889	756	900	900	-	2	✓		
		AR3106	WW	-	-	18	925	600	1070	921	900	900	-	2	✓		
		AR3104	WW	-	-	24	1198	600	1070	915	3000	2250	-	2	✓		
		AR3100TAA**	NAM	-	-	42	1991	600	1070	915	3750	2250	-	2	✓		
		AR3105TAA**	NAM	-	-	45	2124	600	1070	915	3750	2250	-	2	✓		
		-	-	AR3107W	WW	48	2258	600	1070	915	3750	2250	-	2	✓		
		AR3107TAA**	NAM	-	-	48	2258	600	1070	915	3750	2250	-	2	✓		
		-	-	AR3157W	WW	48	2258	750	1070	915	3750	2250	-	2	✓		
	AR3158	WW	-	-	52	2436	750	1070	915	3750	2250	-	2	✓			
	Shock Packaged	AR3100SP	WW	-	-	42	1991	600	1070	915	3750	2250	2000	2	✓		
		AR3150SP	WW	-	-	42	1991	750	1070	915	3750	2250	2000	2	✓		
		AR3300SP	WW	AR3300WSP	WW	42	1991	600	1200	1048	3750	2250	2000	4	✓		
		AR3350SP	WW	AR3350WSPX832	WW	42	1991	750	1200	1048	3750	2250	2000	4	✓		
		AR3105SP	WW	-	-	45	2124	600	1070	915	3750	2250	2000	2	✓		
		AR3155SP	WW	-	-	45	2124	750	1070	915	3750	2250	2000	2	✓		
		AR3305SP	WW	-	-	45	2124	600	1200	1048	3750	2250	2000	4	✓		
		AR3355SP	WW	-	-	45	2124	750	1200	1048	3750	2250	2000	4	✓		
		AR3107SP	WW	-	-	48	2258	600	1070	915	3750	2250	2000	2	✓		
AR3157SP		WW	AR3157WSP	WW	48	2258	750	1070	915	3750	2250	2000	2	✓			
AR3307SP	WW	AR3307WSP	WW	48	2258	600	1200	1048	3750	2250	2000	4	✓				
AR3357SP	WW	-	-	48	2258	750	1200	1048	3750	2250	2000	4	✓				

Regional availability key: **NAM** = North America; **EUR** = Europe; **WW** = Worldwide

\*Commercial Reference (CR) availability is generalized and may not cover all countries. Please check our website to confirm specific CR availability in your country.

\*\*TAA compliant model. All NetShelter products listed are UL, ISTA, RoHS, and REACH certified.

[Learn more](#)

©2025 Schneider Electric. Life Is On | Schneider Electric is a trademark and the property of Schneider Electric SE, its subsidiaries and affiliated companies. All rights reserved.