



Product Overview:

Order a length of cable needed for your pre-designed RF or IR assistive listening system with the LA-390 preassembled cable. Each order comes with both BNC connectors attached to our RG-8 cable.

Highlights:

- RG-8 cable and BNC connectors made for use with RF and IR system installations
- Longest runs with lowest signal loss



WARNING: This product can expose you to chemicals including DIDP, which is known to the State of California to cause cancer. For more information, go to www.P65Warning.ca.gov

Includes:

One (1) RG-8 50 Ohm Preassembled Coaxial Cable in three length options.

Product Specification: RG-8 50 Ohm Preassembled Coaxial Cable	
RF	
Attenuation	1 dB per 50 ft. on 72 MHz, 2 dB per 50 ft. on 216 MHz
Physical	
Cable Type	RG-8/U Low Loss 50 Ohm
Material	Foam Polyethylene Insulation, PVC Jacket, bare copper conductor, bare copper braided shield
Diameter	Outer: .403 in. (10.24 mm), Inner: .285 in. (7.24 mm)
Unit Weight	14.2 lbs. (6.5 kg) per 100 ft.
Shipping Weight	15.0 lbs. (6.8 kg) per 100 ft.