



C2G

15ft (4.6m) TAA-Compliant F-Series Cat5e Snagless Unshielded (UTP) Network Cable - Blue

Part No. AVD_CG_C2G43417



This Cat5e cable meets stringent TAA compliant requirements and is approved for use in United States government projects and facilities. This Snagless Unshielded Cat5e network cable is designed for network adapters, hubs, switches, routers, servers and more. Meets or exceeds all ANSI/TIA-568.2-D Category 5e industry standards for supporting a wide variety of applications, including 1000BASE-T (1 Gigabit Ethernet). Constructed with premium, made in the USA copper cabling with enhanced 350 Mhz maximum frequency for increased performance over standard Cat5e cables. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief.

Features & Benefits

TAA-compliant	Constructed with high quality, made in the USA raw cable for consistent, reliable performance
Snagless RJ45 connector design protects clips from being easily snapped off – great for applications with high insertion cycles	Standard RJ45 connectors and unshielded twisted pair wires
50-micron gold-plated contacts improve signal integrity	Available in lengths up to 100ft
Lifetime warranty	

Specifications

General Info

Product Line	C2G	Color	Blue
UPC Number	757120434177	Country Of Origin	Mexico
Features	PoE (Power Over Ethernet)	Application Sector	Commercial, Industrial, Residential
Warranty Type	Lifetime	Type	Cable

Dimensions

Product Length US	15.0 FT	Cable Length	15 ft
-------------------	---------	--------------	-------

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	REACH Compliant	Yes
--------------	-----	-----------------	-----

Buy American Act Compliance

TAA Compliant	Yes
---------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Jacket Application	Riser Rated	Cable Type	Booted, Ethernet Patch Cable, Unshielded (UTP)
Jacket Rating	CMR Rated	Cable Diameter	5.5 mm
Adapter Rear	RJ-45 Male	Adapter Front	RJ-45 Male