



This Cat6 cable meets stringent TAA compliant requirements and is approved for use in United States government projects and facilities. This Snagless Unshielded Cat6 network cable is designed for network adapters, hubs, switches, routers, servers and more. Meets or exceeds all ANSI/TIA-568.2-D Category 6 industry standards for supporting a wide variety of applications, including 1000BASE-T (1 Gigabit Ethernet). Constructed with premium, made in the USA copper cabling with enhanced 600 MhZ maximum frequency for increased performance over standard Cat6 cables. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a wide variety of colors to easily color-code your network installation.

## Features & Benefits

|                                                                                                                                 |                                                                                               |
|---------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------|
| TAA-compliant                                                                                                                   | Constructed with high quality, made in the USA raw cable for consistent, reliable performance |
| Snagless RJ45 connector design protects clips from being easily snapped off – great for applications with high insertion cycles | Standard RJ45 connectors and unshielded twisted pair wires                                    |
| 50-micron gold-plated contacts improve signal integrity                                                                         | Available in a variety of colors and lengths up to 100ft                                      |
| Lifetime warranty                                                                                                               |                                                                                               |

## Specifications

### General Info

|               |                           |                    |                                     |
|---------------|---------------------------|--------------------|-------------------------------------|
| Product Line  | C2G                       | Color              | Orange                              |
| UPC Number    | 757120435372              | Country Of Origin  | Mexico                              |
| Features      | PoE (Power Over Ethernet) | Application Sector | Commercial, Industrial, Residential |
| Warranty Type | Lifetime                  | Type               | Cable                               |

### Dimensions

|                   |         |              |       |
|-------------------|---------|--------------|-------|
| Product Length US | 10.0 FT | Cable Length | 10 ft |
|-------------------|---------|--------------|-------|

### Listing Agencies / 3rd Party Agencies

|              |     |                 |     |
|--------------|-----|-----------------|-----|
| CE Certified | Yes | REACH Compliant | Yes |
|--------------|-----|-----------------|-----|

Buy American Act Compliance

TAA Compliant      Yes

Technical Information

|                    |                          |                |                                                |
|--------------------|--------------------------|----------------|------------------------------------------------|
| Jacket Material    | PVC (Polyvinyl Chloride) | Wire Gauge     | 24 AWG                                         |
| Jacket Application | Riser Rated              | Cable Type     | Booted, Ethernet Patch Cable, Unshielded (UTP) |
| Jacket Rating      | CMR Rated                | Cable Diameter | 5.6 mm                                         |
| Adapter Rear       | RJ-45 Male               | Adapter Front  | RJ-45 Male                                     |