



C2G

3ft (0.9m) TAA-Compliant F-Series Cat6 Non-Booted Unshielded (UTP) Network Cable - Black

Part No. AVD_CG_C2G43626



This Cat6 cable meets stringent TAA compliant requirements and is approved for use in United States government projects and facilities. This non-booted unshielded Cat6 network cable is designed for network adapters, hubs, switches, routers, servers and more. Meets or exceeds all ANSI/TIA-568.2-D Category 6 industry standards for supporting a wide variety of applications, including 1000BASE-T (1 Gigabit Ethernet). Constructed with premium, made in the USA copper cabling with enhanced 600 MhZ maximum frequency for increased performance over standard Cat6 cables. Available in a wide variety of colors to easily color-code your network installation.

Features & Benefits

TAA-compliant	Constructed with high quality, made in the USA raw cable for consistent, reliable performance
Standard RJ45 connectors and unshielded twisted pair wires	50-micron gold-plated contacts improve signal integrity
Available in lengths up to 25ft	Lifetime warranty

Specifications

General Info			
Product Line	C2G	Color	Black
UPC Number	757120436263	Country Of Origin	Mexico
Features	PoE (Power Over Ethernet)	Application Sector	Commercial, Industrial, Residential
Warranty Type	Lifetime	Type	Cable
Dimensions			
Product Length US	3.0 FT	Cable Length	3 ft
Listing Agencies / 3rd Party Agencies			
CE Certified	Yes	REACH Compliant	Yes
Buy American Act Compliance			
TAA Compliant	Yes		
Technical Information			
Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG

Jacket Application	Riser Rated	Cable Type	Ethernet Patch Cable, Unbooted, Unshielded (UTP)
Jacket Rating	CMR Rated	Cable Diameter	5.6 mm
Adapter Rear	RJ-45 Male	Adapter Front	RJ-45 Male