

CHERRY XTRFY NGALE R

Premium USB mic for recording and streaming



Models may vary from the image shown

STREAM, RECORD AND STAND OUT.

The NGALE R features everything you need for high-quality sound capture without hassle. This standalone USB mic comes with a cardioid polar pattern and smart noise cancellation to capture your voice with clarity, while the RGB illuminated, retro-inspired design makes your streams and videos look as good as they sound.

CRISP AND CLEAR.

The NGALE R prioritizes sound quality over multiple polar patterns, featuring a high-quality cardioid capsule for streaming, voiceovers and solo recordings with greater detail.

LOW-CUT FILTER FOR INTENSE GAMING.

Record or stream your voice across the microphone's entire frequency range, and activate the low-cut filter to minimize noise when gaming. To bring you the best sound quality, the NGALE R offers dual recording modes, easily switchable by holding the touch mute button.

QUICK TO SET UP, EASY TO USE.

The NGALE R easily connects via USB for instant plug-and-play functionality and includes a convenient desk stand. Compatible with 3/8" thread stands, it can also be mounted on a boom arm. Once

the USB cable is plugged in, the on-device controls provide quick access to settings like mute, microphone gain and headset volume. At the touch of a button, you can also activate the low-cut filter, and switch between a range of different LED colors and RGB effects.

HIGHLIGHTS

- Standalone microphone for streaming and recording
- USB plug and play
- Adjustable RGB illumination
- On-device settings and monitoring
- Dual recording modes – low-cut filter for gaming

PRODUCT SPECIFICATIONS

Dimensions product without packaging:	3,94 in x 3,39 in x 7,6 in
Cable-length:	6.56 ft
Product approvals:	<ul style="list-style-type: none">• China RoHS• CE• EU RoHS• FCC• ICES-003 (Canada)• KCC• REACH• UKCA• CP65
System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none">• Linux• Mac OS• Windows 7 or higher
Scope of delivery:	<ul style="list-style-type: none">• microphone• USB-cable• Manual
Sensitivity:	4.7mV/Pa
Model number:	CX-NGALE-R-RGB-BLACK
Max SPL:	112 db
THD Ratio:	0,5 %
Bitrate:	24 bit

Sampling rate: 96 KHz
Warranty: 2 years warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

EAN & Part number	Color
7340086913058 CX-NGALE-R-RGB-BLACK	black

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.