


# 5653RK

Creative Touch 5-Series



- **Integrated Google Play Store**
- **Embedded 18W speakers and 8W subwoofers for impressive sound quality as well as 8 array Microphone**
- **Android 13 OS for improved multitasking & security**
- **Optional Sensor Box - NFC reader & air quality sensors**

Create. Connect. Inspire. Teacher led technology

Optoma's interactive displays are designed to fit the needs of teachers and students seamlessly. By listening to educators and gathering customer feedback, Optoma creates solutions that remove the challenging barriers facing teachers today. The result; intuitive user-friendly software to work in harmony with the way you educate - Create. Connect. Teach.



# Specifications

UPC: 796435 69 064 9, EAN: 5055387667877, Colour: Grey



<b>Display</b>	
Back light	Direct type LED
Size (diagonal)	65"
Resolution	3840(H)*2160(V) Pixel (UHD 4K)
Brightness	400 cd/m2
Contrast ratio	5,000:1
Viewing angle	178°
Response time	6ms
Life	50,000 hours
Display colours	1.07
Speaker count	2
Watts per speaker	18W
Surface hardness	7H
Glass	Toughened, Anti-glare/Fingerprint / HAZE:3-8%
Haze	3-8%
Air gap	0.60mm
Pencil hardness	9H
Touch resolution	32768 x 32768

<b>Physical spec</b>	
Dimensions (W x D x H) mm	1488 x 86 x 908
Wall-hanging screw spec	M8*25mm
VESA holes	600*400mm
In the box	European standard power cord (3m) American standard power cord (3m) U.K standard power cord (3m) USB cable (3m) HDMI cable (3m) USB-C cable (1.5m) 2x Writing Pen Remote control Battery Pen holder Quick start guide

<b>Connections</b>	<b>Inputs</b> 4 x HDMI 2.0, 1 x DisplayPort, 1 x Audio 3.5mm, 1 x S/PDIF, 1 x USB-A service, 4 x USB-A 3.0, 1 x RS232, 1 x RJ45, 2 x USB-C, 1 x OPS slot <b>Outputs</b> 1 x HDMI 2.0, 1 x Audio 3.5mm, 1 x RJ45
Bezel size (top)	35.40mm
Bezel size (bottom)	38.10mm
Bezel size (left)	16.70mm
Bezel size (right)	16.70mm
Net weight	38.6 kg
Gross weight	48.2 kg
Wireless - antenna	Optional Accessory
Wireless - technology	802.11ac/b/g/n/a/ax
Wireless - operating frequency	2.4Ghz/5GHz

<b>Touch system</b>	
System	Windows11/Windows10/Windows8/Windows7/Windows XP /Linux/Mac (1 Touch point only)/Android/Chrome
Touch accuracy	1.00mm
Touch point	Up to 32 points touch and 50 points touch (Windows)
Touch tool	Finger, Passive infra-red pen

<b>Power</b>	
Power supply	100-240V~ 50/60Hz
Power consumption (standby)	0.5W
Power consumption (max)	380W
Power consumption - average (watts)	200
Power consumption - Energy Star (watts)	116

<b>Operation System</b>	
System version	Android 13
CPU	Octa-core (A76*4 + A55*4)
GPU	Mali G610 MC4
RAM	8GB
Storage	64GB
OSD / display languages	17 languages: Arabic, Czech, Danish, Dutch, English, French, German, Italian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish

