


OVERVIEW



1. USB-C (Hi-Speed USB), with PD 2.0 & DP 1.2	4. Power button
2. Brightness/Contrast adjust button	5. Kensington Security Slot
3. Main menu button	6. USB-C (Hi-Speed USB), with PD 2.0 & DP 1.2

PERFORMANCE

Panel

Panel

In-Plane Switching (IPS)

Backlight

WLED

Display Size

14 inches

Max View Area

WxH: 301.6 x 188.5 mm

Resolution

2240 x 1400

Aspect Ratio

16:10

Pixel Pitch

0.1346 x 0.1346 mm

Dot / Pixel Per Inch

189 dpi

Brightness

- Panel: 300 cd/m²
- Set: 270 cd/m²

Contrast Ratio

- Dynamic Contrast Ratio: 3000000:1
- Contrast Ratio: 1500:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 6 ms
- Normal Mode: 8 ms

Refresh Rate

60Hz

Color Gamut

- Coverage Ratio: 100% sRGB (CIE 1931)
- Color Area Ratio: 100% sRGB

Color Support

16.7 Million

Color Depth

8-bit

Operating System

Operating System

- Windows® 11 Support
- Windows® 10 Support

Power Supply

Power Consumption

- Typical / Max: 8W / 9.5W
- Sleep / Off mode: <0.3W
- Switch-off Mode: <0.3W
- Energy Star Power On: 6.8W
- Energy Star TEC: 23.6kWh

Voltage Required

DC 5 to 20 V

Special Features

Special Features

- Lenovo® Accessories and Display Manager
Lenovo® Accessories and Display Manager supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- Natural Low Blue Light

DESIGN

Display

Touchscreen

Supports 10-point touch

Mechanical

Bezel Width

- Thickness of Head: 4.6mm (Minimum)
- Side: 6.1mm
- Top / Bottom: 6.1mm / 27.5mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Highest Position	314.8 x 96.4 x 235.3 mm (12.39 x 3.8 x 9.26 inches)
Lowest Position	314.8 x 96.7 x 224.3 mm (12.39 x 3.81 x 8.83 inches)

Packaging Dimensions (WxDxH)

384 x 76 x 277 mm (15.12 x 2.99 x 10.91 inches)

Weight^[2]

0.7 kg (1.5 lbs)

Packaging Weight

1.9 kg (4.2 lbs)

Mounting

Supports VESA mount 100mm, 2 holes

Stand

Supports 0° to +90° tilt, -90° to +90° pivot, 11mm lift

In the Box

- Monitor with Stand
- 1x USB-C® to USB-C® Cable (1m, 5Gbps)
- 2x Clips
- 1x Touch Pen
- 1x L-Shape Dongle
- 1x Protect Bag
- Quick Setup Guide

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Ports^[1]

Left Ports

1x USB-C® (Hi-Speed USB / USB 2.0), with USB PD 2.0 and DisplayPort™ 1.2, up to 65w PD^[2]

Right Ports

1x USB-C® (Hi-Speed USB / USB 2.0), with USB PD 2.0 and DisplayPort™ 1.2, up to 65w PD^[3]

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

[2], [3] Listed as maximum capacity of power delivery. Actual capacity may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™ (2.5 mm x 6 mm)

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- ENERGY STAR® Certified
- EPEAT™ Gold Registered
- EU Energy Label (C-class)
- RoHS (2011/65/EU)
- Volatile Organic Compound Certification

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

Other Certifications

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Low Blue Light
- TÜV Rheinland® Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow

disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

