

2x4 USB Peripheral Sharing Switch - USB 3.2 Gen 1 (5 Gbps), 2 USB-C Hosts, 4 USB-A Hub Ports

MODEL NUMBER: U315-2X4



Allows two computers to share four USB peripherals, including printers, scanners, flash drives and external hard drives.

Features

Share 4 USB Devices Between 2 Computers at the Same Time

Share a USB printer, scanner, keyboard/mouse, flash drive, external hard drive or other USB peripherals between two computers, and save time, money and precious workspace. This USB switch eliminates the cost of buying multiple USB devices for each computer, as well as the headache of determining where to put them and their cables. All four USB-A hub ports support USB 3.2 Gen 1 data transfer rates up to 5 Gbps.

Switching Back and Forth Takes Just a Push of a Button

If you use more than one computer on a daily basis, whether you're working from home on one computer and playing the latest high-tech games on another, you can share peripherals on both. Just push the button on the front of the U315-2X4 to switch seamlessly between the two host computers. The compact switch takes up very little space on your desktop.

Host Cables Are Included

Connect the two USB-C host cables to the USB-C inputs on your computers. If you would rather use the USB-A inputs on one or both computers, each cable includes a built-in USB-A adapter. **Note:** An optional 3.5 mm power cable is also included. It is only necessary when the USB devices connected to the switch require more power than is available from the host's USB hub port.

Highlights

- Switch between as many as 4 USB-A peripherals at the push of a button
- USB-A ports support USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Included DC power cord provides optional extra power for high-power devices
- USB-C host cables with built-in USB-A adapters included for connecting to computers
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

USB-C or USB-A ports on host computers must support USB 3.2 Gen 1 to achieve USB 3.2 Gen 1 speeds up to 5 Gbps

Package Includes

- U315-2X4 USB Peripheral Sharing Switch
- (2) USB-C host cables with USB-A adapters, 3.3 ft. (1 m)
- 3.5 mm DC to USB-A power cable, 5 ft. (1.5 m)
- Installation Instructions

Specifications

OVERVIEW	
UPC Code	037332287441
Device Compatibility	Chromebook; Computer; Laptop
Technology	USB 3.x
Country/Region	Global



Powering Business Worldwide

TRIPP LITE
SERIES

Host Connector	(2) USB C (FEMALE)
DATA	
Data Ports	(4) USB A (FEMALE)
INPUT	
Bus Powered	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
Power Source Type	AC Adapter; USB
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	6
Side A - Connector 1	(2) USB C (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power) - White when switch A/B host
PHYSICAL	
Color	Black
Material of Construction	ABS
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	5.00mm (Host Cable); 4.00mm (Power Cable)
Wire Gauge (AWG)	20 (Power Cable); 24/30/32 (Host Cable)
Total Number of Ports	6
Shipping Dimensions (hwd / in.)	1.50 x 4.40 x 3.74
Shipping Dimensions (hwd / cm)	3.81 x 11.18 x 9.50
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
Unit Dimensions (hwd / in.)	0.770 x 3.690 x 2.130
Unit Packaging Type	Box



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (lbs.)	0.77
Unit Weight (kg)	0.35
ENVIRONMENTAL	
Operating Temperature Range	32° to 131°F (0° to 55°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% (Non-Condensing)
Storage Humidity Range	0% to 95% (Non-Condensing)
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)
Data Transfer Rate	5 Gbps
Ethernet Support	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	No
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.