

CHERRY XTRFY M50

Lightweight gaming mouse



Models may vary from the image shown

M50. GET IN THE GAME.

Elevate your gaming experience with the M50. With quality components in a lightweight construction and a versatile ergonomic shape with smooth curvature for comfort and control, this mouse is a solid choice for gamers of all levels.

UNIQUE ERGONOMIC SHAPE.

The versatile shape of the M50 is carefully designed for a comfortable grip. With its smooth side curvature and button grooves, it enhances control and accuracy for various hand sizes and grip styles.

QUALITY COMPONENTS.

The M50 brings you reliable performance in an affordable package. With a well-proven sensor, high-quality switches and pure PTFE feet, it's built to provide consistent performance for a long time to come.

CHERRY UTILITY SOFTWARE.

The M50 features 5 customizable on-board profiles. Download the CHERRY UTILITY software and adjust everything from CPI and Polling Rate to macros and button assignments. When you're done adjusting your settings, your personalized profiles are stored directly in the mouse's memory, and available at the touch of a button.

HIGHLIGHTS

- Ergonomic shape
- Lightweight construction
- Quality components
- Performance for all-level gamers

PRODUCT SPECIFICATIONS

Weight main product:	4 oz
Dimensions product without packaging:	4,8 in x 2,48 in x 1,54 in
Cable-length:	5.91 ft
Storage temperature:	-13 °F - 149 °F
Working temperature:	32 °F - 104 °F
Max. Current consumption (mA) Mouse:	100 mA
Product approvals:	<ul style="list-style-type: none">• CE• FCC• KCC• EU RoHS• Windows Hardware Compatibility• UKCA• RCM• VCCI• REACH• CP65
System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none">• Windows 7• Windows 10• Windows 11
Scope of delivery:	<ul style="list-style-type: none">• Mouse• Manual
Reliability:	MTBF 8K hours
Switch type:	standard
Number of keys:	5
Thumb buttons:	yes
Max. resolution (dpi):	12.000 dpi
dpi switch:	yes
Illumination:	no

Software support: CHERRY Utility Software & Assistant
Model number: JM-5000
Warranty: 2 years warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.