

## Slim High-Speed HDMI Cable with Ethernet and Digital Video with Audio, UHD 4K 60 Hz (M/M), Black, 10 ft. (3.1 m)

MODEL NUMBER: P569-010-SLIM



HDMI cable with special slim design connects audio/video components to a 4K display in your home theater or digital signage application.

### Features

#### Connects 4K Audio/Video Equipment in Digital Signage and Home Theater Applications

This high-speed HDMI cable securely connects laptops, tablets, PCs, Blu-ray players, game consoles, Roku/Apple TV boxes, satellite/cable TV receivers and other devices with HDMI outputs to HDTVs, HD monitors, projectors or home theater receivers with HDMI inputs. The 4K P569-010-SLIM is backward compatible with all your existing HDMI devices and will transmit 1080p signals.

#### Special Slim Design for Better Airflow and Easier Installation

The P569-010-SLIM is smaller in diameter than standard HDMI cables. This increases airflow in tight spaces, which helps keep your equipment cool and properly functioning. It also cuts down on clutter in crowded racks, home theaters and patch panels, and makes the cable easier to install around corners and through cable management panels.

#### Transmits 4K Video with 4:4:4 Color

The P569-010-SLIM supports Ultra HD 4K resolutions up to 4096 x 2160 at 60 Hz and uncompressed 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

#### Premium Construction for Superior Performance

This rugged HDMI cable features premium foil and braid shielding that ensures reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Corrosion-resistant gold-plated connectors and contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference. Integral strain relief gives the cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

### Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for heightened video quality
- Special slim design cuts cable clutter and makes it easy to route through tight spaces
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Plug-and-play operation with no software required for easy, immediate installation

### Package Includes

P569-010-SLIM Slim High-Speed HDMI Cable, M/M, Black, 10 ft. (3.1 m)

## Specifications

### OVERVIEW

UPC Code

037332290458



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                |                       |
|--------------------------------|-----------------------|
| Product Type                   | Passive Cable         |
| Technology                     | HDMI                  |
| Cable Type                     | Passive               |
| <b>VIDEO</b>                   |                       |
| Max Supported Video Resolution | 4K 60HZ (4096 X 2160) |
| Max Supported Color Depth      | 24-bit True Color     |
| HDR Support                    | No                    |
| 3D Video Supported             | No                    |
| Chroma Sub Sampling            | 4:4:4                 |
| EDID Support                   | Yes                   |
| Signal Transmission            | Bidirectional         |
| DisplayPort Alt Mode           | No                    |
| <b>AUDIO</b>                   |                       |
| Audio Specification            | Stereo Audio          |
| <b>CONNECTIONS</b>             |                       |
| Side A - Connector 1           | HDMI (MALE)           |
| Side B - Connector 1           | HDMI (MALE)           |
| Connector Plating              | Gold                  |
| Contact Plating                | Gold                  |
| Connector Style                | Straight              |
| Latching or Gripping Connector | No                    |
| <b>PHYSICAL</b>                |                       |
| Color                          | Black                 |
| Material of Construction       | PVC                   |
| Cable Jacket Color             | Black                 |
| Connector Color                | Black                 |
| Cable Jacket Material          | PVC                   |
| Cable Jacket Rating            | VW-1                  |
| Cable Outer Diameter (OD)      | 3.6MM                 |
| Wire Gauge (AWG)               | 36                    |
| Cable Length (ft.)             | 6                     |
| Cable Length (m)               | 1.83                  |
| Cable Length (in.)             | 72                    |



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |                               |
|--|-------------------------------|
| Minimum Bend Radius                          | 36mm                          |
| Shipping Dimensions (hwd / in.)              | 9.00 x 7.00 x 0.50            |
| Shipping Weight (kg)                         | 0.05                          |
| Unit Dimensions (hwd / in.)                  | 9.000 x 7.000 x 0.500         |
| <b>ENVIRONMENTAL</b>                         |                               |
| Operating Temperature Range                  | 32° to 133°F (0° to 45°C)     |
| Storage Temperature Range                    | -40° to 176°F (-40° to 80°C)  |
| Operating Humidity Range                     | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range                       | 5% to 90% RH, Non-Condensing  |
| <b>COMMUNICATIONS</b>                        |                               |
| EDID Compatible                              | Yes                           |
| Consumer Electronics Control (CEC) Supported | No                            |
| <b>FEATURES &amp; SPECIFICATIONS</b>         |                               |
| EMI/RFI Line Noise Protection                | No                            |
| Integrated/Removable Cable                   | No                            |
| MST Support                                  | No                            |
| Antibacterial                                | No                            |
| Fully Molded Connector Ends                  | No                            |
| Ohms   | No                            |
| Integral Strain Relief                       | No                            |
| Impedance-Matched Twisted-Pair Construction  | No                            |
| Scaler Function                              | No                            |
| IP67 Rated                                   | No                            |
| Armored Cable                                | No                            |
| HDCP Specification                           | 1.4                           |
| Driver Required                              | No                            |
| DIN Mountable                                | No                            |
| <b>STANDARDS &amp; COMPLIANCE</b>            |                               |
| Product Compliance                           | CE (Europe); RoHS; UKCA       |
| <b>WARRANTY &amp; SUPPORT</b>                |                               |
| Product Warranty Period (Worldwide)          | Lifetime limited warranty     |



*Powering Business Worldwide*

**TRIPP LITE**  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.