

Product Specifications

HAT3300-2T

Synology

Hardware Specifications

General	
Capacity	2 TB
Form Factor	3.5"
Interface	SATA 6 Gb/s

Performance	
Rotational Speed	5,400 rpm
Maximum Sustained Data Transfer Speed (Typ.)	180 MB/s

Reliability	
Warranty	3 Years
Notes	The warranty period starts from the purchase date as stated on your purchase receipt. (Learn more)

Power Consumption	
Active Idle (Typ.)	2.8 W
Random Read / Write (4KB Q1) (Typ.)	3.1 W
Notes	Power consumption may differ according to configurations and platforms.

Temperature

Operating

0°C to 65°C (32°F to 149°F)

Non-operating

-40°C to 70°C (-40°F to 158°F)

Compatibility

Applied Models

- [HAT3300-2T](#)
- [HAT3300-4T](#)
- [HAT3300-6T](#)
- [HAT3320-8T](#)
- [HAT3310-12T](#)
- [HAT3310-16T](#)