



Poly Studio R30 USB Video Bar No Radio GSA/TAA JITC (980F2AA)

Overview

Simply better meetings

Transform your collaboration with advanced video capabilities and superb audio quality that are simple for anyone on your team to use. The result is meetings that start on time, increase inclusivity, and improve communication and productivity.



Smooth meetings

The Poly Studio R30 Plus solution includes a dynamic video bar, easy-connect dock, and remote control to simplify meetings. Anyone can connect their compatible laptop to the video system which makes it easy for everyone in the room to participate [1].

Reduce wasted time

Eliminate technology headaches with one USB Type-C® cable that easily connects a laptop to the in-room devices and powers your computer. Keep things moving with a remote that lets anyone easily control mute and volume and adjust the camera.

Boardroom-quality conferencing

Bring stunning video quality and audio excellence to meetings in your smaller rooms. Intelligent camera framing, a wide 120-degree field of view, exceptional voice clarity, and smart noise reduction make collaboration productive [2].

Features

Never miss a moment

Poly DirectorAI smart camera framing works behind the scenes to keep you framed how you want- whether that's switching between people speaking, following a presenter, or a close up view of everyone in the room. Keep everyone engaged and involved.

Quick and effortless setup

Swiftly set up your Poly Studio R30: just two cords are needed. Plug in the power and connect your PC via USB and you are ready to go. Remember you may want to connect your PC to the monitor, which would require a separate HDMI cable.

Bring everyone together

Gather the team without feeling cramped. The impressive 120-degree field of view allows everyone to be seen. This wide angle eliminates the need for camera adjustments or awkward seating arrangements, making it perfect for small meeting spaces.

Impeccable noise reduction

Poly NoiseBlock AI and Acoustic Fence Technologies reduce background noise and provide an interference-free audio experience. Minimize distractions, such as keyboard typing, or nearby conversations so you can focus on collaboration.

Clear resolution

Say goodbye to grainy, blurry videos that make it hard to focus and connect. Our stunning 4K resolution, provides you with lifelike visuals that capture every expression, gesture, and nuance for a truly engaging meeting experience.

Rich voice clarity

The powerful integrated speaker delivers rich, crystal-clear audio, enabling participants to hear every word with clarity. The advanced speaker ensures that even the softest-spoken voice is amplified, making meetings more productive.

[1] The Poly Studio R30+ video conferencing solution includes: Poly Studio R30, HP USB-C Dock G5 and Poly Studio Bluetooth® remote control. Compatible laptop operating systems include Windows 10 and higher.; macOS; Chrome OS™.

[2] For optimal performance we recommend using the Poly Studio R30 Plus in a small room approximately 10' x15'/3.05m x 4.57m.

Specifications

Audio	Poly NoiseBlockAI technology; Poly Acoustic Fence technology; Poly Acoustic Clarity technology
Minimum dimensions (W x D x H)	445 x 86 x 81 mm (with monitor clamp); 445 x 68 x 81 mm (without monitor clamp)
Minimum dimensions (W x D x H)	17.5 x 3.4 x 3.2 in (with monitor clamp); 17.5 x 2.7 x 3.2 in (without monitor clamp)
Weight	822 g (with monitor clamp); 737 g (without monitor clamp)
Weight	1 lb (with monitor clamp); 1 lb (without monitor clamp)
Ports	1 USB Type-C® 5Gbps signaling rate; 2 USB 2.0 Type-A; 1 4.5 mm power adapter
Package dimensions (W x D x H)	225 x 525 x 100 mm
Package weight	300 g
Power supply type	External
UPC number	197961119220
Manufacturer Warranty	Poly standard one-year limited warranty
What's in the box	Poly Studio R30; Monitor clamp; AC power adapter; Power cable; USB Type-C® to USB Type-A cable (5 m/16.4 ft); Setup sheet; Removable privacy cap

Additional specifications

Audio standards	UAC Plug and Play compatible
Camera features	Manual pan, tilt and zoom control; Automatic meeting experience powered by Poly DirectorAI including speaker framing, presenter tracking, and conversation mode
Camera resolution	2160p, 4K UHD (3840 x 2160); 1080p, FHD (1920 x 1080); 720p, HD (1280 x 720)
Camera type	Single-lens
Cartons per layer	4
Cartons per pallet	28
Certified collaboration software	Microsoft Teams; Zoom; Google Meet
Color	Sand
Compatible Operating Systems	Windows 10; Windows 11; macOS 10.10 or later; Windows 8.1
Country of origin	Made in Taiwan
Diagonal field of view (dFoV)	120°
Horizontal field of view (hFoV)	110°
Interoperability	Zoom Certified; Google Meet; All cloud service providers through Poly Video App mode; USB Device mode
Lens cover capabilities	Integrated
Management Software	Poly Lens
Microphone pickup range (imperial)	Up to 15 ft
Microphone pickup range (metric)	Up to 4.57 m
Microphone type	Three-microphone element beamforming array
Multiple order quantity	1
Non-Operating Humidity Range	5 to 95%
Operating altitude	10,000 ft
Operating altitude	3,000 m
Operating humidity range	15 to 80%
Operating temperature range	32 to 104 °F
Operating temperature range	0 to 40 °C
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Pallet (layers)	7
Pallet dimensions	39.37 x 47.24 x 79.72 in
Pallet dimensions (W x D x H)	100 x 120 x 202.5 cm

Pallet weight	787.05 lb
Pallet weight	357 kg
Physical security	Standard Kensington lock slot
Power	12V/3A
Products per pallet	112
Products per pallet layer	16
Sensitivity (speaker)	90 dB SPL @ 1000 Hz @ 0.5 m at maximum volume
Speaker bandwidth	100 Hz to 20 kHz
Speaker type	Single speaker
UNSPSC code	45121520
Video standards	UVC Plug and Play compatible
Wireless technologies	Bluetooth® 4.2; WiFi 802.11a/b/g/n/ac (SISO)
Zoom capability	5x (without tracking); 4x (with auto tracking)

Hybrid Work Solutions

Video

★ : Recommended

Video Accessories

Poly Studio E70/P15/R30 Display Clamp	875K8AA
Poly Studio P15/R30 VESA Mount	875L1AA
Poly Studio P15/R30 Wall Mount	783S4AA
Poly Studio R30/USB Bluetooth Remote Control	875L4AA
Poly USB 2.0 Cable (5M)	875H6AA
Poly Video IEC Power Cord	874T5AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 20, 2024 2:55 PM UTC+0000