



K3



HIGH SPEED RETAIL PRINTER

K3 is a high performance thermal printer designed to adapt to any environment.

With its 350mm/s (max) speed it is ideal for printing receipts, coupons, kitchen orders, invoices and tickets. Elegant in design, the K3 features a large roll capacity, anti-jamming technology, and illuminated touch capacitive FEED and COVER OPEN buttons.

FEATURES

- **Resolution:** 203 dpi (8 dot/mm)
- **Printing:** max 350 mm/s
- **Paper width:** 58 mm / 60 mm / 80 mm
- **Paper weight:** from 55 to 90 gr/m²
- **Roll Dimension:** max Ø 100 mm
- **Flash Memory:** Flash SPI 4 MB + 1 MB internal
- **RAM Memory:** 64 MB
- **Data Buffer:** 16 kB
- **Supported Barcode:** UPCA, UPCE, EAN13, EAN8, CODE39, ITF, CODABAR, CODE93, CODE128, CODE32, QRCODE, DATAMATRIX, PDF417, AZTEC
- **Power supply:** 24 Vdc
- **Head Life:** 200 Km
- **Cutter:** 1 million cuts, total or partial
- **Operating temperature:** 0°C + 50°C
- **Dimensions:** 206 mm (W) × 148 mm (D) × 140 mm (H)
- **Weight:** 1.98 Kg



INTERFACES

- **RS232**
- **CASH DRAWER PORT**
- **USB**
- **ETHERNET**
- **Wi-Fi®** (optional)

SENSORS

- **Head temperature**
- **Paper presence**
- **Detection of black mark**
- **Cover open**
- **Low paper**

DRIVERS

- **Windows XP**
- **VISTA** (32/64 bit)
- **Windows 7** (32/64 bit)
- **Windows 8** (32/64 bit)
- **Windows 8.1** (32/64 bit)
- **Windows 10** (32/64 bit)
- **Linux**
- **OPOS**
- **JavaPOS**
- **Android**
- **iOS**

SOFTWARE TOOLS

- **PrinterSet**
- **Virtual COM**

TECHNICAL DETAILS





AVAILABLE MODELS

P/N

911HM010800733

911HM010300B33

DESCRIPTION

PRINTER K3 HIGH SPEED ETH USB RS232

PRINTER K3 HIGH SPEED ETH USB RS232 WIFI