


## USB-C Multiport Adapter - 4K 60 Hz HDMI, USB 3.2 Gen 2 Hub Ports, 100W PD Charging, HDR, HDCP 2.2

MODEL NUMBER: U444-06N-H4U3CS



Adds 4K HDMI, 10G USB-A hub ports and USB-C PD charging to the USB-C or Thunderbolt 3 port on your MacBook or laptop.

### Features

#### USB-C Adapter Turns Your USB-C or Thunderbolt 3 Device into a Multiport Workstation

This versatile 4K adapter adds multiple ports to the USB-C or Thunderbolt 3 port on your MacBook Pro or Windows laptop. The U444-06N-H4U3CS allows you to transmit digital audio and 4K video to a large display, add a thumb drive or other USB peripheral, and power and charge a PD Charging-compliant mobile device. It's an ideal adapter for personal or business workspaces that frequently connect to thumb drives and other external data storage.

#### Supports USB-C DisplayPort Alternate Mode for Converting Audio/Video Signals

By connecting the built-in USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to an HDMI monitor, television or projector without installing special software drivers.

#### Transmits Crystal-Clear 4K Video with HDR and 4:4:4 Color

The U444-06N-H4U3CS supports Ultra HD video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz when connected to a host computer that supports DisplayPort Alt Mode 1.4 and DSC. It supports HDR (High Dynamic Range), providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.3 encryption allows you to stream 4K content with no complications. This adapter also supports uncompressed 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

#### Connects USB Peripherals and Transfers Data at Fast USB 3.2 Gen 2 Speeds

Three high-end USB-A ports accept USB peripherals, such as a flash drive, mouse or keyboard, and provide up to 5V 1.5A (7.5W) for charging and powering mobile devices. The USB 3.2 Gen 2 ports transfer data at speeds up to 10 Gbps for quickly transferring large files between the host and external storage drives. The ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

#### PD 3.0 Charging Port Charges High-Powered Devices via AC Wall Charger

The dedicated USB-C Power Delivery port provides power output up to 20V 5A (100W), which is more than sufficient for charging and powering most newer laptops. Connect the charging port to the device's AC wall charger with a user-supplied USB-C cable rated to 100W charging.

### Highlights

Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for heightened video quality  
Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy  
Converts audio/video signals from sources supporting USB-C DisplayPort Alt Mode  
Power Delivery port provides 20V 5A (100W) output for charging connected host device  
USB 3.2 Gen 2 data ports transmit to external drives and connect peripherals at 10 Gbps

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode (DisplayPort 1.4 and DSC required for 4K @ 60 Hz resolutions)
- Display device with HDMI input

### Package Includes

- U444-06N-H4U3CS USB-C Multiport Adapter
- Installation Instructions



Powering Business Worldwide

TRIPP LITE  
SERIES

**Ready to Use Right from the Package, So You Can Plug and Play Immediately**

The plug-and-play adapter is specifically designed for the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or external power. This adapter is backward compatible with 1080p displays, allowing you to use it with older equipment. Slightly smaller and thinner than most smartphones, the U444-06N-H4U3CS fits into a pocket, purse or laptop bag for convenient connections on the go.

## Specifications

OVERVIEW	
UPC Code	037332287472
Product Type	USB-C Multiport Adapter
Device Compatibility	Amazon Kindle; Chromebook; Computer; Laptop; Monitor/HDTV; Phone; Printer; Projector; Tablet; Video Game System
Technology	HDMI; USB 3.x
Country/Region	Global
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	HDMI (FEMALE)
Video Ports Details	DisplayPort 1.4; HDCP 2.3
Resolutions Supported	3840 x 2160 (4K x 2K) @ 60 Hz when connected to a host that supports DP 1.4 Alt Mode & DSC
Supported Resolutions	3840x2160 (4K)
Max Supported Video Resolution	3840 x 2160 (4K x 2K) @ 60 Hz
Recommended Cabling	User-supplied HDMI cabling that supports at least 4K @ 60 Hz
Extended Mode	Yes
Extended Mode Details	Capable of extending a desktop to a connected HDMI display at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz when using compatible HDMI cabling and connecting from a host that supports DP 1.4 Alt Mode and DSC
Mirror Mode	Yes
Mirror Mode Details	Capable of mirroring video content to a connected HDMI display at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz when using compatible HDMI cabling and connecting from a host that supports DP 1.4 Alt Mode and DSC
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4
EDID Support	Yes
DisplayPort Alt Mode	Yes



Powering Business Worldwide

TRIPP LITE  
SERIES

DSC Support	Yes
<b>DATA</b>	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 2 (10 Gbps)
<b>INPUT</b>	
Built-In Cable Length (in.)	6.69
Built-In Cable Length (cm)	17.0
Bus Powered	Yes
<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	Yes
<b>POWER</b>	
Power Source Type	Bus
Power Consumption (Watts)	100.00
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
<b>CONNECTIONS</b>	
Number of Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	(3) USB A (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Connector Plating	Nickel
Connector Style	Straight
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Connected (White); Transferring Data (Orange)
<b>CHARGING</b>	
Number of Charging Ports	2
Total Charging Amps	5A
Total Charging Watts	100
Charging Port Type	(1) USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports	(2) USB-A: 0.9A; (1) USB-A: 5V 1.5A (7.5W); (1) USB-C: 100W (20V 5A) Power Delivery (PD 3.0)

Charging Ports Details	Dedicated USB-C PD 3.0 charging port provides up to 20V 5A (100W) of charging power to the host USB-A fast charging port provides 5V 1.5A (7.5W) of charging power to a smartphone or other low wattage device 3x USB-A data ports share a combined 12W (5V 2.4A) when charging or powering devices simultaneously
Charging Ports / Amps	1.5A; 5A
Charging Amps per Port	1.5A; 5A
<b>PHYSICAL</b>	
Color	Black; Gray
Material of Construction	Polycarbonate, ABS
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Outer Diameter (OD)	4.3 mm
Wire Gauge (AWG)	34/24
Cable Length (ft.)	0.557
Cable Length (m)	0.17
Cable Length (in.)	6.67
Cable Length (cm)	17
Total Number of Ports	5
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Dimensions (hwd / cm)	2.31 x 14.00 x 10.01
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
Unit Dimensions (hwd / in.)	0.550 x 1.340 x 3.750
Unit Dimensions (hwd / cm)	1.4 x 11.5 x 5.0
Unit Packaging Type	Box
Unit Weight (lbs.)	0.287
Unit Weight (kg)	0.13
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70)
Operating Humidity Range	10 to 85% RH (No Condensation)
Storage Humidity Range	5% to 90 % RH (No Condensation)
Power Provided to Connected Device(s)	100W
<b>FEATURES &amp; SPECIFICATIONS</b>	
Quick Charge Compliant	No



Powering Business Worldwide

TRIPP LITE  
SERIES

USB Hub Ports	Yes
Number of USB Hub Ports	2
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
Data Transfer Rate	10 Gbps
Ethernet Support	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
HDCP Specification	2.3
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
TAA Compliant Option	No
Product Certifications	EN 55032; EN 55035
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.