



# VG2758-2K - 27" 1440P IPS ERGONOMIC DOCKING MONITOR | 100W USB-C, RJ45, DAISY CHAIN


## Key Features



27  
DISPLAY



IPS  
PANEL



2560 x 1440p  
RESOLUTION

## Product Description

Elevate your workspace with ViewSonic's VG2758-2K docking monitor, designed for seamless connectivity, engineered to streamline your setup with daisy chaining via USB-C. Say goodbye to costly docking stations and cable clutter —our sleek, docking monitor allows you to connect multiple screens with a single cable, delivering high resolution stunning visuals while charging your devices simultaneously. Future-ready and versatile, the VG2758-2K offers a range of connectivity including USB-C with 100W of power delivery, HDMI, DisplayPort, and a 5-port USB hub with a mix of USB-A and USB-C ports to connect peripherals. With full ergonomic adjustability, VG2758-2K will enhance productivity and comfort, making it the ultimate upgrade for any modern workspace.

## Specifications

More Information	
UPC	766907027952
Screen Size	27
Viewable Area (in.)	27
Panel Type	IPS
Display Resolution	2560 x 1440
Display Resolution	QHD (2560x1440)
Static Contrast Ratio	1,500:1
Dynamic Contrast Ratio	80,000,000:1
Light Source	LED
Brightness	350 cd/m2
Colors	16.7M
Color Space Support	8 bit true
Aspect Ratio	16:9


<b>Response Time (Typical GTG)</b>	5ms
<b>Viewing Angles</b>	178° horizontal, 178° vertical
<b>Backlight Life (Hours)</b>	30,000
<b>Panel Surface</b>	Anti-Glare type, Hard-coating (3H), Haze 25%
<b>Refresh Rate</b>	100Hz
<b>PC Resolution (max)</b>	2560 x 1440p
<b>Mac® Resolution (max)</b>	2560 x 1440p
<b>USB Type A</b>	3
<b>USB Type C</b>	1x 100W, 2x 15W
<b>3.5mm Audio Out</b>	1
<b>Ethernet LAN (RJ45)</b>	1
<b>HDMI 1.4 In</b>	1
<b>DisplayPort</b>	1
<b>Internal Speakers</b>	2W (x2)
<b>Eco Mode (Conserve)</b>	138
<b>Eco Mode (optimized)</b>	143
<b>Consumption (typical)</b>	149
<b>Consumption (max)</b>	242
<b>Voltage</b>	100-240 VAC, 50-60Hz
<b>Stand-by</b>	0.5
<b>Power Supply</b>	Internal
<b>Cable Organization</b>	Yes
<b>Kensington Lock Slot</b>	1
<b>Physical Controls</b>	Joystick key: Up, Right, Down, Left, Center; Power
<b>On Screen Display</b>	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu
<b>Temperature</b>	32-104° F (0 - 40° C)
<b>Humidity (non-condensing)</b>	20-90%
<b>VESA Compatible</b>	100 x 100 mm
<b>Frequency Horizontal</b>	30 ~ 151 KHz
<b>Frequency Vertical</b>	50 ~ 100 Hz
<b>Height Adjust</b>	150 mm / 5.9 in
<b>Swivel</b>	90°
<b>Pivot (Right/Left)</b>	90° / 90°
<b>Tilt (Forward/Back)</b>	5° / 30°
<b>Regulations</b>	cTUVus, FCC-B, ICES003, Energy Star, EPEAT, CEC
<b>Net (lbs)</b>	16.4

<b>Net Without Stand (lbs)</b>	11
<b>Gross (lbs)</b>	22.4
<b>Net (kg)</b>	7.4
<b>Net Without Stand (kg)</b>	5
<b>Gross (kg)</b>	10.2
<b>Packaging (in.)</b>	27.6W x 16.7H x 6.5D
<b>Physical (in.)</b>	24.12 W x 15.84 ~ 20.69H x 8.6D
<b>Physical Without Stand (in.)</b>	24.12 W x 14.16H x 1.76D
<b>Packaging (mm)</b>	702W x 425H x 166D
<b>Physical (mm)</b>	612.6W x 402.32~525.64H x 218.47D
<b>Physical Without Stand (mm)</b>	612.6 W x 359.77H x 44.75D
<b>Package Contents</b>	LCD Display, Power Cable, DisplayPort Cable, USB Type-C Cable (with USB Type A adaptor), Quick Start Guide
<b>Recycle/Disposal</b>	Please dispose of in accordance with local, state or federal laws.
<b>Warranty</b>	Three-year limited warranty on parts, labor and backlight

UPC: 766907027952

## Contact Sales

[ViewSonic.com](http://ViewSonic.com)

888.881.8781 

email: [salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com) 