




VKP60

60mm Ultra-Compact Receipt/Ticket Kiosk Printer

VKP60 is the kiosk printer for **receipts and tickets**, capable of adapting to a wide range of settings thanks to its **multiple configurations**. Compact, versatile, and packed with features such as **anti-jam**, **total** and **partial cut**, this device fits any type of kiosk with its roll holder adjustable in two positions. The product boasts self-installing Windows®, Linux, OPOS, Java POS, and Status Monitor SDK **drivers** and it supports PrinterSet, CPT, Windows® API, Driver Manager, Android™ API, and iOS API **software tools**. VKP60 is available in two different configurations: compact and paper mouth.




ACCESSORIES

- Roll holder bracket VKP60 with NPE
- VKP60 adapter to 12Vdc
- VKP60 compatible TG2460 fixing kit
- Dongle ETH VKP60
- Dongle RS232 VKP60

TECHNICAL SHEET

	VKP60 - Compact	VKP60 - Paper Mouth	VKP60 - Presenter
Resolution	203 dpi		
Power supply	24V, 12V adapter (optional)		
Printing speed	up to 200 mm/s @24V		
Paper thickness	50 - 130 μm		50 - 100 μm
Roll diameter	max. 100 mm (with CUSTOM roll holder)		
Paper width	44, 50, 54, 58, 60 mm		
Cutter	Total and partial cut		
Interfaces	USB 2.0, Virtual Com, RS232 or ETH (optional)		
Sensors	Paper present, cover open, printhead temperature, cutter home, black mark, anti-jam, optional: near paper end	Paper present, cover open, printhead temperature, cutter home, black mark, paper in output, optional: near paper end	
Character set	PC437, PC850, PC858, PC860, PC862, PC863, PC864, PC865, PC866, Katakana, WPC1250, WPC1251, WPC1252, WPC1253, WPC1254, WPC1255, WPC1256, WPC1257, WPC1258, Chinese GB18030, Korean PC949		
Supported barcodes	UPC-A - UPC-E - EAN13 - EAN8 - CODE39 - ITF - CODABAR - CODE93 - CODE128 - CODE32 Codice QR - Aztec - PDF417 - Datamatrix - GS1 Databar		
Print head life	200 km / 100M pulses		
Cutter life	1M		
LED paper mouth	No	Default	
Drivers	Windows® (32/64 bit), CUPS Linux (32/64 bit), OPOS, Java POS, Status Monitor SDK		
SW tools	PrinterSet, CPT, Windows® API, Driver Manager, Android™ API, iOS API		
Operative temperature	-20 to +70°C ; 10 to 90% RH (no condensation)		
Dimensions	59.5 mm (L) x 86 mm (W) x 86.5 mm (H)	71.5 mm (L) x 86 mm (W) x 89.5 mm (H)	99 mm (L) x 109.8 mm (W) x 87.3 mm (H)
Weight	330 g	340 g	490 g

MODELS



915NA010100300
PRINTER VKP60 USB RS232
COMPACT



915NA020100300
PRINTER VKP60 USB RS232
PAPER MOUTH



915NA030100300
PRINTER VKP60 USB RS232
PRESENTER

Via Berettine, 2 - 43010 Fontevivo PR - VAT: IT02498250345 - TEL: +39 0521 680111 - FAX: +39 0521 610701 - UNIQUE CODE: 8RQN7AZ

The technical data on this website are not binding and may be changed without advanced notice.
Last update: 30 December 2025