



User Manual

Premium High Speed HDMI Cable
with Ethernet M/M- 4K 60Hz 3840x2160

Y10C891-B1

Congratulations

Thank you for purchasing this premium Rocstor product. For optimum performance and safety, please read these instructions carefully before connecting, operating or using this product. Please keep this manual for future reference.

Introduction

Elevate your multimedia experience with the Rocstor Premium 15-ft (4.6m) 4K High-Speed HDMI® 2.0 Cable, engineered to deliver stunning high-definition performance for all your HDMI-compatible devices. Supporting ultra-high resolutions up to 4096x2160 (4K UHD) at 60Hz and an impressive bandwidth of 18Gbps, this cable ensures vibrant visuals with HDR10, rich colors, and crystal-clear audio for an immersive experience. Designed for seamless connectivity, it works effortlessly with HDTVs, gaming consoles, Blu-ray players, and professional AV setups while maintaining backward compatibility with older HDMI standards. Whether for gaming, home theaters, or professional environments, this durable cable with gold-plated connectors and a robust TPE jacket is built to withstand frequent use, delivering reliable performance backed by Rocstor's Lifetime Warranty.

Package Contents

Before attempting to use this unit, please check the packaging and make sure the following items are contained in the packaging:

- Main Unit x1
- User Manual

Features

Upstream:

HDMI Male X1

- Compatible with 4K high definition as well as 1080p resolution devices
- Supports 18Gbps bandwidth and provides high speed performance
- Supports 4K UHD resolution up to 4096x2160p (3840x2160) and HDR
- Gold plated connector



Downstream:


HDMI Male X1

- Compatible with 4K high definition as well as 1080p resolution devices
- Supports 18Gbps bandwidth and provides high speed performance
- Supports 4K UHD resolution up to 4096x2160p (3840x2160) and HDR
- Gold plated connector



Specification

Input / Output Connector	
Input	HDMI Male x1
Output	HDMI Male x1
Mechanical	
Size	15ft (4.6m)
Operating Temperature	0°C to 45°C (32°F to 113°F)
Operating Humidity	10% to 90% RH (no condensation)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Storage Humidity	10% to 90 % RH (no condensation)
American Wire Gauge	28 AWG
Supported Resolution	3840 x 2160
Color	Black
Warranty	
Limited Warranty	Lifetime
Devices Supported	
Audio/Video Devices	Cable Box Computers Monitors HDTV Home Theater System Game Consoles
Regulatory Approvals	
Environmental Certifications	RoHS; WEEE



Support

Technical support is available to all the registered users of Rocstor products.

Technical Support / RMA

Hours: 9:00 am - 5:00 pm PST

Monday to Friday (except holidays)

Tell: +1 (818) 727-7000 (National and international)

Fax: +1 (818) 875-0002

Email: support@rocstor.com

⚠ Safety Information:

WARNING:

Please follow these safety instructions. Failure to do so may result damages or injury. It is normal that the device becomes very warm during use.

Please note that:

Continuous contact with warm surfaces for extended time may cause discomfort or injury. In order to reduce the possibility of overheating or heat-related injuries, always allow needed ventilation around the device and use care when handling it. Avoid instances where your skin is in extended contact with the device when plugged into the host computer. It is not recommended to sleep with the device when plugged into a host computer. Avoid placing the device under a pillow, blanket, or your body when connected to a host computer. If you have a medical condition that affects your ability to detect heat against the body, extra care should be used. Never use the device in locations with water, such as a sink, bathtub, or shower stall. Never connect or disconnect the device with wet hands.



Warranty Information

Warranty Information

This product is backed by limited lifetime warranty. Rocstor warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. Rocstor does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of Rocstor, Inc. and Rocstor (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

©2024 Rocstor, Inc. All rights reserved. Rocstor is registered trademark of Rocstor, Inc. Apple®, the Apple logo, Mac®, MacBook®, MacBook Pro®, MacBook Air®, iPad®, iPad Air®, iPad mini®, iPad Air®, iPhone®, MacOS® are registered trademarks of Apple, Inc. Google® and Chromebook™ are registered trademarks of Google, LLC. Microsoft® is registered trademarks of Microsoft corporation. All other product names and logos mentioned herein may be trademarks of their respective companies. Thunderbolt is a trademark of Intel Corporation or its subsidiaries. USB Type-C® and USB-C® are registered trademark of USB Implementers Forum. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc. Feature and specification are subject to change without notice. All trademarks and registered trademarks are the property of their respective. All rights reserved.

