



EloPOS™ System 15-inch (4:3)

All-in-One Touchscreen Computer



Connectivity-Rich



Retail-Hardened



3-year warranty

Product Overview

The versatile EloPOS System combines modern aesthetics, modular flexibility and commercial-grade reliability. Purpose-built for point of sale, EloPOS offers a 15-inch touchscreen display, choice of Intel 9th generation processors and an integrated expansion hub to connect the peripherals you need - whether a customer facing display, payment reader, printer, cash drawer, barcode scanner or scale. From traditional POS to self-service applications, EloPOS delivers the durability needed to survive continuous public use and is backed by Elo's standard 3-year warranty.

EloPOS utilizes the reliability-tested performance and security of Intel's 9th Generation processors, integrated Trusted Platform Modules, Intel vPro and the Windows 10 operating system. For added flexibility, EloPOS offers models with no OS - all pretested with Linux SuSE, Ubuntu and Red Hat operating systems, providing businesses the best solution for their environment.

Optional accessories include MSR, barcode scanner, fingerprint reader, EMVs and customer facing displays.

USB Type-C interface that provides touch, video and power connectivity

Optional EloCareSM - Advance Unit Replacement service available - If you have an issue with your EloPOS System, just call Elo to have a replacement unit sent.*

EloPOS System 15-inch 4:3 Model

Specifications	Celeron	i3	i5
Processor	Intel® Celeron® Processor J4125 (4M Cache, up to 2.7 GHz) or G4900T (2M Cache, up to 2.9 GHz)	Intel Core i3-9100TE Processor (6M Smart Cache, up to 3.20 GHz by Intel Turbo Boost Technology 2.0)	Intel Core i5-9500TE Processor (9M Smart Cache, up to 3.60 GHz by Intel Turbo Boost Technology 2.0) Intel vPro™ Support
TPM	TPM 2.0		
Active Management Technology	N/A		Intel AMT 11.0 Support
Chipset	N/A or Intel H310 Express	Intel H310 Express	
Video	Intel UHD Graphics 600 or 610		Intel Q370 Express
BIOS	AMI		
Memory (RAM)	4GB 2666MHz DDR4 SO-DIMM on 1 of 2 slots (expandable to 8GB)	4GB 2666MHz DDR4 SO-DIMM on 1 of 2 slots (expandable to 32GB)	8GB 2666MHz DDR4 SO-DIMM on 1 of 2 slots (expandable to 32GB)
Storage	128GB M.2 SATA SSD, 80 TBW; 256GB M.2 SATA SSD, 160 TBW; Optional - M.2 PCIe (NVMe) SSD for selected SKUs		
Operating System Options	No OS; Microsoft Windows 10 IoT Enterprise LTSC 64-bit; Optional - Windows 10 Professional English 64-bit		
Languages	Windows 10 - 36 Language groups		
I/O Ports	3 x USB 3.0 (1 on display head, 2 on I/O); 2 x USB 2.0 (on I/O); 4 x Micro USB 2.0 (on display head); 1 x Powered USB 24V (on I/O); 2 x Powered USB 12V (on I/O); 2 x RJ45; 12V/24V Cash Drawer Port on I/O (EPSON Pinout, 24V default; selectable by internal switch); 1 x LAN RJ45 (Gigabit)		
Wireless Connectivity	802.11 a/b/g/n/ac 2.4GHz and 5GHz; Bluetooth 5.0		
Additional Video Out	1 x Full-function USB-C (Power up to 27W, USB 3.0, Display Port)		
Audio	2 x 2W internal speakers; 1 x 3.5 mm headset jack		
Display	15.0" / 381 mm diagonal, active matrix TFT LED LCD		
Surface Treatment	Anti-glare		
Aspect Ratio	4:3 (standard)		
Active Display Area (W x H)	11.97" x 8.98" / 304.1 mm x 228.1 mm		
Native (optimal) Resolution	1024 x 768 @ 60Hz		
Number of Colors	262,144		
Brightness (typical)	LCD panel: 400 nits; TouchPro PCAP: 340 nits		
Response Time Total (typical)	23 msec		
Viewing Angle (typical)	Horizontal: 80°/80° or 160° total / Vertical: 80°/80° or 160° total		
Contrast Ratio (typical)	800:1		
Touch Technologies	TouchPro® PCAP with up to 10 touches		
Power	External 24VDC universal-type power supply brick; AC input voltage: 100-240 VAC; Input frequency: 50-60 Hz; Maximum output power: 180W		
Max Power Consumption	i2 Model: 30W; i3 Model: 63W; i5 Model: 78W; SLEEP: < 5W; OFF: BIOS EUP disabled (default) < 4W, BIOS EUP enabled < 0.5W		
Dimensions	With Stand: 14.16" x 15.37" x 8.71" / 359.7 mm x 390.4 mm x 221.3 mm; Without Stand: 14.16" x 11.17" x 3.07" / 359.7 mm x 283.7 mm x 78.1 mm		
Shipping Dimensions	With Stand: 17.91" x 14.65" x 20.04" / 455 mm x 372 mm x 509 mm; Without Stand: 18.19" x 8.50" x 14.80" / 462 mm x 216 mm x 376 mm		
Weight	With Stand: 11.6 lbs / 5.3 kg; Without Stand: 7.61 lbs / 3.45 kg		
Shipping Weight	With Stand: 18.1 lbs / 8.2 kg; Without Stand: 11.02 lbs / 5 kg		
Temperature	Operating: 0°C to 35°C (32°F to 95°F); Storage: -20°C to 60°C (-4°F to 140°F)		
Humidity (non-condensing)	Operating: 20% to 80%; Storage: 5% to 95% (38.7°C max wet bulb temperature)		
Regulatory approvals and declarations	UL/cUL, FCC, TUV, CE, CB, Mexico NOM, RCM/R-NZ, VCCI, Argentina S-Mark, CCC, UKCA		
Mounting Options	75mm VESA mount		
Warranty	3-year warranty extendable up to 5 years		
Extended Warranty Options	4 year - E819598; 5 year - E819795; 3 year + AUR - E820186; 4 year + AUR - E820388; 5 year + AUR - E820582		
MTBF	50,000 hours demonstrated		
What's in the box	EloPOS, NA Power Cord, EU Power Cord, Power Adapter - 180W, Cable RJ-45 to DB-9, Cable cover locking screw, QIG		

Ordering Information

Part Number	Processor	OS	Memory	Storage	Mount
E545090	G4900T	None	4GB	128GB SSD	Stand
E545855	G4900T	Windows 10	4GB	128GB SSD	Stand
E234757	J4125	Windows 10	8GB	128GB SSD	Stand
E547949	G4900T	None	4GB	128GB SSD	Wall Mount
E494164	J4125	Windows 10	4GB	128GB SSD	Wall Mount
E547189	G4900T	None	8GB	128GB SSD	Wall Mount
E931706	i3-9100TE	None	4GB	128GB SSD	Stand
E931896	i3-9100TE	Windows 10	4GB	128GB SSD	Stand
E590570	i3-9100TE	None	4GB	128GB SSD	Wall Mount
E494361	i3-9100TE	Windows 10	4GB	128GB SSD	Wall Mount
E432087	i3-9100TE	Window 10	8GB	128GB SSD	Wall Mount
E932090	i5-9500TE	None	8GB	128GB SSD	Stand
E932274	i5-9500TE	Windows 10	8GB	128GB SSD	Stand
E407443	i5-9500TE	Windows 10	8GB	128GB SSD	Wall Mount
E485078	i5-9500TE	None	8GB	128GB SSD	Wall Mount
E590763	i5-9500TE	None	8GB	256GB SSD	Wall Mount
E859791	i5-9500TE	Window 10	8GB	256GB SSD	Stand

Learn more about Elo at [EloTouch.com](https://www.elotouch.com).

Americas

Tel +1 408 597 8000
elosales.na@elotouch.com

Europe (EMEA)

Tel +32 (0)16 70 45 00
EMEA.Sales@elotouch.com

Asia Pacific

Tel +86 (21) 3329 1385
www.elotouch.com.cn

* Coverage is available wherever Elo devices are sold in the United States. Select coverage is available in other countries. Terms & Conditions Apply..

Elo reserves the right to change or update, without notice, any information contained herein; to change, without notice, the design, construction, materials, processing or specifications of any products; and to discontinue or limit production or distribution of any products. Elo, the Elo logo, EloCare, EloPOS and TouchPro are either trademarks or registered trademarks of Elo Touch Solutions, Inc. All other trademarks are the property of their respective owners. © 2024 Elo Touch Solutions, Inc. All rights reserved. 24111AES00134

