

OVERVIEW



1. Kensington Security Slot	7. USB 3.2 Gen 1
2. Power connector	8. USB 3.2 Gen 1 (BC)
3. HDMI 2.1 TMDS	9. Audio line-out (3.5mm)
4. DisplayPort 1.4	10. USB 3.2 Gen 1
5. DisplayPort out	11. USB 3.2 Gen 1
6. USB-B 3.2 Gen 1	

PERFORMANCE

Panel

Panel

4-side NearEdgeless, In-Plane Switching

Backlight

WLED

Display Size

27 inches

Max View Area

WxH: 596.7 x 335.7 mm

Resolution

2560 x 1440

Aspect Ratio

16:9

Pixel Pitch

0.233 x 0.233 mm

Dot / Pixel Per Inch

109 dpi

Brightness

350 cd/m²

Contrast Ratio

- Dynamic Contrast Ratio: 3000000:1
- Contrast Ratio: 1000:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms
- Off Mode: 14 ms

Refresh Rate

- 60Hz (Typical)
- 75Hz (Max.)^[1]

Color Gamut

- 99% sRGB
- 95% DCI-P3
- 99% BT.709

Color Support

1.07 Billion

Color Depth

10-bit (8-bit+FRC)

Screen Surface Treatment

- Hard Coating (3H)
- Anti-glare

Notes:

[1] Under specified settings.

Operating System

Operating System

- Windows® 11 Support
- Windows® 10 Support

Multi-Media

Camera

- No bundled webcam (Support ThinkVision® MC 60 Monitor Webcam, sold separately)
- ThinkVision® MC 60 monitor webcam (Some models only)

Speakers

Optional Modular Soundbar support (MS30 Monitor Soundbar)

Power Supply

Power Consumption

- Typical / Max: 23W / 68W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Energy Star Power On: 20W
- Energy Star TEC: 60kWh
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- HDR10 Compliance
- Factory Calibration: Avg. Delta E<2
- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support
Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems).
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- Natural Low Blue Light
- Smart Power
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

DESIGN

Mechanical

ThinkCentre® M Series Support

ThinkCentre® M Series Tiny Support
For supporting Tiny devices, additional Tiny Clamp Bracket Mounting Kit III (PN: 4XF1K72399) is needed (sold separately).

Bezel Width

- Side: 2mm
- Top / Bottom: 2mm / 2mm

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)^[1]

Models	Dimensions
Lowest Position	611.9 x 204.5 x 380.3 mm (24.09 x 8.05 x 14.97 inches)
Highest Position	611.9 x 204.5 x 535.3 mm (24.09 x 8.05 x 21.07 inches)
Head Only	611.9 x 48.0 x 353.4 mm (24.09 x 1.89 x 13.91 inches)

Packaging Dimensions (WxDxH)

690 x 148 x 525 mm (21.17 x 5.83 x 20.67 inches)

Weight^[2]

Models	Weight
Monitor With Stand	6.8 kg (15.0 lbs)

Monitor Head Only	4.7 kg (10.4 lbs)
-------------------	-------------------

Packaging Weight

10.0 kg (22.1 lbs)

Mounting

Supports VESA mount 100mm

Stand

Supports -5° to +23.5° tilt, left & right 45 swivel, -90° to +90° pivot, up to 155mm lift

In the Box

- Monitor with Stand
- 1x DP Cable (1.8m)
- 1x USB-A to USB-B Cable (1.8m)
- 1x Power Cable (1.8m)
- Factory Calibration Report
- Quick Setup Guide

Notes:

- [1] The system dimensions may vary depending on configurations.
- [2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Ports^[1]

Rear Ports

- 1x USB-B 3.2 Gen 1, USB upstream
- 4x USB 3.2 Gen 1 (1x BC 1.2), USB downstream
- 1x HDMI® 2.1 TMDS^[2]
- 1x DisplayPort™ 1.4
- 1x DisplayPort™ out
- 1x Power Connector
- 1x audio-out (3.5mm)

Notes:

- [1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
- USB 2.0: 480 Mbit/s;
- USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
- USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
- USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
- USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;
- Thunderbolt™ 3/4: 40 Gbit/s.
- [2] Supports 2560x1440@60Hz as specified in HDMI® 2.1

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- ENERGY STAR® Certified
- EPEAT™ Gold Registered^[2]
- RoHS compliant
- TCO Certified
- TCO edge

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2] EPEAT™ is registered where applicable, please visit epeat.net for registration status by country.

Other Certifications

Other Certifications

- Eyesafe® Certified
 - TÜV Rheinland® Eye Comfort Certification
 - TÜV Rheinland® Low Blue Light (Hardware Solution)
-
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
 - The specifications on this page may not be available in all regions, and may be changed or updated without notice.

