



GCEH4K

# 4K HDMI Console Extender w/ Keyboard and Mouse Support

The GCEH4K extends HDMI signals, including 4K@60Hz video and high-quality audio, over up to 70 meters of Ethernet cables. It supports various HDR formats and offers features such as KVM (keyboard, video, mouse) extension and Power over Cable (PoC). Ideal for home theaters, conference rooms, and digital signage.



HDMI®  
UNIVERSAL SERIAL BUS INTERFACE



## Features

- HDCP 2.2 compliant
- Supports 18Gbps video bandwidth
- Supports video resolution up to 4K @60Hz RGB/YCBCR 4:4:4
- Supports HDR, HDR10, HDR10+, and Dolby Vision pass through
- HDMI and KVM over one single Cat5e/6/6A cable up to 230ft/70m
- Zero latency
- Supports mouse & keyboard, touch panel extension via USB
- EDID copy pass-through function between the source device and display device
- Support bi-directional POC (Power over Cable) function
- Audio formats: LPCM 2.0/2.1/5.1/6.1/7.1, Dolby Digital, Dolby TrueHD, Dolby Digital Plus (DD+)
- Support 3.5mm analog audio de-embedding, audio is output through the L/R OUT port of the receiver
- With USB KVM pass-through function, USB1.1 compliant, support remote-control by keyboard and mouse

## Requirements

### Transmitter:

- 1 x HDMI Source up to 3840x2160
- 1 x HDMI Display (Optional)

## Package Contents

- 1 x Wired HDMI Transmitter
- 1 x Wired HDMI Receiver
- 1 x USB-A to USB-A Cable
- 1 x 12V/1A Locking Power Adapter

[www.iogear.com](http://www.iogear.com)



- 1 x Ethernet Cable (Cat5e/6/6A) up to 230ft/70m
- 1 x USB-A port for Keyboard and Mouse Support
- 1 x Power source\*

- 4 x Mounting Ears
- 8 x Machine Screws
- 1 x User Manual
- 1 x Warranty Card

**Receiver:**

- 1 x HDMI Display
- 1 x Standard 3 button mouse
- 1 x Standard 104 key keyboard
- 1 x Power source\*

\* 1 x 12V/1A Power adapter included. Power-Over-Ethernet will share power to both units



## Specifications

FUNCTION	GCEH4K	DIMENSIONS	GCEH4K
Console Connectors		Unit Dimensions	
Monitor	1 x HDMI Female	Height	.87in.
Keyboard	1 x USB Type A Female	Depth	3.5in.
Mouse	1 x USB Type A Female	Width	2.7in.
CPU Connectors		Unit Package Dimensions	
Keyboard, Mouse, and Monitor	1 x HDMI 1x USB-B Female	Height	2.95in.
Unit to Unit Connectors	1 x RJ45 Female	Width	8.47in.
Power Connections	1 x DC Jack	Depth	5.31in.
LEDs		Master Carton	
Local	1 x Link Signal Indicator 1 x Data Signal Indicator	Height	11.5in.
Remote	1 x Link Signal Indicator 1 x Data Signal Indicator	Width	9.76in.
Power Consumption	Local: DC12V, 12W; Remote: DC12V, 12W	Depth	17.68in.
Power		Master Carton Qty.	12
Voltage	DC12V	Weight	
Amps	1A	Master Carton Wt.	FILL
Video Resolution	Up to 3840x2160@60Hz	Unit Pack Wt.	FILL
Cable Distance	Up to 230ft (70m)	Unit Wt. w/accessories	FILL
Environment		Unit Wt.	.75lb
Operation Temperature			
Storage Temperature			
Humidity			
Housing			
Case	Metal		