C2G

C2G
100ft (30.5m) RJ11 High Speed Internet Modem Cable
Part No. CG-28726



Enables data transmission up to 10 times faster than an ordinary phone cable when connecting telephones, answering machines, and fax machines. Ultra-flexible jacket makes cable installation easy. 24k gold-plated connectors provide corrosion resistance for maximum conductivity. Snagless, molded connector enables increased flexibility and durability for effective strain relief.

Foil double-shielding with the braid shield reduce interference while the twisted-pair construction minimizes crosstalk for high speed, error-free data transfer.

Features & Benefits

- Use to connect a modem to a telephone jack
- Double foil shielded to reduce EMI
- Standard RJ11 telephone connectors
- Available in lengths up to 100ft

Specifications

General Info

Product Line	C2G	UPC Number	757120287261
Country Of Origin	China	Application Sector	Commercial, Industrial, Residential
Warranty Type	Lifetime	Type	Cable

Dimensions

Product Length US	100.0 FT	Cable Length	100 ft
Outside Diameter	5.5 mm		

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	REACH Compliant	Yes

Additional Information

RoHS Compliant	Yes

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Cable Type	Modem	Jacket Rating	Standard / Non-Rated
Indoor/Outdoor	Indoor	Connector 2	RJ-11 Male
Connector 1	RJ-11 Male	Operating Temperature	-20°-80°C
Storage Temperature	-20° - 80° C		