



HP Engage One Pro 15.6 G2 AiO System (BF6S8UT)



Overview

Sleek design. Fast performance. Customizable experiences.

Elevate your customer experiences and power business operations. The HP Engage One Pro G2 combines a sleek yet durable design with powerful compute and is customizable for your specific business needs.

Sophisticated design meets versatile deployment.

The sleek HP Engage One Pro G2 is purposefully designed for custom deployments. Choose from three screen sizes, multiple operating systems, and a vast ecosystem of peripherals that attach flush to the screen keeping countertops clutter-free.

Durability you need. Security you can trust.

This system is built to endure. HP Engage One Pro G2 is backed by military standard testing and resists dust and liquid intrusion (IP44 rated)[3]. HP Wolf Security for Business creates a hardware-enforced, always-on defense against modern threats. [4]

Fast performance for exceptional experiences.

Enable fast, seamless customer transactions and interactions with up to an Intel® Core™ i7 processor[1], 64GB DDR5 memory, 8 TB NVME M.2 SSD storage, and WiFi 7[2]. Manage your system remotely with optional Intel® vPro™.

Sustainability in Action.

HP is innovating with purpose and intention to drive impactful, positive, lasting change. This device is crafted with at least 85% post-consumer recycled[5] plastic, comes in recycled packaging[6], and is ENERGY STAR® certified and EPEAT® Gold registered.

[1] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[2] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. WiFi 7 (802.11BE) functionality requires compatible Windows 11 OS, compatible processor, and separately purchased WiFi 7 router to support backwards compatibility with prior 802.11 specs. Available in countries where WiFi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices.

[3] Liquid intrusion IP44 rating only applies to head unit. MIL-STD-810G testing is not intended to demonstrate fitness of U.S. Department of Defense (DoD) contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental requires an optional HP Accidental Damage Protection Care Pack.

[4] HP Wolf Security for Business requires Windows 10 or 11 Pro and higher, includes various HP security features and is available on HP Pro, Elite, RPOS and Workstation products. See product details for included security features.

[5] Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT standard for computers, IEEE 1680.1-2018 standard.

[6] 100% of HP paper-based packaging is from recycled or certified sustainable sources. HP paper and fiber based packaging for PCs, displays, home and office print, and supplies is reported by suppliers as recycled or certified, with a minimum of 97% by volume verified by HP. Packaging is the box that comes with the product and all paper-based materials inside the box. Packaging for personal systems accessories and spare parts is not included.

Specifications

Operating system	Windows 11 IoT Enterprise
Processor family	Intel® Celeron® processor
Processor	Intel® Celeron® G6900T (2.8 GHz base frequency, 4 MB L3 cache, 2 cores, 2 threads) ^[6]
Memory	8 GB DDR5-5600 MT/s (1 x 8 GB)
Memory Slots	2 SODIMM
Internal Storage	256 GB PCIe® NVMe™ M.2 SSD
Internal drive bays	Two M.2
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics 710
Display	39.6 cm (15.6") diagonal, FHD (1920 x 1080), touch, IPS, anti-glare, 400 nits, 45% NTSC
Display	15.6" diagonal, FHD (1920 x 1080), touch, IPS, anti-glare, 400 nits, 45% NTSC ^[15,16]
Audio	Integrated HD audio with Realtek ALC3247 codec with standards internal speakers and stereo headphone jack, 2W
Dimensions (W x D x H)	15.2 x 1 x 15.2 cm (pro stand); 39.16 x 2.64 x 24.1 cm (head landscape); 39.16 x 24.1 x 2.64 cm (head portrait); 23.15 x 11 x 11 cm (advanced stand) <i>(Stand only.)</i>
Dimensions (W x D x H)	0.6 x 0.4 x 0.6 in (pro stand); 9.1 x 4.3 x 4.3 in (advanced stand); 15.4 x 1 x 9.5 in (head landscape); 15.4 x 1 x 9.5 in (head portrait) <i>(Stand only.)</i>
Weight	3.37 kg (15.6" display models); 0.06 kg (pro stand); 1.7 kg (advanced stand)
Weight	7.4 lb (15.6" display models); 1 lb (pro stand); 3.7 lb (advanced stand)
Ports	2 USB Type-A 5Gbps signaling rate (HP Sleep and Charge); 2 USB Type-A 5Gbps signaling rate; 1 audio-out; 1 USB Type-C® 10Gbps signaling rate (140W USB Power Delivery, DisplayPort™) ^[8]
Expansion slots	1 M.2 2230 ^[22]
Ports	1 security lock slot
Ports	1 USB Type-A 5Gbps signaling rate
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card
Power	280 W external power adapter, up to 89% efficiency
Sustainable impact specifications	Low halogen; 25% ITE-derived closed loop plastic; 75% post-consumer recycled plastic; 80% recycled aluminum in the rear plate; 15% recycle SGCC steel chassis; 50% ocean-bound plastic in fan enclosure
UPC number	199251038914

Support service included

HP 3y NBD Onsite RPOS Support Bundling. For terms and conditions, please visit <https://h20195.www2.hp.com/v2/GetPDF.aspx/4AA5-6385ENW> & <https://www8.hp.com/h20195/v2/getpdf.aspx/4AA5-7123ENUS.pdf>

Additional specifications

Accessories	A2XQ3AV Engage One Pro AiO RJ45 Extender Cable; A2XQ4AV HP Engage Indicator Light; A2XU2AV HP DIB EngageOnePro 6.6 Display; A40ZCAV HP Engage 10 inch Attached Display; A40ZDAV HP Engage 10 White Display; A40ZFAV HP Engage 10t Attached Display; A40ZGAV HP Engage 10t White Display; A2XR9AV HP Engage One Pro Integrated MSR; A2XU6AV HP Engage One Pro Integrated MSR White; A2XT9AV HP Adv Fan Attach Port Replicator; A2XU3AV HP Engage 2x20 Black Attached Display; A2XU4AV HP Engage One Pro FingerPrint Reader; A2XV2AV HP USB to Serial Port Adapter; A2XW2AV HP 6.6w Attached Display; A2XW3AV HP Engage 6.6 Attached Display
Barcode reader	Optional HP Engage One Pro Integrated Barcode Scanner
Bluetooth version	Bluetooth® 5.3
Color gamut	45% NTSC
Datasheet photo 1	AHID/6509577e6e4e5673d99db6ee90017bff709d3c6c
Datasheet photo 3	AHID/fdcba3dc6d447490f735e1b55766a5b7f8c6e555
Datasheet photo 4	AHID/78cf9b870edce6c8b836e4e5c148e95ef882285e
Datasheet photo 5	AHID/37b578740f998c6b3f537e60e389044af7646dcb
Display brightness	400
Display brightness uom	nits
Display panel technology	IPS
Display resolution (pixels)	1920 x 1080
Display resolution standard	FHD
Display size (diagonal) uom	"
Display size (diagonal, imperial)	15.6
Display size (diagonal, metric)	39.6
Display size (diagonal, metric) uom	cm
Display surface treatment	Anti-glare
Display touchscreen type	Touch screen
External I/O ports footnote number	[9]
External I/O ports footnote number	[10]
I/O Port location	Display head
I/O Port location	Internal
I/O Port location	Side
Magnetic stripe reader	Optional integrated magnetic stripe reader
Manageability Features 1	Intel® vPro® with AMT 11.0

Manageability Features 2	TPM 2.0
Manageability Features 3	HP System Software Manager (SSM)
Manageability Features 4	HP Image Assistant
Manageability Features 5	HP Client Security Manager
Manageability Features footnote number 5	[17]
Memory layout (slots & size)	1 x 8 GB
Memory module type	SODIMM
Memory size	8
Memory size uom	GB
Memory speed	5600
Memory speed uom	MT/s
Memory type	DDR5
Number of memory slots	1
Operating humidity range	20 to 85% RH
Operating temperature range	10 to 40°C
Operating temperature range	50 to 104°F
Processor Brand	Intel®
Processor base frequency	2.8
Processor cache	4 MB L3
Processor core	2
Processor family	Celeron®
Processor frequency UOM	GHz
Processor model	G6900T
Processor threads	2
Security management	Seamless Firmware Update Service
Security management	Secured-core PC capable
Security management	HP Sure Sense
Security management	HP Client Security Manager Gen7
Security management	Windows Hello Enhanced Sign-in Security (ESS) Enable
Security management	Absolute Persistence Module
Security management	HP Secure Erase
Security management	Trusted Platform Module TPM 2.0 Embedded Security Chip shipped with Windows 10 (Common Criteria EAL4+ Certified)(FIPS 140-2 Level 2 Certified)
Security management	HP Sure Click
Security management	HP Sure Admin

Security management	HP BIOSphere Gen6
Security management	HP Platform Certificate
Security management	HP Sure Run Gen6
Security management	HP Tamper Lock
Security management	HP Sure Start
Security management footnote number	[23]
Security management footnote number	[19]
Security management footnote number	[30]
Security management footnote number	[25]
Security management footnote number	[27]
Security management footnote number	[24]
Security management footnote number	[29]
Software included	HSA Fusion for Commercial
Software included	HP Connection Optimizer
Software included	myHP
Software included	HP PC Hardware Diagnostics UEFI
Software included	Touchpoint Customizer for Commercial
Software included	HP Notifications
Software included	HP PC Hardware Diagnostics Windows
Software included	HP Privacy Settings
Software included	HP Desktop Support Utilities
Software included	HP Support Assistant
Software included	HP QuickDrop
Software included	HSA Telemetry for Commercial
Software included footnote number	[20]
Software included footnote number	[21]
Software included footnote number	[28]
Standard memory note	Transfer rates up to 5600 MT/s.
Storage capacity	256
Storage capacity uom 01	GB

Storage form factor 01	M.2
Storage interface 01	PCIe®
Storage interface protocol 01	NVMe™
Storage type	SSD
Storage type 01	SSD
UNSPSC code	43211505
Wireless Model	Wi-Fi 6E AX211
Wireless antenna	2x2
Wireless standard	Wi-Fi 6E
Wireless supplier	Intel®

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[8] HP 140W port only compatible with the 140W cable included with the product. Cable required for the HP Engage One Pro to operate.

[15] Actual brightness will be lower with touch screen.

[16] For further details please refer to Quick Specs document.

[22] Wireless cards are optional or add-on features and requires separately purchased wireless access point and internet service. Availability of public wireless access points limited. The specifications for the 802.11ac WLAN are draft specifications and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the notebook to communicate with other 802.11ac WLAN devices.

Services

HP Care Pack Services

★ : Recommended

Personal Systems Commercial Care Pack Services

HP 4y Onsite RPOS Supp	UE6F5E ★
HP 3y Onsite w/Predictive Detection Alerts RPOS	UE9J5E ★
HP 3y Onsite w/Predictive Detection Alerts/Preferred Access RPOS	UE9K7E ★
HP 1y Post Warranty Onsite w/Predictive Detection Alerts RPOS	U67VZPE
HP 1y Post Warranty Onsite w/Predictive Detection Alerts/ Peripherals Desktop	U67W0PE
HP 3 year Recover - Restore Onsite SW Supp	U80LQE
HP 3 year Recover Hard Disk Data SW Supp	U80LNE
HP 3y Onsite w/DMR RPOS Supp	UE6F7E
HP 3y Onsite w/DMR/Peripherals RPOS Supp	UE9J2E
HP 3y Onsite w/Peripherals RPOS Supp	UE6G0E
HP 3y Onsite w/Predictive Detection Alerts/DMR RPOS	UE9J8E
HP 3y Onsite w/Predictive Detection Alerts/DMR/Peripherals RPOS	UE9K4E
HP 3y Onsite w/Predictive Detection Alerts/Peripherals RPOS	UE9K1E
HP 3y Onsite w/Predictive Detection Alerts/Preferred Access/DMR RPOS	UE9LOE
HP 3y Onsite w/Predictive Detection Alerts/Preferred Access/DMR/Peripherals RPOS	UE9L6E
HP 3y Onsite w/Predictive Detection Alerts/Preferred Access/Peripherals RPOS	UE9L3E
HP 4y Onsite w/DMR RPOS Supp	UE6F8E
HP 4y Onsite w/DMR/Peripherals RPOS Supp	UE9J3E
HP 4y Onsite w/Peripherals RPOS Supp	UE6G1E
HP 4y Onsite w/Predictive Detection Alerts RPOS	UE9J6E
HP 4y Onsite w/Predictive Detection Alerts/DMR RPOS	UE9J9E
HP 4y Onsite w/Predictive Detection Alerts/DMR/Peripherals RPOS	UE9K5E
HP 4y Onsite w/Predictive Detection Alerts/Peripherals RPOS	UE9K2E
HP 4y Onsite w/Predictive Detection Alerts/Preferred Access RPOS	UE9K8E
HP 4y Onsite w/Predictive Detection Alerts/Preferred Access/DMR RPOS	UE9L1E
HP 4y Onsite w/Predictive Detection Alerts/Preferred Access/DMR/Peripherals RPOS	UE9L7E
HP 4y Onsite w/Predictive Detection Alerts/Preferred Access/Peripherals RPOS	UE9L4E

HP 5y Onsite RPOS Supp	UE6F6E
HP 5y Onsite w/DMR RPOS Supp	UE6F9E
HP 5y Onsite w/DMR/Peripherals RPOS Supp	UE9J4E
HP 5y Onsite w/Peripherals RPOS Supp	UE9J1E
HP 5y Onsite w/Predictive Detection Alerts RPOS	UE9J7E
HP 5y Onsite w/Predictive Detection Alerts/DMR RPOS	UE9K0E
HP 5y Onsite w/Predictive Detection Alerts/DMR/Peripherals RPOS	UE9K6E
HP 5y Onsite w/Predictive Detection Alerts/Peripherals RPOS	UE9K3E
HP 5y Onsite w/Predictive Detection Alerts/Preferred Access RPOS	UE9K9E
HP 5y Onsite w/Predictive Detection Alerts/Preferred Access/DMR RPOS	UE9L2E
HP 5y Onsite w/Predictive Detection Alerts/Preferred Access/DMR/Peripherals RPOS	UE9L8E
HP 5y Onsite w/Predictive Detection Alerts/Preferred Access/Peripherals RPOS	UE9L5E

Personal Systems Hardware Support Onsite Service

HP 1 year Post Warranty Next Business Day Onsite RPOS Solution Support	UL597PE
HP 1y Post Warranty Onsite RPOS Support	U8CD0PE

Accessories

Point of Sales System Options

★ : Recommended

POS Display Accessories

HP Engage 10 HD No Stand + VESA Mount Monitor	3F1W8AA
HP Engage 10t HD No Stand + VESA Mount Monitor	3F1W9AA
HP Engage 2x20 Customer Facing Display	6K552AA
HP Engage One 10.1-inch Display	1XD80AA
HP Engage One 10.1-inch Touch Display	1XD81AA
HP Engage One W 10.1-inch Display	3FH66A8
HP Engage One W 10.1-inch Display	3FH66AA
HP Engage One W 10.1-inch Touch Display	3FH67A8
HP Engage One W 10.1-inch Touch Display	3FH67AA

Disclaimer—Copyright

© Copyright 2015. Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Mar 26, 2025 11:52 AM UTC+0000