

# Pipe protection profile P30

Article number	1115130	Sales unit quantity	5 Piece
Colour	Yellow / black	Sales unit EAN	4005546735818
Packaging unit	5 pieces / pack	Packing weight (gross)	1652 G
Base EAN	4005546735801	Country of origin	CN



## Product description

- Self-adhesive, flexible pipe protection profile made of polyurethane foam.
- For indoor use only
- Suitable for pipes or cables with a diameter of 20 mm - 40 mm that are placed near walkways for structural reasons.
- Ideal for use in manufacturing, shipping department and warehousing, stairwells or in confined areas such as basements or garages with low passageways, etc.
- Marks danger spots, protects pipes and lines and mitigates impact injuries.
- Profiles can be shortened to the desired length with a sharp cutter knife
- Colour according to ASR A1.3 similar to RAL 1004/9003 (signal yellow/signal black)
- Fire test according to DIN EN 13501-1:2018-12 class E
- Temperature resistant from -30°C - + 70°C
- Profile length: 1 m
- Inner diameter: 30 mm

## Product features

Outer width (mm)	50
Outer height (mm)	25
Outer depth / length	1,000 mm
Brand	DURABLE
Inner width (mm)	30

# Pipe protection profile P30

Shape	Round
Self-adhesive type	Permanent
Material thickness	10 mm
Special colour	Similar to RAL 1003 signal yellow / 9004 signal black
Application area	Indoor area, protected outdoor area
Mounting type	Self-adhesive