



Powering Business Worldwide

TRIPP LITE  
SERIES

## PDU Power Cords, C13 to P-Lock C14 - Heavy-Duty, 15A, 250V, 14 AWG, 10 ft. (3.1 m), Red, 6 Pack

MODEL NUMBER: P005-E10-ARD-6



Connect computers, servers or switches to a PDU with a P-Lock C13 or C39 power connector and extend existing power connections by 10 ft.

### Features

#### C13-to-C14 Power Cables for Network Devices That Require a Heavy-Gauge Connection

These power extension cords feature 14 AWG wire suitable for high power connections, making them a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. The P005-E10-ARD-6 can be used to power computers, servers, switches or other devices commonly found in a small data center, office workstation or other lower-amp application. The 10-foot (3.1-meter) length helps reduce cable clutter by providing a tailor-made fit between the device and the PDU in a crowded rack enclosure. Six PDU power cables are included, an ideal pack for large-scale equipment rollouts.

#### Forms a Special Locking Connection with a P-Lock Outlet

The P-Lock C14 connector forms a secure connection with a PDU with a P-Lock outlet, including Eaton G4 and newer PDUs with C13 and C39 outlets. The P-Lock connection helps reduce costly downtime caused by accidental cable disconnections in a crowded rack or PDU space. The P005-E10-ARD-6 lets you replace a non-locking C14/C13 cable or upgrade an entire PDU application by pairing with an Eaton PDU or other PDU with P-Lock outlets.

#### Red Jackets Help Avoid Misidentification That Can Cause Costly Downtime

The UL-listed cables have a red PVC jacket with fully molded red ends, which is easy to identify quickly in a crowded PDU or UPS system and helps prevent the cables from becoming accidentally disconnected.

### Highlights

- Recommended for powering computers, servers and other network devices
- P-Lock C14 connector eliminates accidental cable disconnections in a crowded PDU
- Thick 14 AWG wire gauge manages high power levels required for larger equipment
- Red cable jacket allows quick identification of devices in a crowded rack enclosure
- 6 PDU power cables included, ideal for large-scale equipment rollouts

### Package Includes

(6) PDU Power Cords, C13 to P-Lock C14, 10 ft. (3.1 m), Red

## Specifications

| OVERVIEW             |                                                   |
|----------------------|---------------------------------------------------|
| UPC Code             | 037332292858                                      |
| Product Type         | PDU Power Cord                                    |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region       | North America                                     |



Powering Business Worldwide

TRIPP LITE  
SERIES

| INPUT                              |                              |
|------------------------------------|------------------------------|
| Maximum Input Amps                 | 15                           |
| Voltage Compatibility (VAC)        | 100-250                      |
| CONNECTIONS                        |                              |
| Side A - Connector 1               | IEC-320-C14                  |
| Side B - Connector 1               | IEC-320-C13                  |
| PHYSICAL                           |                              |
| Plug Color                         | Red                          |
| Cable Jacket Color                 | Red                          |
| Connector Color                    | Red                          |
| Cable Jacket Material              | PVC                          |
| Cable Jacket Rating                | VW-1                         |
| Power Cord Jacket Type             | SJT                          |
| Cable Outer Diameter (OD)          | 9.3mm                        |
| Number of Conductors               | 3                            |
| Wire Gauge (AWG)                   | 14                           |
| Wire Gauge (OD - mm <sup>2</sup> ) | 2.08                         |
| Cable Length (ft.)                 | 10                           |
| Cable Length (m)                   | 3.05                         |
| Shipping Dimensions (hwd / in.)    | 18.11 x 14.17 x 0.50         |
| Shipping Weight (kg)               | 3.07                         |
| Unit Dimensions (hwd / in.)        | 10.000 x 7.990 x 0.500       |
| ENVIRONMENTAL                      |                              |
| Operating Temperature Range        | 23° to 158°F (-5° to 70°C)   |
| Storage Temperature Range          | 14° to 140°F (-10° to 60°C)  |
| Relative Humidity                  | 35 TO 85% RH, Non-Condensing |
| FEATURES & SPECIFICATIONS          |                              |
| Antibacterial                      | No                           |
| Angled Plug                        | No                           |
| High Voltage                       | Yes                          |
| Locking Plug                       | Yes                          |
| Coiled Power Cord                  | No                           |



Powering Business Worldwide

TRIPP LITE  
SERIES

| STANDARDS & COMPLIANCE              |                           |
|-------------------------------------|---------------------------|
| Product Certifications              | cUL Listed; UL Listed     |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.