Lenovo D20-30 Monitor 66E9KAC4IN

PSREF
Product Specifications Reference

PERFORMANCE

Display Size
19.5″

View Area
432.96x238.05 mm

Panel
Twisted Nematic

Backlight
WLED

Aspect Ratio
16:9

Resolution
1600x900

Pixel Pitch
0.271x0.264 mm

Dot / Pixel Per Inch
94 dpi

View Angle (H / V)
170° / 160°

Response Time
2ms (On) / 5ms (Off)

Color Support
16.7 Million

Refresh Rate
60Hz

Brightness
250 cd/m²

Contrast Ratio
1000:1

Color Gamut
72% NTSC

Screen Surface Treatment
Anti-glare

Curvature
None

Camera
None

Microphone
None

Speakers
None

Power Consumption (Typical / Maximum)
12W / 15W

Power Adapter
Integrated

Touchscreen
None

Smart System
None

DESIGN

Stand
Tilt Stand

Case Color
Raven Black

Side Bezel Width
15.3 mm

Mounting
Supports VESA mount 100mm

ThinkCentre M Series Support
Tiny, Nano Support

Pen
Pen Not Supported

Dimensions (WxDxH)[1]
- Unpacked with Stand | 464.8 x 180.4 x 351.6 mm (18.30 x 7.10 x 13.84 inches)
- Unpacked Head Only | 464.8 x 48.3 x 283.5 mm (18.30 x 1.90 x 11.16 inches)

Packaging Dimensions (WxDxH)
560 x 125 x 350 mm (22.05 x 4.92 x 13.78 inches)

Weight[2]
- Monitor With Stand | 2.5 kg (5.5 lbs)
- Monitor Head Only | 2.2 kg (4.8 lbs)

Packaging Weight
3.7 kg (8.2 lbs)

CONNECTIVITY

USB Port
None

Video Connector
1x HDMI® 1.4, 1x VGA

Network Connectivity
None

SERVICE

Base Warranty
3-year

CERTIFICATIONS

Environmental Certification
Energy Star Certified, TCO 9.0, TCO Edge 2.0, EPEAT™ Silver, RoHS, Volatlle Organic Compound Certification

Ergonomic Certification
TÜV Rheinland® Low Blue Light, TÜV Rheinland® Flicker Free

Sync Technology
None

SOFTWARE

Operating System
Support Windows® 7, Windows® 10, Windows® 11

ACCESSORIES

In the Box
- Monitor with stand
- 1x HDMI® cable (1.8m)
- 1x Power cable (1.8m)
- Quick setup guide
- Warranty booklet

MODEL

Region : ASN
EAN / UPC / JAN: 0196119950814 / 196119950814 / None
Announce Date : 2022-02-14



Product image is a sample, it may not match the real color of this model
Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

United States of America



Kensington MicroSaver DS 2.0 Cable Lock from Lenovo 4XE1L68273



ThinkCentre Tiny VESA Mount II 4XF0N03161



Please click here to view the full list of accessories.

Lenovo PSREF
Product Specifications Reference