



UH1510P EQ USB-C® 5Gbps Triple Video Driverless Mobile Dock

Part Number: K34040WW | UPC Code: 0 85896 34040 9

Triple video for Windows in a mobile dock.

Professionals want triple monitor support for maximum productivity wherever they are working. Most mobile docking stations are limited to single or dual monitor configurations, which leaves desktop docks as the only connectivity option, but those come with the added inconvenience of being heavy and bulky, especially when accounting for the power brick. Offering more display options to enhance productivity at the desk and reducing the need for dongles and adapters while traveling, the UH1510P EQ USB-C® 5Gbps Triple Video Driverless Mobile Dock supports up to three external displays and allows you to travel with less weight and clutter. Offering a smart and sustainability-focused 11-in-1 design, it uses your laptop's USB-C power adapter or battery for charging to eliminate an additional power brick and provides plenty of data ports so you can streamline the movement of files without the need for additional adapters or dongles.

Features include:

- Up to Triple 1080p for Windows
- Supports Thunderbolt™ 4 & 5, USB4®, and USB-C® Alt Mode devices
- Windows 10 or later, macOS 11 or later, iPadOS 13 or later, and Samsung DeX®
- Plug-and-play USB-C® driverless solution
- Up to 85W power pass-through
- 11-in-1 design with 5 USB ports and UHS-I SD3.0 Micro and SD card slots
- Sleek, compact design
- Contains at least 63% post-consumer recycled (PCR) content*
- Delivered in FSC® certified packaging
- Free Kensington DockWorks™ software**
- 2-year limited warranty




*Does not include cable.

**Available for Windows only.

UH1510P EQ USB-C® 5Gbps Triple Video Driverless Mobile Dock

Part Number: K34040WW | UPC Code: 0 85896 34040 9

Front




Back



UH1510P EQ USB-C® 5Gbps Triple Video Driverless Mobile Dock

Part Number: K34040WW | UPC Code: 0 85896 34040 9




Triple Video for Windows

Extend the visual productivity of your mobile workstation to support up to Triple 1080p @ 60Hz, Dual 4K @ 60Hz for Windows devices, and Single 4K @ 60Hz for both Windows and MacBook devices.



Universal Compatibility

Supports USB-C® based devices (Thunderbolt™ 4 & 5, USB4®, and USB-C® Alt Mode) running Windows 10 or later, macOS 11* or later, iPadOS 13* or later, and Samsung DeX®. **iPadOS or macOS supports only a single 4K @ 60Hz in extended mode.*



USB-C® Driverless Solution

No need to download, install, or update software — an ideal USB-C® plug-and-play solution.



Up to 85W Power Pass-Through

Plug your laptop's USB-C® power adapter (85W or greater) into the dock for pass-through power to the laptop, or power the dock and connected devices using the laptop's battery when traveling. Optional 100W Power Adapter sold separately (K33821NA).



11-in-1 Design with 5 USB Ports

Optimize peripheral connectivity with 3 x USB-A 3.2 Gen1 ports, 2 x USB-C® ports (one for power-pass through and one for device charging), UHS-I SD3.0 Micro and SD card slots, 2 x HDMI® and 1 x DP video connections, and 1 x Gigabit Ethernet port.




Sleek, Compact Design

Easily fits into your travel backpack or carrying case for productivity on the go. Includes a 6.7" (17cm) USB-C® cable for connecting to your host device.



Sustainability Focused

The plastic in this product contains at least 63% post-consumer recycled (PCR) content* — and it is delivered in Forest Stewardship Council (FSC®) certified packaging.



Free Kensington DockWorks™ Software and 2-Year Limited Warranty

Free DockWorks™ software** delivers the best connection, performance, and security from your Kensington dock. Enjoy peace of mind knowing you are covered by Kensington with a professional warranty.

*Does not include cable.
**Available for Windows only.

UH1510P EQ USB-C® 5Gbps Triple Video Driverless Mobile Dock

Part Number: K34040WW | UPC Code: 0 85896 34040 9

System Requirements

Systems Supported	All laptops with USB-C port (must support USB-C Alt Mode)
Operating Systems Supported	Windows® 10 or above; macOS 11 or above; iPadOS 13 and above; Samsung Dex®
Plug & Play	Yes
System Resource Requirement	CPU: Intel® Core™ i5 6th generation or above Memory: 8Gb or above GPU: Intel® HD Graphics 620 or above
USB-C Power Delivery	Power pass-through up to 85W PD3.0: 5V/9V/12V/15V @3A, 20V @ 4.25A

USB Interface

Type of USB Connector	USB-C Connector
Host Connector	Supports USB 3.2 Gen2 Type-C with USB-C Alt Mode

USB, Video, Memory Card, and Ethernet Connections

Ports	2x HDMI 2.0 1x DP++ 1.4 3x USB-A 3.2 Gen 1 1x USB-C 3.2 Gen 1 1x SD 3.0 Slot 1x Micro SD 3.0 Slot 1x USB-C (for power pass-through only, up to 85W) 1x Ethernet 10/100/1000 Mbps
-------	---

Network Connections

Ethernet Port	RJ45
Compatible Ethernet Speeds	10/100/1000 Mbps

Host Connectivity

Host Docking Connector	USB-C cable with Power Pass-Through up to 85W
------------------------	---

Video Connections

Video Connectors	2x HDMI 2.0 1x DP++ 1.4
Maximum Resolution Supported	Single: Up to 1x 4K (3840x2160) @ 60Hz Dual: Up to 2x 4K (3840x2160) @ 60Hz Triple: Up to 3x 1080p @ 60Hz *macOS only supports a single video output
HDCP Support	Yes, supports HDCP 2.3

UH1510P EQ USB-C® 5Gbps Triple Video Driverless Mobile Dock

Part Number: K34040WW | UPC Code: 0 85896 34040 9

Material Specifications

Exterior	Black PC with texture
Product Color	Black
Post-Consumer Recycled Content	The plastic in this dock contains at least 63% post-consumer recycled (PCR) content, not including cable

Product Dimensions

Cable Dimensions	Diameter: 0.2in (5mm) Length: 6.7in (17cm)
Unit Weight	5.4oz (154g)
Unit Dimensions without Peripherals	5.9 x 2.8 x 0.8in (150 x 71 x 21mm)

Packaging Dimensions

Packaging Style	Retail Colored Box with Hang Tag
Packaging Dimensions	7.0 x 5.11 x 1.4in (180 x 130 x 35mm)
Packaging Weight	0.18kg (0.40lbs)
Packaging Content	1 x UH1510P Mobile Dock 1 x Quick Installation Guide 1 x Compliance Sheet 1 x Warranty Card 1 x Welcome Card
Master Carton	10pcs

Power & Environmental

Relative Humidity	0% to 85% with operating temperature @ 77°F (22°C)
Operating Temperature	32 to 113°F (0 to 45°C)
Storage Temperature	-14 to 158°F (-25 to 70°C)

Country Of Origin, Regulatory, and Warranty

Country of Origin	China
Certifications & Compliance	FCC, CE, UKCA, RCM, CB, VCCI, RoHS, ACCO RSL
Warranty	2-Year Limited



All specifications are subject to change without notice. Products may not be available in all markets. Kensington® and Kensington, The Professionals' Choice™ are trademarks of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. © 2025 Kensington Computer Products Group, a division of ACCO Brands. k24-23050p

Kensington

The Professionals' Choice™