



C2G
75ft (22.9m) C2G Performance Series Ultra Flexible Active High Speed HDMI™ Cable - 4K 30Hz In-Wall, CMG (FT4) Rated
Part No. AVD_CG_C2G10385

C2G Performance Series Ultra Flexible Active High Speed HDMI™ Cables extend HDMI™ signals over a high performance active HDMI™ cable and support HDMI™ audio and video features including 4K Ultra HD.

These cables are perfect for connecting a wide variety of devices from computers to projectors and monitors, AV presentation furniture, or in-wall applications requiring high speed HDMI™ features and video resolutions up to 4K (4096 x 2160) at 60Hz - perfect for conference rooms, classrooms, houses of worship, and other commercial installations.

This Ultra Flexible Active High Speed HDMI™ Cable was designed for installations in tight spaces and offers commercial grade connectors that feature compact overmolding for high density environments, integrated finger grips on the top, bottom, and sides, for easy insertion and removal, and the gripping connector shell has 2x greater port retention to keep your devices connected. The gold plated connectors on the cable allow for better shielding, increased electrical conductivity, and durability.

C2G Performance Series Ultra Flexible Active High Speed HDMI™ Cable amplifies the signal from the source and sends it longer distances without degrading that signal. Active HDMI™ cables can only run in one direction - connect the source end to the source and the display end to your display. The connectors are conveniently labeled for source and display, so there is no confusion with this directional cable. The source connector end even has a tag on the cable as an extra reminder. Lastly, this fully-functional, high bandwidth cable has been tested to perform at industry standards and is backed by a lifetime warranty.



Features & Benefits

Supports output resolutions up to 4K (3840 x 2160) at 60Hz, providing high-quality video for viewing your screen content	In-wall (CMG/FT4) rated jacket, so you can safely run the cable inside of a wall and have a clutter free, clean look
Integrated finger grips on the connectors for easy insertion and removal	Gripping connector shell for 2x greater port retention
Gold plated connectors for increased electrical conductivity and enhanced durability	Directional cable with source connector labeled and tagged to easily differentiate from the labeled display connector
Supports CEC extensions for control of consumer electronics devices through a single control point	Backed by five-year warranty

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120103851	Country Of Origin	China
Features	Gripping Connectors	Application Sector	Commercial
Warranty Type	5-Year	Type	HDMI Cable

Dimensions

Product Weight US	2.65 kg	Product Length US	75.0 FT
Cable Length	75 ft		

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	REACH Compliant	Yes
--------------	-----	-----------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Operating Temperature Min	-40 °C
Wire Gauge	24 AWG	Video Resolution	4K 30Hz
Storage Humidity	85% RH (Non-Condensing)	Plating Specification	Gold

Jacket Application	In-Wall Rated	Bend Radius	76 mm
Signal Transmission	Unidirectional	Operating Temperature Max	79 °C
Cable Type	High Speed HDMI, Ultra-Flexible	Jacket Rating	CL2 Rated, CMG Rated, FT4 Rated
Cable Diameter	9.5 mm	Data Transfer Rate	10.2 Gbps
Connector 2	HDMI Male	Connector 1	HDMI Male
Video Output Support	HDMI	Operating Temperature	-40°-75°C
Operating Humidity	85% RH (Non-Condensing)	Video Input Support	HDMI
Conductor Material	Copper	Storage Temperature	-10° - 55° C