




SPECIFICATIONS

Marketing Name	GeForce RTX™ 5060 Ti 8G VENTUS 2X OC PLUS
Model Name	G506T-8V2CP
Graphics Processing Unit	NVIDIA® GeForce RTX™ 5060 Ti
Interface	PCI Express® Gen 5 x16 (uses x8)
Core Clocks	Extreme Performance: 2617 MHz (MSI Center) Boost: 2602 MHz
CUDA® CORES	4608 Units
Memory Speed	28 Gbps
Memory	8GB GDDR7
Memory Bus	128-bit
Output	DisplayPort x 3 (v2.1b) HDMI™ x 1 (As specified in HDMI™ 2.1b: up to 4K 480Hz or 8K 120Hz with DSC, Gaming VRR, HDR)
HDCP Support	Y
Power consumption	180 W
Power connectors	8-pin x1
Recommended PSU	600 W
Card Dimension (mm)	227 x 127 x 41 mm
Weight (Card / Package)	573 g / 834 g
DirectX Version Support	12 Ultimate
OpenGL Version Support	4.6
Maximum Displays	4
G-SYNC® technology	Y
Digital Maximum Resolution	7680 x 4320

CONNECTIONS



1. DisplayPort
2. HDMI™

FEATURES




Dual Fan
Two fans and a huge heatsink ensure a cool and quiet experience for you.




STORMFORCE FAN
Seven fan blades, claw texturing, and a circular arc are designed for optimal airflow with minimal noise.



Reinforcing Backplate
The reinforcing backplate features a flow-through design that provides additional ventilation.



Zero Frozr
The fans completely stop when temperatures are relatively low, eliminating all noise.



DrMOS
DrMOS power stage solutions provide great efficiency with low power loss and enhanced voltage controls.



Fuse
Additional fuses built into the custom PCB provide additional safeguards against electrical damage.



MSI Center
The exclusive MSI Center software lets you monitor, tweak and optimize MSI products in real-time.



Afterburner
Take full control with the most recognized and widely used graphics card overclocking software in the world.