

Specifications



Eaton P032-E04

PDU Power Cord, C13 to P-Lock Lite C20 - 15A, 100-250V, 14 AWG, 4 ft. (1.2 m), Black

General specifications

PRODUCT NAME	Eaton Tripp Lite series P-Lock power cord
CATALOG NUMBER	P032-E04
UPC	037332295316
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12.8 in
PRODUCT WIDTH	8.9 in
PRODUCT WEIGHT	0.49 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	CSA C22.2. UL Listed cUL Listed
GLOBAL CATALOG	P032-E04
PRODUCT TYPE	P-Lock power cord



Powering Business Worldwide

Product specifications

INPUT CURRENT -MAX	15 Ampere
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
RELATIVE HUMIDITY	35 TO 85% RH, Non-Condensing
STORAGE TEMPERATURE	23° to 158°F (-5° to 70°C)
DEVICE COMPATIBILITY	Computer Monitor/HDTV PDU Printer Server Tablet UPS
AWG-SIZE	14
CABLE LENGTH	4 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	9.3mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	2.08
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P032-E04 PDU Power Cord, C13 to P-Lock Lite C20, 4 ft. (1.2 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage Locking Plug
CABLE JACKET MATERIAL	PVC
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C13
SIDEB CONNECTOR1	IEC-320-C20
CONNECTOR GROUP	C13 C20
CONNECTOR	IEC 320-C13 IEC 320-C20

Resources

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

