



**C2G**  
**Dual USB-C® Power Adapter - 65W**  
Part No. AVD\_CG\_C2G58880



The 65W Dual USB-C Power Adapter from C2G is a great solution for fast and efficient charging. Designed to power Chromebooks, laptops, and tablet hybrids, this adapter features two USB-C ports that deliver up to 65W of power, ensuring seamless productivity at home, in the office, or on the go. Engineered for durability and convenience, the adapter includes foldable AC prongs, reducing the risk of damage when not in use. Safety is a top priority with built-in protections, including overcurrent, overvoltage, overload, short circuit, and over-temperature protection, providing peace of mind while charging your devices. With its sleek and elegant design, this power adapter combines style with functionality, making it a must-have accessory for professionals and students alike. Stay powered and protected with the 65W Dual USB-C Power Adapter from C2G.

## Features & Benefits

- Dual USB-C Ports** – Supports up to 65W for powering and charging two devices simultaneously with total output of up to 65W for efficient power delivery
- Foldable AC Prongs** – Reduces the risk of damage when not in use, making it ideal for travel.
- Advanced Safety Protections** – Includes overcurrent, overvoltage, overload, short circuit, and over-temperature protection for safe and reliable charging.
- Compatible with top laptop brands**, including Apple®, Microsoft® Surface®, and other leading laptops and tablets.
- Power outputs of 5V-3A, 9V-3A, 15V-3A and 20V-2.25A** for device charging
- Sleek and Elegant Design** – Combines style with functionality for a professional and modern look.

## Specifications

### General Info

Product Line	C2G	Color	White
UPC Number	757120588801	Country Of Origin	Vietnam
Features	USB-C Charging	Outlet Type	USB-Charging
Application Sector	Commercial, Residential	Warranty Type	5-Year

### Dimensions

Product Width US	1.5 in	Product Weight US	0.31 lb
Product Depth US	2.0 in	Product Height US	1.6 in

---

## Additional Information

---

RoHS Compliant	Yes	Energy Savings	No
----------------	-----	----------------	----

---

## Technical Information

---

Operating Temperature Min	0 °C	Output Voltage	20 V
---------------------------	------	----------------	------

---

Storage Humidity	5-95% RH (Non-Condensing)	Number of Ports	2
------------------	---------------------------	-----------------	---

---

USB Amperage	3.25 A	Operating Temperature Max	25 °C
--------------	--------	---------------------------	-------

---

Input Voltage	100 to 240 V	Wattage	65 W
---------------	--------------	---------	------

---

Connector 2	USB-C Female	Connector 1	USB-C Female
-------------	--------------	-------------	--------------

---

Power Delivery	65 W	Operating Temperature	0°-25°C, 32°-77°F
----------------	------	-----------------------	-------------------

---

Operating Humidity	20-90% RH (Non-Condensing)	Voltage	20.0 V
--------------------	----------------------------	---------	--------

---

Storage Temperature	0° - 25° C, 32° - 77° F
---------------------	-------------------------

---