

**OVERVIEW**



1. Card slot	4. Microphone
2. Volume button	5. USB-C (Hi-Speed USB), with charging
3. Power button	6. Headphone / microphone combo jack (3.5mm)

Notes:

- Card slot is for microSD card (WLAN model) or nano-SIM + microSD card (WWAN model)

## PERFORMANCE

### Processor

#### Processor

Processor Name	Cores	Max Frequency	Memory Support	Processor Graphics
MediaTek Helio G85	Octa-core 2x A75 + 6x A55	A75@2.0GHz / A55@1.8GHz	LPDDR4x	Arm Mali-G52 MC2 GPU

### Operating System

#### Operating System<sup>[1]</sup>

Android™ 14 or later

Notes:

[1] For latest operating system and security patches deliver plan, please visit <https://support.lenovo.com/solutions/ht501098>.

### Graphics

#### Graphics

Arm Mali-G52 MC2 GPU

### Memory

#### Max Memory

4GB soldered memory, not upgradable

#### Memory Type

LPDDR4x

### Storage

#### Max Storage Support\*\*

- 64GB eMMC 5.1 on systemboard
- 128GB eMMC 5.1 on systemboard
- microSD card, supports up to 1TB

### Removable Storage

#### Card Reader\*\*

- Nano-SIM + microSD card slot (WWAN models)
- microSD card slot (WLAN models)

### Multi-Media

#### Speakers

2 side speakers, optimized with Dolby Atmos®

#### Microphone

Single microphone

#### Camera

Front 2.0MP, fixed focus, face unlock; rear 8.0MP, autofocus

#### VoiceCall

- Voice call<sup>[1]</sup>
- No support

Notes:

[1] Use of Voice call requires cellular data plan. Voice call functionality details may vary based on local operator network, data and messaging services. Please contact your carriers for details.

### Sensor

#### Vibration Motor

- Eccentric Rotating Mass (ERM)<sup>[1]</sup>
- No support

**Sensors**

- Accelerometer sensor
- Hall sensor
- Virtual light sensor
- Virtual proximity sensor<sup>[2]</sup>

Notes:

[1], [2] for WWAN model

**Battery**

**Battery**

5100mAh (typical) Rechargeable Li-ion Battery<sup>[1]</sup>

**Max Battery Life<sup>[2]</sup>**

Video streaming: 12.5 hr of YouTube streaming

Web browsing: 16.5 hr of Chrome browsing

Notes:

[1] Support 15W quick charge

[2] All battery life claims are approximate and based on internal testing under optimal laboratory and network conditions. Actual battery performance will vary depending on numerous factors including product configuration and usage, software, operating conditions, wireless functionality, power management settings, screen brightness and other factors. The maximum capacity of the battery will naturally decrease with time and usage.

**Power Adapter**

**Power Adapter**

- 10V/2A (20W) AC adapter, 100-240V, 50-60Hz
- No power adapter

**DESIGN**

**Display**

**Display<sup>[1]</sup>**

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
8.7"	HD (1340x800)	Multi-touch	TFT LCD (IPS)	480nits	Anti-fingerprint	5:3	1500:1	60% NTSC	60Hz	85° / 85° / 85° / 85°	TÜV Low Blue Light (Software Solution), 179 PPI

**Touchscreen**

In-cell multi-touch, supports 10-point touch

**Screen-to-Body Ratio**

86%

Notes:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

**Input Device**

**Pen**

No support

**Mechanical**

**Dimensions (WxDxH)<sup>[1][2]</sup>**

211 x 124.8 x 8.5 mm (8.31 x 4.91 x 0.33 inches)

**Weight<sup>[3]</sup>**

Around 320 g (0.71 lbs)

**Case Color\*\***

- Luna grey
- Seafoam green

**Case Material**

Plastic

**Buttons**

- Power button
- Volume button

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The height is 9.45 mm (0.37 inches) with the camera bump.

[3] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

## CONNECTIVITY

### Network

**WLAN + Bluetooth®**

Wi-Fi® 5, 802.11ac 1x1 Wi-Fi® + Bluetooth® 5.3

**WWAN**

- 4G LTE
- No support

**Cellular Bands<sup>[1]</sup>**

GSM: 850/900/1800/1900MHz

UMTS: B1/2/4/5/6/8/19

FDD LTE: B1/2/3/4/5/7/8/12/13/17/18/19/20/26/28(a+b)/66

TDD LTE: B38/40/41

**Wi-Fi® Direct**

Support

**Wi-Fi® Display**

Support

**FM Radio**

FM Radio

**Location Services**

Models	Location
WLAN models	GPS + GLONASS + Galileo + Beidou
WWAN models	GPS + GLONASS + Galileo + Beidou + A-GPS

Notes:

[1] For WWAN models

### Ports<sup>[1]</sup>

**Standard Ports**

- 1x USB-C® (Hi-Speed USB / USB 2.0), with charging, digital audio
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

Notes:

[1] The transfer speed of the ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

## SERVICE

### Warranty

#### Base Warranty\*\*<sup>[1]</sup>

- 1-year carry-in service
- 1-year mail-in service
- 1-year courier service
- 2-year (1-yr battery) carry-in service
- 2-year (2-yr battery) carry-in service
- 2-year (1-yr battery) courier service
- 2-year (2-yr battery) courier or carry-in service
- 3-year (1-yr battery) courier service

Notes:

[1] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

## ACCESSORIES

### Bundled Accessories

#### Bundled Accessories\*\*\*<sup>[1]</sup>

- Bumper case
- Clear case
- Folio case
- Lenovo® E310 True Wireless Stereo Earbuds
- None

Notes:

[1] For more compatible accessories, please click [Here](#).

## OPERATING REQUIREMENTS

### Operating Environment

#### Temperature

Operating: 0°C (32°F) to 40°C (104°F)

Storage: -20°C (-4°F) to 60°C (140°F)

## CERTIFICATIONS

### Green Certifications<sup>[1]</sup>

#### Green Certifications

- ENERGY STAR® 9.0 (only available for TB305FU)
- Energy rating D (TB305FU). View details by EPREL registration number [2344005](#).<sup>[2]</sup>
- ErP Lot 6/26
- RoHS compliant
- Energy rating D (TB305XU). View details by EPREL registration number [2344016](#).<sup>[3]</sup>

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2], [3] Energy rating by EPREL is optional and only available in selected countries.

### Other Certifications

#### Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

## SOFTWARE

## Preinstalled Software

### Preinstalled Software<sup>[1]</sup>

- Assistant
- Calculator
- Calendar
- Camera
- Chrome
- Clock
- Contacts
- Drive
- Entertainment Space
- Files
- Fitbit
- FM radio
- Find my device
- Gboard
- Gmail
- Google
- Google One
- Google TV
- Kids Space
- Lenovo® Vantage
- Maps
- Meet
- Messages
- News
- Opera
- Play Books
- Play Games
- Phone<sup>[2]</sup>
- Photos
- Play Store
- Recorder
- Smart Connect
- Tide
- WPS Office
- Weather
- YouTube
- YouTube Kids
- YouTube Music

#### Notes:

[1] Actual application availability varies by country/region.

[2] For WWAN models

- Feature with \*\* means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Feature with \*\*\* means that one or more options listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. **LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

