


GC311G2

StreamLine MINI⁺



A Winning Start to Your Live Stream Journey

Features :



Better Visual Experience
High Quality Video



3-Step to Go Live
Plug & Play



Stunning Clarity
HDR Pass-Through



Ultra-Low Latency



Multiple Video Format




Seamless Capture



- Plug in and stream or record instantly
- Go live on multiple platforms with ease

AVerMedia Streaming Center is a centralized control hub combining streaming device controls, video adjustment and audio tuning into one powerful software, simplifying workflows for easy live streaming.

Connection:



Specifications :

- **Interface:** UBS 3.0 Type-C
- **Video Input & Output (Pass-Through):** HDMI 2.0
- **Audio Input & Output (Pass-Through):** HDMI 2.0
- **Max Pass-Through Resolutions:** 2160p60 HDR, 1440p144 HDR, 1080p240 HDR
- **Max Capture Resolutions:** 1080p60
- **Supported Resolutions (Video input):** 2160p, 1440p, 1080p, 1080i, 720p, 576p, 480p, 480i
- **Video Format:** NV12, YUY2, MJPEG
- **Dimension:** (W x D x H): 112.5 x 66.1 x 20.9 mm (4.43 x 2.6 x 0.82 in)
- **Weight:** 85 g (3 oz)

Supported AVerMedia Software:

- AVerMedia Assist Central Pro
- AVerMedia Streaming Center (Windows only)
- Firmware update tool

What's in the box :

- StreamLine MINI+ (GC311G2)
- Type C to Type A Cable
- Quick Start Guide

System Requirements:

Windows® 10 / 11 x64 or later

- **Desktop:** Intel® Core™ i5-6XXX / AMD Ryzen™ 3 XXX or above + NVIDIA® GeForce® GTX 1060 / AMD RX5700 or above
- **Laptop:** Intel® Core™ i7-7700HQ + NVIDIA® GeForce® GTX 1050Ti or above
- 4 GB RAM (8 GB recommended)

macOS 13 / 14 or later

- Apple M1 or 3.6 GHz quad-core Intel Core i7
- Apple M1 or Radeon Pro 555 with 2 GB of VRAM
- 16 GB of 2400 MHz DDR4 memory

iPadOS 17 or later (Type-C port)

Package Dimensions:

- **Single Box (L x H x D):** 173.2 x 118 x 67.1 mm (6.82 x 4.65 x 2.64 in.)
- **Carton (L x W x H):** 36.5 x 24.9 x 38.2 cm (14.37 x 9.8 x 15.03 in)

Shipping Weight:

- **Single Box :** 252.8 g (0.56 lbs.)
- **Carton :** 5.714 Kg (12.60 lbs.) (20 pcs per carton)

EAN (WW)	4711289505730	EAN (JP)	4711289505761
UPC (WW)	850070892292		

- Specifications are subject to change without prior notice.
- Please visit the AVerMedia official website at www.avermedia.com for the latest information.