

US 2-PIN POWER SUPPLY, 9W



TECHNICAL DATA

GENERAL

Input voltage	100 - 240 VAC
Input frequency	50/60 Hz
Input current	0.45 A
Output voltage	9 VDC
Output current	1.0 A
Input connector	US (Type A)
Output connector	2-PIN, with cord end terminals

ADDITIONAL

Input voltage absolute maximum	90 - 262 VAC
Input frequency absolute maximum	47 - 63 Hz
Inrush current	40 A
Output voltage absolute maximum	8.55 - 9.45 VDC
Short circuit protection	✓
HIPOT (dielectric withstand test)	Primary to Secondary: 3000 VAC
MTBF	50000 h

Certification

UL 60950-1
CSA C22.2 No. 60950-1-07
47 CFR FCC part 15 subpart B, 10-1-2016
ANSI C63.4:2014
IEC 62321-7-1:2015, IEC 62321-6:2015, IEC 62321-5:2013,
IEC 62321-4:2013, IEC 62321:2008 Annex C

