# Poly TC10 Black Touch Controller GSA/TAA (977L6AA)

## Overview

**Meet. Schedule. Join**

The Poly TC10 touch control panel makes meetings more productive and allows users to easily schedule workspaces and conference rooms.

### Easier room scheduling

Meeting spaces are a breeze to schedule with a Zoom-certified scheduling panel. Multi-color LED lights let you know the vacancy status before you approach the door. And the touch screen lets you schedule your next meeting space in seconds.

### Clean and simple installation

Our versatile touch panel is sleek and professional. Mount it on walls or glass or place it on a table with its flexible stand. Adjust the angle for visibility. With a single cable for power and connectivity, it maintains a clean profile.

### Complete call control

Instantly take charge of calls and enjoy seamless access to your favorite cloud video apps on your room's video system. Control of your video calls with ease and share content with a tap.

# Features

### Useful inside or outside any room

The incredible versatility enables it to be used outside the room for scheduling, or inside the room as a video and room controller.

### Large, clear display

The TC10 offers a clear, high-resolution 10” touch display that makes its intuitive controls easy to find and use.

### Sleek design

The TC10 offers a uniquely tidy, professional-looking setup, thanks to its sleek design and convenient single cable for both power and connectivity.

### Certified for Zoom

Schedule and conduct Zoom meetings with ease via seamless, Zoom-certified integration with the app.

### Certified for Microsoft Teams

Deploy as a controller for Microsoft Teams on Android when paired to a Poly video system or install outside the room as a Microsoft Teams Panel for scheduling.

# Specifications

| | |
|---|---|
| **Display size (diagonal)** | 25.7 cm (10.1") |
| **Display size (diagonal)** | 10.1" |
| **Panel technology** | IPS |
| **Dimensions (W x D x H)** | 260 x 184 x 64 mm |
| **Dimensions (W x D x H)** | 10.25 x 7.25 x 2.5 in |
| **Weight** | 1.27 kg |
| **Weight** | 2.79 lb |
| **Ports** | 1 RJ-45 |
| **Package dimensions (W x D x H)** | 190 x 210 x 55 mm |
| **Package weight** | 300 g |
| **Special features** | Air Quality Sensor; Proximity sensor; Scheduler; Wall mountable; Standalone mode |
| **UPC number** | (ABA) 197961074093; (AC3) 198122592135 |
| **Manufacturer Warranty** | Poly standard one-year limited warranty |
| **What's in the box** | Poly TC10; Wall mount kit; Table stand; Mounting hardware; RJ-45 cable; Quick start QR code; Warranty card; Poly Lens coaster |

## Additional specifications

| | |
|---|---|
| **Aspect ratio** | 16:10 |
| **Brightness** | 300 nits |
| **Cartons per layer** | 5 |
| **Cartons per pallet** | 35 |
| **Certified collaboration software** | Zoom |
| **Contrast ratio** | 1000:1 |
| **Horizontal viewing angle** | 75° |
| **Interoperability** | Support for native 3rd party applications includes: Zoom Rooms, 8x8, BlueJeans, GoToRoom, Tencent, RingCentral, DialPad and others (when paired to a Poly Video OS system); Integration with Extron (environmental controls) |
| **Management Software** | Poly Lens; Device Management Service[1] |
| **Master carton dimension (imperial)** | 5.02 lb |
| **Master carton dimension (metric)** | 40 x 60 x 28.8 cm |
| **Master carton weight (metric)** | 2.28 kg |
| **Multiple order quantity** | 4 |
| **Native resolution** | WXGA (1280 x 800) |
| **Non-Operating Humidity Range** | 5 to 95% |
| **Non-operating temperature - Celsius** | -20 to 60 °C |
| **Non-operating temperature - fahrenheit** | -4 to 158 °F |
| **Operating altitude** | 3,048 m |
| **Operating altitude** | 10,000 ft |
| **Operating humidity range** | 15 to 80% |
| **Operating temperature range** | 0 to 40 °C |
| **Operating temperature range** | 32 to 104 °F |
| **Package dimensions (W x D x H)** | 7.48 x 8.26 x 2.16 in |
| **Package weight** | 0.66 lb |
| **Pallet (layers)** | 7 |
| **Pallet dimensions** | 47.24 x 39.37 x 84.68 in |
| **Pallet dimensions (W x D x H)** | 120 x 100 x 215.1 cm |
| **Pallet weight** | 787.05 lb |
| **Pallet weight** | 357 kg |
| **Physical security** | Standard Kensington lock slot |

| | |
|---|---|
| **Power** | Power over Ethernet (PoE), compatible with IEEE 802.3at class 0 |
| **Products per pallet** | 140 |
| **Products per pallet layer** | 20 |
| **UNSPSC code** | 45111902 |
| **Vertical viewing angle** | 75° |

---

*[1] Requires downloadable software on Poly.com/lens. Host PC requires Windows 10 or higher.*

---

# Services

## Communication & Collaboration

★ : Recommended

### Poly Support Services

| | |
|---|---|
| 3 Year Poly+ TC10 | **P37760312 ★** |
| 1 Year Partner Poly+ Onsite TC10 | P37760158 |
| 1 Year Partner Poly+ TC10 | P37760160 |
| 1 Year Poly Elite Custom TC10 for Citi use only | E37760650 |
| 1 Year Poly Elite FRURAD TC10 For Commercial use | U99P0PV |
| 1 Year Poly Elite FRURAD TC10 Government Agency Use only | U99NTPV |
| 1 Year Poly Elite Onsite FRURAD TC10 For Commercial use | U99P1PV |
| 1 Year Poly Elite Onsite FRURAD TC10 Government Agency Use only | U99NVPV |
| 1 Year Poly Elite Onsite TC10 | E37760114 |
| 1 Year Poly Elite TC10 | E37760112 |
| 1 Year Poly+ FRURAD TC10 For Commercial use | U99NWPV |
| 1 Year Poly+ FRURAD TC10 Government Agency Use only | U99NNPV |
| 1 Year Poly+ Onsite FRURAD TC10 For Commercial use | U99NXPV |
| 1 Year Poly+ Onsite FRURAD TC10 Government Agency Use only | U99NQPV |
| 1 Year Poly+ Onsite TC10 | P37760114 |
| 1 Year Poly+ TC10 | P37760112 |
| 1 Year extension of 5yr HW Replacement TC10 with advanced part replacement HSP Only | D37760DS1 |
| 3 Year Partner Poly+ Onsite TC10 | P37760358 |
| 3 Year Partner Poly+ TC10 | P37760362 |
| 3 Year Poly Elite Onsite TC10 Service | U86S5PV |
| 3 Year Poly Elite TC10 | E37760312 |
| 3 Year Poly+ FRURAD TC10 For Commercial use | U99NYPV |
| 3 Year Poly+ FRURAD TC10 Government Agency Use only | U99NRPV |
| 3 Year Poly+ Onsite FRURAD TC10 For Commercial use | U99NZPV |
| 3 Year Poly+ Onsite FRURAD TC10 Government Agency Use only | U99NSPV |
| 3 Year Poly+ Onsite TC10 | P37760314 |
| 5 Year Next Business Day HW Replacement TC10 HSP Only | D37760DS5 |
| Service Reactivtion Fee TC10 for product less than one year out of support coverage | R37760801 |
| Service Reactivtion Fee TC10 for product more than one year out of support coverage | R37760802 |

| | |
|---|---|
| Upgrade embedded 1yr Poly+ to 1yr Poly Elite TC10 | E37760912 |
| Upgrade embedded 1yr Poly+ to 1yr Poly+ Onsite TC10 | P37760102 |
| Upgrade embedded 1yr Poly+ to 3yr Partner Poly+ Onsite TC10 | P37760788 |
| Upgrade embedded 1yr Poly+ to 3yr Partner Poly+ TC10 | P37760351 |
| Upgrade embedded 1yr Poly+ to 3yr Poly+ Onsite TC10 | P37760309 |
| Upgrade embedded 1yr Poly+ to 3yr Poly+ TC10 | P37760103 |
| Upgrade embedded 3yr Partner Poly+ to 3yr Partner Poly+ Onsite TC10 | P37760555 |
| Upgrade embedded 3yr Partner Poly+ to 3yr Poly+ Onsite TC10 | P37760444 |
| Upgrade embedded 3yr Partner Poly+ to 3yr Poly+ TC10 | P37760333 |

## Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Sep 11, 2025 10:59 AM UTC+0000