



## QSW-L3208-2C6T

Management Type	Lite Managed
Number of Ports	8
10GbE BASE-T (RJ45)	6 10G/5G/2.5G/1G/100M
10GbE SFP+/RJ45 Combo Ports	2 Note: The 10GbE SFP+ ports are backward compatible with 1GbE SFP; the RJ45 (copper) combo port supports up to five speeds (10G/5G/2.5G/1G/100M).
Power Supply Description	Adapter
Max. Power Consumption	36W
Input Power Type	DC
Input Voltage Range	12V/3A
MAC Address Table	16K
Total Non-Blocking Throughput	80Gbps
Switching Capacity	160Gbps
Management Interface	Web
Console	RJ45
Energy Efficient Ethernet (IEEE 802.3az compliant)	Yes
Fan	System: 4 x 4 cm (12V)

Supported Standards	IEEE 802.3 Ethernet IEEE 802.3u 100BASE-T IEEE 802.3ab 1000BASE-T IEEE 802.3bz 2.5G/5GBASE-T IEEE 802.3z 1000BASE-SX/LX IEEE 802.3an 10GBASE-T IEEE 802.3ae 10G Fiber IEEE 802.3x Full-Duplex Flow Control IEEE 802.1Q VLAN Tagging IEEE 802.3ad LACP IEEE 802.1AB LLDP IEEE 802.1p Class of Service IEEE 802.3az EEE
Form Factor	Desktop
LED Indicators	Per Port: Speed/Link/Activity Per System: Power/Loop/Fan
Buttons	Reset button
Dimensions (HxWxD)	44 x 210 x 160 mm
Weight (Net)	1.29 kg
Weight (Gross)	2.61 kg
Operating Temperature	0°C to 40°C (32°F to 104°F)
Relative Humidity	0~90% Non-condensing
Certifications	CE, UKCA, FCC, IC, VCCI, RCM, BSMI, LVD, KC
Electromagnetic Compliance	CLASS A
Jumbo Frames	12K
Warranty	2 Years

Note: QNAP reserves the right to replace partial parts or accessories if the original is no longer available from its manufacturer/supplier. Any replacement would be fully tested and verified to meet strict compatibility and stability guidelines and will deliver identical performance to the original.

Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.