



# Firebox T125

Includes IntelligentAV, 4x 1Gb and 1x 2.5Gb ports, with optional Wi-Fi 7 for smart, space-saving network protection



## High-Speed Security, Especially Designed for Remote Sites

Engineered for today's agile workforces, the T125 combines advanced threat protection with SD-WAN compatibility, making it ideal for small sites, branch offices, and remote locations. It offers enterprise-level networking in a compact design, equipped with dual-band SMA antennas for wireless flexibility and 2.5 Gbps-capable interfaces for high-speed connectivity. With all logging and reporting features included at no additional cost, users gain access to over 100 dashboards and reports, including PCI and HIPAA standards.

*We use WatchGuard firewalls at multiple locations. These models vary from small to large but we use the full security suite at all sites. These firewalls are easy to configure but offer exception value in the security elements that the full suite adds. This all comes at a cost point much lower than the competition.*

~Verified User


### Firebox T125/T125-W Technical Specifications

| Throughput <sup>1</sup>        |   |
|--------------------------------|---|
| UTM (full scan) <sup>2</sup>   | 510 Mbps  |
| Firewall (IMIX)                | 660 Mbps  |
| VPN (IMIX)                     | 480 Mbps  |
| HTTPS (IPS enabled, full scan) | 270 Mbps  |
| Antivirus                      | 880 Mbps  |
| IPS (full scan)                | 725 Mbps  |
| Firewall (UDP 1518)            | 2.28 Gbps   |
| VPN (UDP 1518)                 | 1.44 Gbps   |
| Capacity                       |   |
| Network Interfaces             | 1 x 2.5 GbE, 4 x 1 GbE  |
| I/O interfaces                 | 1 Serial/2 USB-A 3.2  |
| Concurrent connections         | 3,850,000   |
| Concurrent connections (proxy) | 125,000   |
| New connections per second     | 26,500  |
| VLANs                          | Unrestricted  |
| WSM licenses (incl)            | 0   |
| EDR Core Sensors included      | 5   |
| VPN Tunnels                    |   |
| Branch Office VPN              | 10  |
| Mobile VPN                     | 10  |
| Security Features              |   |
| Firewall                       | Stateful packet inspection, TLS decryption, proxy firewall  |
| Application proxies            | HTTP, HTTPS, FTP, DNS, TCP/UDP, POP3S, SMTPS, IMAPS, and Explicit Proxy<br>IMAPS and Explicit Proxy |
| Threat protection              | DoS attacks, fragmented & malformed packets<br>blended threats                                      |
| Filtering options              | Browser Safe Search, Google for Business  |
| VPN                            |   |
| Site to Site VPN               | IKEv2, IPSec, Policy and Route Based Tunnels, TLS hub and spoke                                     |
| Remote Access VPN              | IKEv2, IPSec, L2TP, TLS   |
| Visibility                     |   |
| Logging and notifications      | WatchGuard Cloud & Dimension, Syslog, SNMP v2/v3  |
| Reporting                      | WatchGuard Cloud includes over 100 pre-defined reports, executive summary, and visibility tools     |

**Firebox T125/  
T125-W**

**Technical Specifications**

|  |   |   |
|--|---|---|
| <b>Certifications</b>                    |   |   |
| Security                                 | Pending: CC, FIPS 140-2   |   |
| Safety                                   | NRTL/CB   |   |
| Network                                  | IPv6 Ready Gold (routing)   |   |
| Hazardous substance control              | WEEE, RoHS, REACH   |   |
| <b>Networking</b>                        |   |   |
| SD-WAN                                   | Multi-wan failover, dynamic path selection, jitter/loss/latency measurement |   |
| Dynamic Routing                          | RIP, OSPF, BGP  |   |
| High Availability                        | Active/passive, active/active   |   |
| QoS                                      | 802.1Q, DSCP, IP Precedence   |   |
| Traffic Management                       | By policy or application  |   |
| IP address assignment                    | Static, DHCP (server, client, relay), PPPoE, DynDNS                         |   |
| NAT                                      | Static, dynamic, 1:1, IPSec traversal, policy-based                         |   |
| Link aggregation                         | 802.3ad dynamic, static, active/backup                                      |   |
| <b>Physical and Power Specifications</b> |   |   |
| Product Dimensions                       | 9" x 8.25" x 1.7" (230x210x44mm)  |   |
| Shipping Dimension                       | 12.2"x 9.8"x 3.9" (311x250x98 mm)   |   |
| Product Weight                           | T125: 2.92 lbs (2.07 kg)<br>T125-W: 3.11 lbs (2.17 kg)                      |   |
| Shipping Weight                          | T125: 4.52 lbs (2.05 kg)<br>T125-W: 4.80 lbs (2.18 kg)                      |   |
| Power Consumption                        | 20 Watts (Max)  |   |
| Power                                    | 100-240 VAC Autosensing   |   |
| <b>Environment</b>                       | <b>Operating</b>  | <b>Storage</b>                                |
| Temperature                              | 32° F to 104° F<br>0° C to 40° C  | -40° F to 158° F<br>-40° C to 70° C           |
| Relative Humidity                        | 10% to 85%<br>non-condensing  | 10% to 85%<br>non-condensing                  |
| Altitude                                 | 0 to 9,843 ft at 95° F<br>(3,000 m at 35° C)                                | 0 to 15,000 ft at 95° F<br>(4,570 m at 35° C) |
| MTBF                                     | 846,422 hours   |   |



**Strong Security at Every Layer**

Uniquely architected to be the industry's smartest, fastest, and most effective network security products, WatchGuard solutions deliver in-depth defenses against advanced malware, ransomware, botnets, trojans, viruses, drive-by downloads, data loss, phishing, and much more.

<sup>1</sup> Throughput rates are determined using multiple flows through multiple ports and will vary depending on the environment and configuration. Max firewall throughput tested via direct connection using 1518-byte UDP frames based on RFC 2544 methodology. All testing performed on Fireware version 2025.1.

<sup>2</sup> UTM throughput is measured using HTTP traffic with AV, IPS, and Application Control enabled, and does not account for all security services available on the appliance.

Contact your WatchGuard reseller or call WatchGuard directly (1.800.734.9905) for help determining the right model for your network. Visit [www.watchguard.com/sizing](http://www.watchguard.com/sizing) to access the online Product Sizing Tool.

For details, talk to your authorized WatchGuard reseller or visit [www.watchguard.com](http://www.watchguard.com).

|                                    | Standard Support  | Basic Security    | Total Security |
|------------------------------------|-------------------|-------------------|----------------|
| Stateful Firewall                  | ✓                 | ✓                 | ✓              |
| VPN                                | ✓                 | ✓                 | ✓              |
| SD-WAN                             | ✓                 | ✓                 | ✓              |
| Access Portal*                     | ✓                 | ✓                 | ✓              |
| Intrusion Prevention Service (IPS) |                   | ✓                 | ✓              |
| Application Control                |                   | ✓                 | ✓              |
| WebBlocker                         |                   | ✓                 | ✓              |
| spamBlocker                        |                   | ✓                 | ✓              |
| Gateway AntiVirus                  |                   | ✓                 | ✓              |
| Reputation Enabled Defense         |                   | ✓                 | ✓              |
| Network Discovery                  |                   | ✓                 | ✓              |
| APT Blocker                        |                   |                   | ✓              |
| DNSWatch                           |                   |                   | ✓              |
| IntelligentAV**                    |                   |                   | ✓              |
| ThreatSync (XDR)                   |                   |                   | ✓              |
| EDR Core                           |                   |                   | ✓              |
| WatchGuard Cloud                   |                   |                   |                |
| Log Data Retention                 |                   | 90 Days           | 365 Days       |
| Report Data Retention              |                   | 1 Day             | 30 Days        |
| Support                            | Standard (24 x 7) | Standard (24 x 7) | Gold (24 x 7)  |

\*Not available on Firebox T115-W, T20/T20-W, T25/T25-W, or T35-R. Total Security Suite required for M270, M370, M470, M570, M670, FireboxV and Firebox Cloud.  
\*\*Not available on Firebox T115-W, T20/T20-W, T25/T25-W, or T35-R.