

Firebox T125

Includes IntelligentAV, 4x 1Gb and 1x 2.5Gb ports, with optional Wi-Fi 7 for smart, space-saving network protection



High-Speed Security, Especially Designed for Remote Sites

Engineered for today's agile workforces, the T125 combines advanced threat protection with SD-WAN compatibility, making it ideal for small sites, branch offices, and remote locations. It offers enterprise-level networking in a compact design, equipped with dual-band SMA antennas for wireless flexibility and 2.5 Gbps-capable interfaces for high-speed connectivity. With all logging and reporting features included at no additional cost, users gain access to over 100 dashboards and reports, including PCI and HIPAA standards.

We use WatchGuard firewalls at multiple locations. These models vary from small to large but we use the full security suite at all sites. These firewalls are easy to configure but offer exception value in the security elements that the full suite adds. This all comes at a cost point much lower than the competition.

~Verified User

Firebox T125/T125-W

Technical Specifications

Throughput ¹	
UTM (full scan) ²	510 Mbps
Firewall (IMIX)	660 Mbps
VPN (IMIX)	480 Mbps
HTTPS (IPS enabled, full scan)	270 Mbps
Antivirus	880 Mbps
IPS (full scan)	725 Mbps
Firewall (UDP 1518)	2.28 Gbps
VPN (UDP 1518)	1.44 Gbps
Capacity	
Network Interfaces	1 x 2.5 GbE, 4 x 1 GbE
I/O interfaces	1 Serial/2 USB-A 3.2
Concurrent connections	3,850,000
Concurrent connections (proxy)	125,000
New connections per second	26,500
VLANs	Unrestricted
WSM licenses (incl)	0
EDR Core Sensors included	5
VPN Tunnels	
Branch Office VPN	10
Mobile VPN	10
Security Features	
Firewall	Stateful packet inspection, TLS decryption, proxy firewall
Application proxies	HTTP, HTTPS, FTP, DNS, TCP/UDP, POP3S, SMTPS, IMAPS, and Explicit Proxy IMAPS and Explicit Proxy
Threat protection	DoS attacks, fragmented & malformed packets blended threats
Filtering options	Browser Safe Search, Google for Business
VPN	
Site to Site VPN	IKEv2, IPSec, Policy and Route Based Tunnels, TLS hub and spoke
Remote Access VPN	IKEv2, IPSec, L2TP, TLS
Visibility	
Logging and notifications	WatchGuard Cloud & Dimension, Syslog, SNMP v2/v3
Reporting	WatchGuard Cloud includes over 100 pre-defined reports, executive summary, and visibility tools

Firebox T125/ T125-W

Technical Specifications

Certifications		
Security	Pending: CC, FIPS 140-2	
Safety	NRTL/CB	
Network	IPv6 Ready Gold (routing)	
Hazardous substance control	WEEE, RoHS, REACH	
Networking		
SD-WAN	Multi-wan failover, dynamic path selection, jitter/loss/latency measurement	
Dynamic Routing	RIP, OSPF, BGP	
High Availability	Active/passive, active/active	
QoS	802.1Q, DSCP, IP Precedence	
Traffic Management	By policy or application	
IP address assignment	Static, DHCP (server, client, relay), PPPoE, DynDNS	
NAT	Static, dynamic, 1:1, IPSec traversal, policy-based	
Link aggregation	802.3ad dynamic, static, active/backup	
Physical and Power Specifications		
Product Dimensions	9" x 8.25" x 1.7" (230x210x44mm)	
Shipping Dimension	12.2"x 9.8"x 3.9" (311x250x98 mm)	
Product Weight	T125: 2.92 lbs (2.07 kg)	
	T125-W: 3.11 lbs (2.17 kg)	
Shipping Weight	T125: 4.52 lbs (2.05 kg)	
	T125-W: 4.80 lbs (2.18 kg)	
Power Consumption	20 Watts (Max)	
Power	100-240 VAC Autosensing	
Environment	Operating	Storage
Temperature	32° F to 104° F	-40° F to 158° F
	0° C to 40° C	-40° C to 70° C
Relative Humidity	10% to 85% non-condensing	10% to 85% non-condensing
Altitude	0 to 9,843 ft at 95° F (3,000 m at 35° C)	0 to 15,000 ft at 95° F (4,570 m at 35° C)
MTBF	846,422 hours	

Strong Security at Every Layer


Uniquely architected to be the industry's smartest, fastest, and most effective network security products, WatchGuard solutions deliver in-depth defenses against advanced malware, ransomware, botnets, trojans, viruses, drive-by downloads, data loss, phishing, and much more.

1 Throughput rates are determined using multiple flows through multiple ports and will vary depending on the environment and configuration. Max firewall throughput tested via direct connection using 1518-byte UDP frames based on RFC 2544 methodology. All testing performed on Firewall version 2025.1.

2 UTM throughput is measured using HTTP traffic with AV, IPS, and Application Control enabled, and does not account for all security services available on the appliance.

Contact your WatchGuard reseller or call WatchGuard directly (1.800.734.9905) for help determining the right model for your network. Visit www.watchguard.com/sizing to access the online Product Sizing Tool.

For details, talk to your authorized WatchGuard reseller or visit www.watchguard.com.



	Standard Support	Basic Security	Total Security
Stateful Firewall	✓	✓	✓
VPN	✓	✓	✓
SD-WAN	✓	✓	✓
Access Portal*	✓	✓	✓
Intrusion Prevention Service (IPS)		✓	✓
Application Control		✓	✓
WebBlocker		✓	✓
spamBlocker		✓	✓
Gateway AntiVirus		✓	✓
Reputation Enabled Defense		✓	✓
Network Discovery		✓	✓
APT Blocker			✓
DNSWatch			✓
IntelligentAV**			✓
ThreatSync (XDR)			✓
EDR Core			✓
WatchGuard Cloud			
Log Data Retention		90 Days	365 Days
Report Data Retention		1 Day	30 Days
Support	Standard (24 x 7)	Standard (24 x 7)	Gold (24 x 7)

*Not available on Firebox T115-W, T20/T20-W, T25/T25-W, or T35-R. Total Security Suite required for M270, M370, M470, M570, M670, FireboxV and Firebox Cloud.

**Not available on Firebox T115-W, T20/T20-W, T25/T25-W, or T35-R.