DATASHEET

Firebox T185



Available with built-in SFP+ interface, 2.5Gb ports, 4GB RAM, and up to 1.83 Gbps UTM for high-demand sites. Plus, faster BOVPN performance.

Enterprise-Grade Security for Branch Offices and Retail Environments

The Firebox T185 is the most powerful tabletop firewall in the Firebox T Series, designed to handle heavier traffic loads in demanding environments. It features SFP+ fiber, providing flexible, high-performance connectivity tailored to your network needs. Plus, it includes a highly reliable built-in power supply and a Kensington Lock to ensure the device's physical security.

"We use WatchGuard firewalls at multiple locations. These models vary from small to large but we use the full security suite at all sites. These firewalls are easy to configure but offer exception value in the security elements that the full suite adds. This all comes at a cost point much lower than the competition."

~Verified User

Firebox T185	Technical Specifications
Throughput [1]	
UTM (full scan)[2]	1.83 Gbps
Firewall (IMIX)	5.70 Gbps
VPN (IMIX)	1.14 Gbps
HTTPS (IPS enabled, full scan)	1.00 Gbps
Antivirus	2.80 Gbps
IPS (full scan)	2.40 Gbps
Firewall (UDP 1518)	7.90 Gbps
VPN (UDP 1518)	2.20 Gbps
Capacity	
Interfaces	4 x 1 GbE, 4 x 2.5 GbE, 1 x SFP/SFP+
I/O interfaces	1 Serial/2 USB-A 3.2
Concurrent connections	3,850,000
Concurrent connections (proxy)	130,000
New connections per second	26,500
VLANs	Unlimited
WSM licenses (incl)	4
EDR Core Sensors included	50
VPN Tunnels	
Branch Office VPN	100
Mobile VPN	100
Security Features	
Firewall	Stateful packet inspection, TLS decryption, proxy firewall
Application proxies	HTTP, HTTPS, FTP, DNS, TCP/UDP, POP3S, SMTPS, IMAPS and Explicit Proxy
Threat Protection	DoS attacks, fragmented & malformed packets blended threats
Filtering Options	Browser Safe Search, Google for Business
VPN	
Site to Site VPN	IKEv2, IPSec, Policy and Route Based Tunnels, TLS hub and spoke
Remote Access VPN	IKEv2, IPSec, L2TP, TLS
Visibility	
Logging and notifications	WatchGuard Cloud & Dimension, Syslog, SNMP v2/v3
Reporting	WatchGuard Cloud includes over 100 pre-defined reports, executive summary and visibility tools


DATASHEET

Firebox T185 Technical Specifications

Certifications	
Security	Pending: CC, FIPS 140-3
Safety	NRTL/CB
Network	IPv6 Ready Gold (routing)
Hazardous substance control	WEEE, RoHS, REACH
Networking	
SD-WAN	Multi-wan failover, dynamic path selection, jitter/loss/latency measurement
Dynamic Routing	RIP, OSPF, BGP
High Availability	Active/passive, active/active
QoS	802.1Q, DSCP, IP Precedence
Traffic Management	By policy or application
IP address assignment	Static, DHCP (server, client, relay), PPPoE, DynDNS
NAT	Static, dynamic, 1:1, IPSec traversal, policy-based
Link aggregation	802.3ad dynamic, static, active/backup
Physical and Power Specifications	
Product Dimensions	13" x 8.35" x 1.7" (330 x 212 x 44 mm)
Shipping Dimension	17.0"x 12.0"x 5.3" (435 x 306 x 135 mm)
Product Weight	5.33 lbs (2.43 kg)
Shipping Weight	7.26 lbs (3.30 kg)
Power Consumption	25 Watts (no PoE) 90 Watts (PoE)
Power	100-240 VAC Autosensing

Environment	Operating	Storage
Temperature	32° F to 104° F 0° C to 40° C	-40° F to 158° F -40° C to 70° C
Relative Humidity	10% to 85% non-condensing	10% to 85% non-condensing
Altitude	0 to 9,843 ft at 95° F (3,000 m at 35° C)	0 to 15,000 ft at 95° F (4,570 m at 35° C)
MTBF	172,411 hours	





Strong Security at Every Layer

Uniquely architected to be the industry's smartest, fastest, and most effective network security products, WatchGuard solutions deliver in-depth defenses again advanced malware, ransomware, botnets, trojans, viruses, drive-by downloads, data loss, phishing, and much more.

1 Throughput rates are determined using multiple flows through multiple ports and will vary depending on the environment and configuration. Max firewall throughput tested via direct connection using 1518-byte UDP frames based on RFC 2544 methodology. All testing performed on Fireware version 2025.1.

2 UTM throughput is measured using HTTP traffic with AV, IPS, and Application Control enabled, and does not account for all security services available on the appliance.

Contact your WatchGuard reseller or call WatchGuard directly (1.800.734.9905) for help determining the right model for your network. Visit www.watchguard.com/sizing to access the online Product Sizing Tool.

For details, talk to your authorized WatchGuard reseller or visit **www.watchguard.com.**

	Standard Support	Basic Security	Total Security
Stateful Firewall	✓	✓	✓
VPN	✓	✓	✓
SD-WAN	✓	✓	✓
Access Portal*	✓	✓	✓
Intrusion Prevention Service (IPS)		✓	✓
Application Control		✓	✓
WebBlocker		✓	✓
spamBlocker		✓	✓
Gateway AntiVirus		✓	✓
Reputation Enabled Defense		✓	✓
Network Discovery		✓	✓
APT Blocker			✓
DNSWatch			✓
IntelligentAV**			✓
ThreatSync (XDR)			✓
EDR Core			✓
WatchGuard Cloud			
Log Data Retention		90 Days	365 Days
Report Data Retention		1 Day	30 Days
Support	Standard (24 x 7)	Standard (24 x 7)	Gold (24 x 7)

*Not available on Firebox T115-W, T20/T20-W, T25/T25-W, or T35-R. Total Security Suite required for M270, M370, M470, M570, M670, FireboxV and Firebox Cloud.
**Not available on Firebox T115-W, T20/T20-W, T25/T25-W, or T35-R.

U.S. SALES +1.800.734.9905 INTERNATIONAL SALES +1.206.613.0895 WEB www.watchguard.com WatchGuard Technologies, Inc.

No express or implied warranties are provided for herein. All specifications are subject to change and expected future products, features or functionality will be provided on an if and when available basis. ©2025 WatchGuard Technologies, Inc. All rights reserved. WatchGuard, the WatchGuard logo, Firebox, DNSWatch, IntelligentAV are trademarks or registered trademarks of WatchGuard Technologies, Inc. in the United States and/or other countries. All other tradenames are the property of their respective owners. Part No. WGCE67855_080425