



## SPECIFICATIONS

|                                    |                                                 |
|------------------------------------|-------------------------------------------------|
| <b>Radiator Size</b>               | 360 mm                                          |
| <b>Radiator Dimensions (WxDxH)</b> | 394 x 119.6 x 27mm / 15.51 x 4.69 x 1.06 inches |
| <b>Radiator Material</b>           | Aluminum                                        |
| <b>Water Cooling Tube Material</b> | EPDM                                            |
| <b>Number of Fans</b>              | 3                                               |
| <b>Fan Dimensions (WxDxH)</b>      | 120 x 120 x 25 mm / 4.7 x 4.7 x 0.98 inches     |
| <b>Fan Air Flow</b>                | 62.6 CFM                                        |
| <b>Fan Bearing</b>                 | Rifle Bearing                                   |
| <b>Fan Life Expectancy</b>         | 40,000 hrs@40°C                                 |
| <b>Fan Rated Current</b>           | 0.15A(Max:0.18A)                                |
| <b>Fan Power Consumption</b>       | 1.8W(Max:2.16W)                                 |
| <b>PWM Mode</b>                    | Yes                                             |
| <b>Cable Length (PWM Cable)</b>    | 450 mm; 17.71 inches                            |
| <b>Fan Connector</b>               | 5V ARGB 3-PIN Header                            |
| <b>Block Lighting</b>              | ARGB GEN2                                       |
| <b>Fan Lighting</b>                | ARGB Gen2                                       |
| <b>Pump Life Expectancy</b>        | 25,000 hours in typical use                     |
| <b>Pump Noise Level</b>            | 20 dBA (avg.)                                   |
| <b>Pump Rated Current</b>          | 0.24A                                           |
| <b>Pump Power Consumption</b>      | 2.88W                                           |
| <b>Pump Speed</b>                  | 3800 RPM ± 10%                                  |
| <b>Pump Connector</b>              | 3-PIN Header<br>5V ARGB 3-PIN Header ( Female ) |
| <b>Cold Plate Material</b>         | Copper                                          |
| <b>Block Dimensions (WxDxH)</b>    | 70.9 x 69.3 x 56.98 mm                          |
| <b>Intel Socket Support</b>        | LGA 1700 / 1851                                 |
| <b>AMD Socket Support</b>          | AM5 / AM4                                       |
| <b>Accessories</b>                 | Thermal paste x 1<br>Screws x 12                |