



SPECIFICATIONS

Radiator Size	240 mm
Radiator Dimensions (WxDxH)	277 x 119.6 x 27.2mm / 10.90 x 4.69 x 1.06 inches
Radiator Material	Aluminum
Water Cooling Tube Material	EPDM
Number of Fans	2
Fan Dimensions (WxDxH)	120 x 120 x 25 mm / 4.7 x 4.7 x 0.98 inches
Fan Air Flow	62.6 CFM
Fan Bearing	Rifle Bearing
Fan Life Expectancy	40,000 hrs@40°C
Fan Rated Current	0.15A(Max:0.18A)
Fan Power Consumption	1.8W(Max:2.16W)
PWM Mode	Yes
Cable Length (PWM Cable)	450 mm; 17.71 inches
Fan Connector	5V ARGB 3-PIN Header
Block Lighting	ARGB GEN2
Fan Lighting	ARGB Gen2
Pump Life Expectancy	25,000 hours in typical use
Pump Noise Level	20 dBA (avg.)
Pump Rated Current	0.24A
Pump Power Consumption	2.88W
Pump Speed	3800 RPM ± 10%
Pump Connector	3-PIN Header 5V ARGB 3-PIN Header (Female)
Cold Plate Material	Copper
Block Dimensions (WxDxH)	70.9 x 69.3 x 56.98 mm
Intel Socket Support	LGA 1700 / 1851
AMD Socket Support	AM5 / AM4
Accessories	Thermal paste x 1 Screws x 8