



SPECIFICATIONS

Radiator Size	360 mm
Radiator Dimensions (WxDxH)	394 x 119.6 x 27.2mm / 15.51 x 4.69 x 1.06 inches
Radiator Material	Aluminum
Water Cooling Tube Material	EPDM
Fan Dimensions (WxDxH)	120 x 120 x 25 mm / 4.7 x 4.7 x 0.98 inches
Fan Air Flow	64.898 CFM
Fan Bearing	Rifle Bearing
Fan Speed	500~2050 ± 150 RPM
Fan Life Expectancy	40,000 hrs@40°C
Fan Rated Current	0.14 A±0.028 A
Fan Power Consumption	1.68W±0.336W
PWM Mode	Yes
Cable Length (PWM Cable)	800±15mm 31.49 inches
Fan Connector	5V ARGB 3-PIN Header
Fan Lighting	ARGB GEN2
Pump Life Expectancy	50,000 hours in typical use 40°C
Pump Noise Level	20 dBA (avg)
Pump Load Current	0.21A±0.042A
Pump Power Consumption	2.52W±0.504W
Pump Speed	3400 RPM ± 340 RPM
Intel Socket Support	LGA 1700 / 1851
AMD Socket Support	AM5 / AM4
Panel Size	2.1"
Panel Type	IPS
Panel Resolution	480 x 480
Panel Brightness	600 nits