



Accessories Guide

TC701

Ultra-rugged mobile computing reimagined for the AI-powered frontline




Table of Contents

Accessories that POWER devices

Cradles

Single-slot ShareCradles	4
Multi-slot ShareCradles Kits	6
Multi-slot ShareCradles	8
Legacy ShareCradle Cups	10
ShareCradle Components	12
Mounting Options for Chargers	13

Batteries

Spare Li-ion Batteries	15
Spare Battery Chargers	16

Power Supplies, Cables, and Adaptors

Power Supply and Cable Matrix	18
Country-Specific AC Line Cords	19

Accessories that PROTECT devices

Soft Goods

Hand Strap, and Screen Protector	21
Soft Holster, Stylus, and Tether	22

Accessories that ENABLE devices

Trigger Handles

Electronic Trigger Handle and Wrist Strap	24
---	----

Headsets

Wired Headsets and Accessories for Workforce Connect	26
Wireless Headsets and Accessories for Voice-Directed Picking	27

Third Party Accessories

RAM Vehicle Docks	29
ProClip Vehicle Cradles	30
Isiris Mounting Solution	32

Cradles

[Single-slot ShareCradles](#)

[Multi-slot ShareCradles Kits](#)

[Multi-slot ShareCradles](#)

[Legacy ShareCradle Cups](#)

[ShareCradle Components](#)

[Mounting Options for Chargers](#)

Single-slot ShareCradles

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
One-Device ShareCradle SKU# CRDCUP-TC7A-IDF 	TC701 Fast-Charging ShareCradle for a Single Device. <ul style="list-style-type: none">• Device with standard battery charges from 0–70% in about 45 minutes.• Connects to charge contacts and USB-C port on the bottom of the device.• Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)
One-Device Ethernet ShareCradle SKU# CRD-TC7A-1SE 	TC701 Ethernet ShareCradle for a Single Device. <ul style="list-style-type: none">• Device with standard battery charges from 0–90% in about 1¾ hours.• Connects to charge contacts and USB-C port on the bottom of the device.• There is an Ethernet Port, and spare USB-C port.• Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)
Two-Device ShareCradle SKU# CRDCUP-TC7A-2D 	TC701 Charge-Only ShareCradle for Two Devices. <ul style="list-style-type: none">• Device with standard battery charges from 0–90% in about 2 hours.• Connects to charge contacts on the bottom of the device.• Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)

Single-slot ShareCradles

[Cradles](#)

[Batteries](#)



[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
<p>One-Device & One-Battery ShareCradle SKU# CRD-TC7A-2SC1B</p> 	<p>TC701 Charge-Only ShareCradle for a Single Device and its Spare Battery.</p> <ul style="list-style-type: none">• Device with standard battery charges from 0–90% in about 2 hours.• Connects to charge contacts on the bottom of the device.• Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)
<p>One-Device & One Battery Ethernet ShareCradle SKU# CRD-TC7A-2SE1B</p> 	<p>TC701 Ethernet ShareCradle for a Single Device and its Spare Battery.</p> <ul style="list-style-type: none">• Device with standard battery charges from 0–90% in about 2 hours.• Connects to charge contacts and USB-C port on the bottom of the device.• There is an Ethernet Port, and spare USB-C port.• Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX ('XX' in SKU to get the right plug style based on region)

Multi-Slot ShareCradles Kits

[Cradles](#)

[Batteries](#)



[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
<p>Five-Device ShareCradle Kit SKU# CRD-TC7A-5SC5DF-1</p> 	<p>TC701 Fast-Charging ShareCradle for Five Devices.</p> <ul style="list-style-type: none"> • Device with standard battery charges from 0–70% in about 45 minutes. • Connects to charge contacts and USB-C port on the bottom of the device. • Includes: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW • Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. • Sold Separately: Country-Specific AC Line Cord (listed later in this document).
<p>Five-Device Ethernet ShareCradle Kit SKU# CRD-TC7A-5SE5D-1</p> 	<p>TC701 Ethernet ShareCradle for Five Devices.</p> <ul style="list-style-type: none"> • Device with standard battery charges from 0–90% in about 1¾ hours. • Connects to charge contacts and USB-C port on the bottom of the device. • There is an Ethernet Port, and spare USB-C port. • Includes: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW • Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. • Sold Separately: Country-Specific AC Line Cord (listed later in this document).

Multi-Slot ShareCradles Kits

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#

Description

Five-Device & Five-Battery ShareCradle Kit

SKU# **CRD-TC7A-5SC5D5B-1**



TC701 Charge-Only ShareCradle for Five Devices and Five Spare Batteries.

- Device with standard battery charges from 0–90% in about 2 hours.
- Connects to charge contacts on the bottom of the device.
- Includes: Power Supply with Attached DC Cable [SKU# PWR-BGA12V150W1WW](#).
- Can be mounted on a standard 19-inch rack system using mounting bracket [SKU# BRKT-SCRD-SMRK-01](#).
- Sold Separately: Country-Specific AC Line Cord (listed later in this document).

10-Device ShareCradle Kit

SKU# **CRD-TC7A-5SC10D-1**



TC701 Charge-Only ShareCradle for 10 Devices.

- Device with standard battery charges from 0–90% in about 2 hours.
- Connects to charge contacts on the bottom of the device.
- Includes: Power Supply with Attached DC Cable [SKU# PWR-BGA12V150W1WW](#).
- Can be mounted on a standard 19-inch rack system using mounting bracket [SKU# BRKT-SCRD-SMRK-01](#).
- Sold Separately: Country-Specific AC Line Cord (listed later in this document).

Multi-Slot ShareCradles

[Cradles](#)

[Batteries](#)



[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
<p>Five-Device ShareCradle SKU# CRD-TC7A-5SC5DF</p> 	<p>TC701 Fast-Charging ShareCradle for Five Devices.</p> <ul style="list-style-type: none"> • Device with standard battery charges from 0–70% in about 45 minutes. • Connects to charge contacts and USB-C port on the bottom of the device. • Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. • Sold Separately: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW, and Country-Specific AC Line Cord (listed later in this document).
<p>Five-Device Ethernet ShareCradle SKU# CRD-TC7A-5SE5D</p> 	<p>TC701 Ethernet ShareCradle for Five Devices.</p> <ul style="list-style-type: none"> • Device with standard battery charges from 0–90% in about 1¾ hours. • Connects to charge contacts and USB-C port on the bottom of the device. • There is an Ethernet Port, and spare USB-C port. • Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. • Sold Separately: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW, and Country-Specific AC Line Cord (listed later in this document).

Multi-Slot ShareCradles

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#2

Description

Five-Device & Five-Battery ShareCradle

SKU# **CRD-TC7A-5SC5D5B**



TC701 Charge-Only ShareCradle for Five Devices and Five Spare Batteries.

- Device with standard battery charges from 0–90% in about 2 hours.
- Connects to charge contacts on the bottom of the device.
- Can be mounted on a standard 19-inch rack system using mounting bracket [SKU# BRKT-SCRD-SMRK-01](#).
- Sold Separately: Power Supply with Attached DC Cable [SKU# PWR-BGA12V150W1WW](#), and Country-Specific AC Line Cord (listed later in this document).

10-Device ShareCradle

SKU# **CRD-TC7A-5SC10D**



TC701 Charge-Only ShareCradle for 10 Devices.

- Device with standard battery charges from 0–90% in about 2 hours.
 - Connects to charge contacts on the bottom of the device.
 - Can be mounted on a standard 19-inch rack system using mounting bracket [SKU# BRKT-SCRD-SMRK-01](#).
 - Sold Separately: Power Supply with Attached DC Cable [SKU# PWR-BGA12V150W1WW](#), and Country-Specific AC Line Cord (listed later in this document).
-

Legacy ShareCradle Cups

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
<p>One-Device Replacement ShareCradle Cup SKU# CRDCUP-NGTC7A-01</p> 	<p>TC701 Replacement Charge-Only Device Cup for One Device</p> <ul style="list-style-type: none"> Enables the use of TC701 devices with Legacy ShareCradles by replacing the existing TC72 / TC77 series device cup. Includes a pre-installed TC701 shim.
<p>Five-Device Replacement ShareCradle Cup SKU# CRDCUP-NGTC7A-05</p> 	<p>TC701 Replacement Charge-Only Device Cup for Five Devices</p> <ul style="list-style-type: none"> A set of five Charge-Only ShareCradle Cups. Enables the use of TC701 devices with Legacy ShareCradles by replacing the existing TC72 / TC77 series device cup. Includes pre-installed TC701 shims.
<p>One-Device Replacement Ethernet ShareCradle Cup SKU# CRDCUP-NGTC7AE-01</p> 	<p>TC701 Replacement Ethernet Device Cup for One Device</p> <ul style="list-style-type: none"> Enables the use of TC701 devices with Legacy ShareCradles by replacing the existing TC72 / TC77 series device cup. Includes a pre-installed TC701 shim.
<p>Five-Device Replacement Ethernet ShareCradle Cup SKU# CRDCUP-NGTC7AE-05</p> 	<p>TC701 Replacement Ethernet Device Cup for Five Devices</p> <ul style="list-style-type: none"> A set of five Ethernet ShareCradle Cups. Enables the use of TC701 devices with Legacy ShareCradles by replacing the existing TC72 / TC77 series device cup. Includes pre-installed TC701 shims.

Legacy ShareCradle Cups

[Cradles](#)

[Batteries](#)


[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
<p>TC701 Shim SKU# SHIM-CRD-TC7A</p> 	<p>TC701 Replacement Shim</p> <ul style="list-style-type: none">• Replaces the TC73 / TC78 shim to make Legacy ShareCradles compatible with TC701 devices.

ShareCradle Components

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
TC701 Holder SKU# HLD-TC7A-01 	TC701 Holder for Devices <ul style="list-style-type: none">Included in all ShareCradles designed for devices.
Ethernet Single-Slot ShareCradle Base SKU# CRD-ETHSNGLEBASE-01 	Ethernet Single-Slot ShareCradle Base <ul style="list-style-type: none">Included in all single-slot Ethernet ShareCradle Configurations.
Fast-Charging ShareCradle Base SKU# CRD-FCBASE-01 	Fast-Charging ShareCradle Base <ul style="list-style-type: none">Included in all multi-slot ShareCradles except for the Ethernet model.
Ethernet ShareCradle Base SKU# CRD-ETHBASE-01 	Ethernet ShareCradle Base <ul style="list-style-type: none">Included in the multi-slot Ethernet ShareCradle configuration.

Mounting Options for Chargers

[Cradles](#)

[Batteries](#)

[Power Supplies,](#)
[Cables and](#)
[Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party](#)
[Accessories](#)

Item/SKU#	Description
Mounting Bracket SKU# BRKT-SCRD-SMRK-01	Use five-slot ShareCradle mounting bracket to attach five- slot TC701 cradles to the wall or mount on a 19-inch server rack. <ul style="list-style-type: none">• Offers cable routing slots and removable tray that stores / conceals power supply.• Adjustable orientations: 25° angle for high-density (multi-slot chargers). Horizontal (single-slot or four-slot spare Li-ion charger).• Four 4-slot spare battery chargers can be mounted as shown with mounting bracket.• Compatible with all multi-slot ShareCradles for TC701.• Use to mount to wall or with standard 19-inch server rack for more density and save space.



Batteries

[Spare Li-ion Batteries](#)

[Spare Battery Chargers](#)

Batteries

Spare Li-ion Batteries

[Cradles](#)

[Batteries](#)



[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description						
<p>Standard Capacity Battery SKU# BTRY-TC5A7A-SC-01</p> 	<p>5000 mAh Standard Capacity Battery with PowerPrecision Plus.</p> <ul style="list-style-type: none"> • Premium-grade battery cells with longer lifecycle and tested to meet rigorous controls and standards. • Obtain advanced battery state of health information including charge level and battery age based on usage patterns. 						
<p>Extended Capacity Battery SKU# BTRY-TC5A7A-EC-01</p> 	<p>7240 mAh Extended Capacity Battery with PowerPrecision Plus.</p> <ul style="list-style-type: none"> • Premium-grade battery cells with longer lifecycle and tested to meet rigorous controls and standards. • Obtain advanced battery state of health information including charge level and battery age based on usage patterns. 						
<p>Wireless Charging Battery SKU# BTRY-TC5A7A-WC-01</p> 	<p>5000 mAh Standard Capacity Battery with Wireless Charging and PowerPrecision Plus.</p> <ul style="list-style-type: none"> • Premium-grade battery cells with longer lifecycle and tested to meet rigorous controls and standards. • Obtain advanced battery state of health information including charge level and battery age based on usage patterns. <table border="1" data-bbox="889 1377 1393 1507"> <thead> <tr> <th colspan="2">Compatibility (Wireless Battery)</th> </tr> </thead> <tbody> <tr> <td>TC701 WAN (Cellular)</td> <td>Yes</td> </tr> <tr> <td>TC701 LAN (WiFi)</td> <td>No</td> </tr> </tbody> </table>	Compatibility (Wireless Battery)		TC701 WAN (Cellular)	Yes	TC701 LAN (WiFi)	No
Compatibility (Wireless Battery)							
TC701 WAN (Cellular)	Yes						
TC701 LAN (WiFi)	No						

Batteries

Spare Battery Charger

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
<p>Spare Battery Charger SKU# CRDCUP-TC5A7A-4B</p> 	<p>Spare Battery Charger to Charge any Four TC701 Li-ion batteries.</p> <ul style="list-style-type: none">• Can be used standalone or up to 4 chargers can be mounted on Mounting Bracket SKU# BRKT-SCRD-SMRK-01.• Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)



Power Supply, Cables, and Adaptors

[Power Supply and Cable Matrix](#)

[Country-Specific AC Line Cords](#)

Power Supply, Cables and Adapters

Power Supply and Cable Matrix

[Cradles](#)

[Batteries](#)


[Power Supplies, Cables and Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party Accessories](#)

SKU#	Description	Notes
PWR-BGA12V150W1WW 	Level VI AC/DC power supply brick. AC Input: 100–240V, 2.5A. DC Output: 12V, 12.5A, 150W.	Sold Separately. To be used with Country-Specific AC Line Cords.
CBL-EC5X-USBC3A-01 	USB-C to USB-C Communications and Charging Cable, 1M Long, Support 3.0 support speed and fast charge.	Sold separately. Used with PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)
PWR-WUA5V45W1US 	USB type C power supply adaptor with United States plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1EU 	USB type C power supply adaptor with European Union plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1GB 	USB type C power supply adaptor with United Kingdom plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1AU 	USB type C power supply adaptor with Australia plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1CN 	USB type C power supply adaptor with China plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1KR 	USB type C power supply adaptor with Korea plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1IN 	USB type C power supply adaptor with India plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1AR 	USB type C power supply adaptor with Argentina plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1BR 	USB type C power supply adaptor with Brazil plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.

Power supply, cables and adapters

Country-specific AC line cords, Grounded 3-Prong

[Cradles](#)

[Batteries](#)













[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

SKU#	Description
23844-00-00R	 North America (United States, Canada, Mexico) Commonly used with chargers mounted in server racks; 7.5 feet long
50-16000-678R	 North America (United States, Canada, Mexico) 0.9 meters (3 feet) long
50-16000-221R	 North America (United States, Canada, Mexico) 1.8 meters (6 feet) long
50-16000-727R	 Brazil 1.8 meters (6 feet) long
50-16000-680R	 Argentina 1.8 meters (6 feet) long
50-16000-217R	 American Samoa, Australia, New Guinea 1.8 meters (6 feet) long
50-16000-218R	 Japan 1.8 meters (6 feet) long
50-16000-219R	 Antigua, Bermuda, Burma, Channel Islands, Hong Kong, Iraq, Ireland, Malaysia, North Ireland, Scotland, Singapore, United Kingdom, Wales 1.8 meters (6 feet) long
50-16000-257R	 China 1.8 meters (6 feet) long
50-16000-220R	 Europe, Abu Dhabi, Bolivia, Dubai, Egypt, Iran, Korea, Russia, Vietnam 1.8 meters (6 feet) long
50-16000-671R	 Italy 1.8 meters (6 feet) long
50-16000-669R	 India, South Africa, Africa 1.8 meters (6 feet) long

Soft Goods

[Hand Strap, and Screen Protector](#)

[Soft Holster, Stylus, and Tether](#)

Soft Goods

Hand Strap, and Screen Protector

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#

Description

Hand Strap

SKU# **SG-TC5A7A-HDSTP-01**



TC701 Hand Strap

- Allows device to be easily held in palm of hand.
 - Attaches directly to device.
 - Includes loop for holding optional stylus.
 - Also available as a 3-pack — 3 hand straps— SKU# SG-TC5A7A-HDSTP-03
- * Please note this accessory is a consumable and may require replacement during the device's lifespan.

Screen Protector

SKU# **SG-TC5A7A-SCRNP-01**



TC701 Screen Protector

- SKU# SG-TC5A7A-SCRNP-01
 - Screen protector - Tempered glass.
 - Includes alcohol wipes, cleaning cloth, and instructions needed for screen protector installation.
 - Also available as a 3-pack — 3 screen protectors — SKU# SG-TC5A7A-SCRNP-03.
- * Please note this accessory is a consumable and may require replacement during the device's lifespan.
-

Soft Holster, Stylus, and Tether

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
<p>Soft Holster SKU# SG-NGTC5TC7-HLSTR-01</p> 	<p>TC701 Soft Holster</p> <ul style="list-style-type: none">• Vertical orientation with open bucket design to accommodate TC501 with optional pistol-grip trigger handle, and / or hand strap.• Strap on rear of holster allows adjustment for use with the accessory options mentioned above.• Includes loop for storage of optional stylus. Nonrotating for maximum durability.• Holster is leather material and includes cut-out for speaker output. <p>* Please note this accessory is a consumable and may require replacement during the device's lifespan.</p>
<p>Stylus SKU# SG-STYLUS-TCX-MTL-03</p> 	<p>TC701 Stylus</p> <ul style="list-style-type: none">• Heavy-duty and made from stainless steel / brass. No plastic parts — real-pen feel. Can be used in rain.• Micro-knit, hybrid-mesh, fiber tip provides silent, smooth gliding use. 5" length.• Big improvement over rubber-tipped or plastic-tipped stylus.• Compatible with all capacitive touch screen devices.• Tether to device or hand strap using SKU# SG-TC5NGTC7NG-TETHR-03. <p>* Please note this accessory is a consumable and may require replacement during the device's lifespan.</p>
<p>Tether SKU# SG-TC5NGTC7NG-TETHR-03</p> 	<p>TC701 Stylus Tether</p> <ul style="list-style-type: none">• When hand strap is used, tether should attach to hand strap SKU# SG-TC5A7A-HDSTP-01 directly (not to terminal towel bar).• String type tether prevents loss of stylus.• NOTE: Other Zebra coiled tethers are not recommended for use with TC701 as they may interfere with other accessories. <p>* Please note this accessory is a consumable and may require replacement during the device's lifespan.</p>

Trigger Handle

[Electronic Trigger Handle and Wrist Strap](#)

Trigger Handle

Electronic Trigger Handle and Wrist Strap

[Cradles](#)

[Batteries](#)



[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
<p>Electronic Trigger Handle SKU# TRG-TC7A-ELEC-01</p> 	<p>TC701 Electronic Trigger Handle</p> <ul style="list-style-type: none">• The drop specification is 7 feet to concrete.• Uses electrical trigger via contacts on back side of TC701.• Trigger handle accessory offers customers the option of using the product in a gun form factor, ideal for scan-intensive situations.• Compatible with both standard and extended capacity batteries.• Sold separately: Optional wrist strap SKU# SG-PD40-WLD1-01.
<p>Wrist Strap SKU# 50-12500-066</p> 	<p>Wrist Strap</p> <ul style="list-style-type: none">• Attaches to bottom of Snap-on Trigger Handle SKU# TRG-TC7A-ELEC-01. <p>* Please note this accessory is a consumable and may require replacement during the device's lifespan.</p>

Headsets

[Close gaps, Open possibilities with Workcloud Sync](#)

Usher in a new era of transformation—one led by your frontline and powered by Zebra Workcloud Sync. One where communication and information flows freely and gaps between teams, workflows and data are closed.

With Workcloud Sync, hindered workers become effective problem solvers, contributing their best. Critical workflows are streamlined in one place, on one device, equipping workers with the information they need, right at their fingertips.

Only Zebra offers the most complete lineup of software and rugged hardware with the scalability, support and service needed to make the greatest impact where it counts—on the frontline.

Learn more about how you can elevate your frontline workers with Zebra Workcloud Sync.

[Rugged Bluetooth HD voice headsets for the most demanding industrial environments](#)

When it comes to enabling speech-driven applications and voice communications in warehouses, manufacturing plants and outdoor yards, you need a headset that is specially designed for the job. The HS3100 Bluetooth Headset is loaded with features that offer everything you need in an industrial headset.

[Learn more about how these headsets deliver a superior voice experience](#)

Wireless headsets and accessories for voice-directed picking

Headsets

Wired Headset for Workcloud Sync

[Cradles](#)

[Batteries](#)

[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
Wired Headset SKU# HDST-USBC-PTT1-01	PTT headset with USB-C connector; one-piece solution. <ul style="list-style-type: none">• For Push-To-Talk (PTT) applications with volume up / volume down / PTT buttons. Compatible with PTT Express / PTT Pro.• Rotating earpiece allows for right or left ear configuration. Mono headset with microphone.• Includes clip for attaching PTT button to clothing.



Headsets

Rugged Bluetooth Headset

[Cradles](#)

[Batteries](#)






[Power Supplies,
Cables and
Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Headsets](#)

[Third Party
Accessories](#)

Item/SKU#	Description
HS31 00 Bluetooth Headset SKU# HS3100-OTH 	HS3100 Rugged Bluetooth Headset <ul style="list-style-type: none">• HS3100 Rugged Bluetooth Headset Over-The-Head Headband includes HS3100 Boom Module and HSX100 OTH Headband Module
HS31 00 Bluetooth Headset SKU# HS3100-BTN-L 	HS3100 Rugged Bluetooth Headset <ul style="list-style-type: none">• HS3100 Rugged Bluetooth Headset (Behind-the-neck headband left)
HS31 00 Bluetooth Headset SKU# HS3100-OTH-SB 	HS3100 Rugged Bluetooth Headset <ul style="list-style-type: none">• HS3100 Rugged Bluetooth Headset (Over-the-head headband) includes HS3100 Shortened Boom Module and HSX100 OTH headband module
HS31 00 Bluetooth Headset SKU# HS3100-BTN-LSB 	HS3100 Rugged Bluetooth Headset <ul style="list-style-type: none">• HS3100 Rugged Bluetooth Headset (Behind-the-neck headband left) includes HS3100 Shortened Boom Module and HSX100 BTN headband module
HS31 00 Bluetooth Headset SKU# HS3100-SBOOM-01 	HS3100 Rugged Bluetooth Boom Module <ul style="list-style-type: none">• HS3100 Shortened Boom Module (includes microphone boom, battery and wind screen)

Third Party Accessories

[RAM Vehicle Docks](#)

[ProClip Vehicle Cradles](#)

[Isiris Mounting Solution](#)



RAM® Vehicle Docks for Zebra TC701



Key Features



Pogo Pin Charging
Uses integrated pogo pins and device docking contacts to protect the charge port and enhance ruggedness.



USB-C Connectivity
Integrated USB-C connector supports charging, data transfer, and Workstation Connect, enabling fast, confident docking while reducing connector wear.



Removable Inserts
Custom inserts, or “shims”, ensure a secure fit and smooth, fumble-free docking.



Wireless Charger Compatible
Add a RAM® Wireless Charger directly to the dock when a Wireless Charging Battery is installed for seamless wireless charging.

Compatible Docks

3PTY-RAM-HOL-ZE41-1U
RAM® Powered Dock with Pogo Pins for TC701

3PTY-RAM-HOL-ZE41L-1U
RAM® Locking Powered Dock with Pogo Pins for TC701

3PTY-RAM-HOL-ZE41C-1U
RAM® Powered Dock with USB-C for TC701

3PTY-RAM-HOL-ZE41KL-C-1U
RAM® Locking Powered Dock with USB-C for TC701

3PTY-RAM-HOL-ZE41-NPU
RAM® Cradle for TC501/TC701
Wireless Charger Compatible

3PTY-RAM-HOL-ZE41KL-NPU
RAM® Locking Cradle for TC501/TC701
Wireless Charger Compatible

Hardwire Chargers



3PTY-RAM-GDS-CHARGE-V3C-3U
GDS® 10-30V Power Delivery Hardwire Charger with Male USB Type-C

3PTY-RAMGDSCHARGEM55V7B1U
GDS® 10-30V Hardwire Charger with USB-A to DC Cable





TC701 CRADLES



- Non-charge, Pogo-pin or USB-C dock connector options
- Channeled sidewalls guide the device for perfect docking
- Tilt-swivel on back can angle 15 degrees for optimal viewing
- Works with hand strap and extended battery
- Custom-fit to the device
- Drop-in style for easy one-handed docking and undocking
- Holds the device firmly and securely in place
- Made from durable ABS and Acetal plastic
- Designed for MIL-STD standard vehicle vibration
- For a complete mounting solution pair this cradle with an AMPS compatible mount

TC701 Cradles and Accessories

TC701 Cradles			
PART #	NON-CHARGE	POGO PIN CONNECTOR	USB-C CONNECTOR
3PTY-PCLIP-701470		•	
3PTY-PCLIP-701473			•
3PTY-PCLIP-711470	•		

Power supply not included. See table below.

POWER SUPPLIES	CIG PLUG POWER	HARD WIRED POWER	POGO PIN CONNECTOR	USB-C CONNECTOR
3PTY-PCLIP-945081		•	•	
3PTY-PCLIP-945082	•		•	
3PTY-PCLIP-217239		•		•
3PTY-PCLIP-945014	•			•

Complete TC701 Product Line ▶ [Zebra TC701 Cradles](#)

Mounting Options for a Complete Solution ▶ [Pedestal Mounts](#) | [Forklift Mounts](#)

Or Contact Us ▶ b2binsidesales@proclipusa.com

EXPLORE OUR
ZEBRA PRODUCT LINE



Universal suction cup holder

simply
practical



**A COMFORTABLE
AND SECURE
MOUNTING
SOLUTION**

- Ultra strong
- Quick-release

It.no. 3PTY-IS-599600
Universal suction cup holder
with arm 3.54"/90 mm
and quick-release lever

